


Inductors, Commercial, Molded, Axial Leaded



ELECTRICAL SPECIFICATIONS

Inductance Tolerance: $\pm 10\%$ on Q-meter for $1\ \mu\text{H}$ to $22\ \mu\text{H}$ $\pm 5\%$ 1000 cps bridge for $27\ \mu\text{H}$ to $10\ 000\ \mu\text{H}$

Note

- L and Q are not always tested at the same frequency. Inductance values tested on Q-meter, are tested at standard test frequencies.

Dielectric Strength: $700\ V_{\text{RMS}}$ at sea level

Operating Temperature: $-55\ ^\circ\text{C}$ to $+125\ ^\circ\text{C}$

Self-Resonant Frequency: Minimum SRF measured with full length leads on grid-dip meter

Q: Measured on a Q-meter

Rating: $1/2\ \text{W}$ dissipation for L models

MECHANICAL SPECIFICATIONS

Terminal Strength: Meets 5 lb pull test when tested per MIL-PRF-15305 (latest revision)

FEATURES

- Miniature shielded inductor
- High inductance-to-size ratio
- Inductance range is $0.10\ \mu\text{H}$ to $180\ 000\ \mu\text{H}$
- Encapsulated non-flammable shielded unit
- $0.164\ \text{''}$ [$4.17\ \text{mm}$] diameter by $0.450\ \text{''}$ [$11.43\ \text{mm}$] long envelope
- Offers extremely high inductance for density packaging
- Compliant to RoHS directive 2002/95/EC



RoHS
COMPLIANT

DENSITY SPECIFICATIONS

Weight: 4.1 g maximum


ENVIRONMENTAL SPECIFICATIONS

Moisture Resistance: Meets requirements of MIL-PRF-15305

Shock Resistance: Meets requirements of MIL-PRF-15305

Vibration: High frequency, 10 Hz to 2000 Hz at $20\ \text{G} \pm 10\%$ maximum for 12 logarithmic swings, each of 20 min duration repeated for each of three mutually perpendicular planes

DIMENSIONS in inches [millimeters]



STANDARD ELECTRICAL SPECIFICATIONS

MODEL ⁽¹⁾	IND. (μH)	TOL. (%)	Q MIN.	TEST FREQUENCY Q (MHz)	SRF MIN. (MHz)	DCR MAX. (Ω)	RATED DC CURRENT (mA)	IRON CORE
IM-10RFCL-12	1.0	± 10	130	15	136	0.03	4000	
IM-10RFCL-12	1.2	± 10	130	15	124	0.03	4000	
IM-10RFCL-12	1.5	± 10	130	10	112	0.03	4000	
IM-10RFCL-12	1.8	± 10	130	10	100	0.03	4000	
IM-10RFCL-12	2.2	± 10	130	10	92	0.04	3500	
IM-10RFCL-12	2.7	± 10	100	10	82	0.04	3500	
IM-10RFCL-12	3.3	± 10	100	7.9	72	0.04	3500	
IM-10RFCL-12	3.9	± 10	80	7.9	68	0.05	3100	
IM-10RFCL-12	4.7	± 10	75	7.9	64	0.05	3100	
IM-10RFCL-12	5.6	± 10	65	7.9	58	0.06	3000	
IM-10RFCL-12	6.8	± 10	65	7.9	52	0.06	3000	
IM-10RFCL-12	8.2	± 10	65	7.9	46	0.11	2400	
IM-10RFCL-12	10	± 10	75	5.0	40	0.15	1800	
IM-10RFCL-12	12	± 10	75	5.0	36	0.23	1600	
IM-10RFCL-12	15	± 10	75	5.0	32	0.3	1300	
IM-10RFCL-12	18	± 10	75	5.0	29	0.4	1150	
IM-10RFCL-12	22	± 10	75	2.5	26	0.5	1000	

Note

⁽¹⁾ Model electricals and tolerances shown

STANDARD ELECTRICAL SPECIFICATIONS							
MODEL ⁽¹⁾	IND. (μH)	TOL. (%)	Q MIN.	TEST FREQUENCY Q (MHz)	SRF MIN. (MHz)	DCR MAX. (Ω)	RATED DC CURRENT (mA)
IM-10RFCL-12	27	± 5	70	2.5	24	0.6	900
IM-10RFCL-12	33	± 5	70	2.5	22	0.7	850
IM-10RFCL-12	39	± 5	70	2.5	21	1.1	720
IM-10RFCL-12	47	± 5	75	2.5	20	1.3	620
IM-10RFCL-12	56	± 5	80	2.5	18	1.8	540
IM-10RFCL-12	68	± 5	100	2.5	16	2.4	450
IM-10RFCL-12	82	± 5	100	2.5	14	2.8	425
IM-10RFCL-12	100	± 5	100	1.5	13	3.2	400
IM-10RFCL-12	120	± 5	100	1.5	12	4.8	360
IM-10RFCL-12	150	± 5	100	1.0	11	6.4	280
IM-10RFCL-12	180	± 5	95	1.0	10	9.5	240
IM-10RFCL-12	220	± 5	95	1.0	9	12	200
IM-10RFCL-12	270	± 5	70	1.0	7	13	195
IM-10RFCL-12	330	± 5	65	0.79	6	14	190
IM-10RFCL-12	390	± 5	65	0.79	5	15.5	180
IM-10RFCL-12	470	± 5	60	0.79	4	17	170
IM-10RFCL-12	560	± 5	75	0.50	3	18.5	165
IM-10RFCL-12	680	± 5	75	0.50	2.50	20	155
IM-10RFCL-12	820	± 5	75	0.50	2.00	22	150
IM-10RFCL-12	1000	± 5	75	0.50	1.90	24	145
IM-10RFCL-12	1200	± 5	75	0.50	1.70	27	137
IM-10RFCL-12	1500	± 5	75	0.40	1.50	29	130
IM-10RFCL-12	1800	± 5	65	0.40	1.40	32	125
IM-10RFCL-12	2200	± 5	65	0.25	1.20	35	120
IM-10RFCL-12	2700	± 5	65	0.25	1.00	40	112
IM-10RFCL-12	3300	± 5	65	0.25	0.95	45	105
IM-10RFCL-12	3900	± 5	65	0.25	0.80	49	100
IM-10RFCL-12	4700	± 5	65	0.25	0.75	53	95
IM-10RFCL-12	5600	± 5	65	0.25	0.70	60	90
IM-10RFCL-12	6800	± 5	65	0.25	0.60	67	85
IM-10RFCL-12	8200	± 5	65	0.25	0.50	75	82
IM-10RFCL-12	10 000	± 5	65	0.15	0.45	80	80

IRON CORE

Note

⁽¹⁾ Model electricals and tolerances shown

MARKING
- Color coded

ORDERING INFORMATION				
IM-10RFCL-12	1.0 μH	10 %	EZ	e2
MODEL	INDUCTANCE VALUE	INDUCTANCE TOLERANCE	PACKAGE CODE	JEDEC LEAD (Pb)-FREE STANDARD

GLOBAL PART NUMBER															
I	M	1	0	R	F	C	L	E	Z	1	R	0	K	1	2
MODEL							PACKAGE CODE		INDUCTANCE VALUE			INDUCTANCE TOLERANCE	SERIES		



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.