

# High Frequency, Surface Mount, Laser Spiral, Coated Inductors



## FEATURES

- Very small size
- High self-resonant frequency values
- High Q values relative to size at higher frequencies
- Coated coil provides protection and moisture resistance
- Compatible with vapor phase and infrared reflow soldering
- Tape and reel packaging for automatic handling, 10 000/reel, EIA-481
- L and Q value not affected by mounting orientation
- Compliant to RoHS Directive 2002/95/EC
- Halogen-free according to IEC 61249-2-21 definition



**RoHS**  
COMPLIANT  
HALOGEN  
**FREE**

STANDARD ELECTRICAL SPECIFICATIONS							
IND. (nH)	TOL.	TEST FREQ. (MHz)		Q MIN.	SRF MIN. (MHz)	DCR MAX. ( $\Omega$ )	RATED DC CURRENT (mA) <sup>(1)</sup>
		L	Q				
1.0	0.3 nH, 0.2 nH	100	800	21	6000	0.05	400
1.2	0.3 nH, 0.2 nH	100	800	21	6000	0.06	400
1.5	0.3 nH, 0.2 nH	100	800	21	6000	0.07	400
1.8	0.3 nH, 0.2 nH	100	800	21	6000	0.08	400
2.2	0.3 nH, 0.2 nH	100	800	21	6000	0.09	400
2.7	0.3 nH, 0.2 nH	100	800	21	5500	0.10	400
3.3	0.3 nH, 0.2 nH	100	800	21	5500	0.12	400
3.9	0.3 nH, 0.2 nH	100	800	20	5200	0.15	360
4.7	0.3 nH, 0.2 nH	100	800	20	4800	0.17	360
5.6	0.3 nH, 0.2 nH	100	800	20	4600	0.19	340
6.8	5 %	100	800	19	4000	0.30	320
8.2	5 %	100	800	19	3500	0.35	320
10	5 %, 2 %	100	800	19	2800	0.41	320
12	5 %, 2 %	100	800	19	2800	0.45	320
15	5 %, 2 %	100	800	19	2500	0.60	240
18	5 %, 2 %	100	800	19	2200	0.70	240
22	5 %, 2 %	100	800	19	2000	0.80	200
27	5 %, 2 %	100	800	19	1800	1.20	200
33	5 %, 2 %	100	800	18	1800	1.40	170
39	5 %, 2 %	100	800	18	1800	1.70	150
47	5 %, 2 %	100	800	17	1800	2.10	140
56	5 %, 2 %	100	800	17	1500	2.50	130
68	5 %, 2 %	100	800	15	1500	4.00	120
82	5 %, 2 %	100	800	15	1400	4.50	110
100	5 %, 2 %	100	800	14	1200	5.50	90

### Note

(1) Value obtained when current flows and temperature has risen 15 °C

## ELECTRICAL SPECIFICATIONS

**Inductance Range:** 1.0 nH to 100 nH

**Inductance and Tolerance:**  $\pm 0.3$  nH for 1.0 nH to 5.6 nH,  $\pm 5$  % for 6.8 nH to 100 nH


**Operating Temperature:** - 40 °C to + 100 °C

**Core Material:** Ceramic

## TEST EQUIPMENT

- Inductance and Q measured on HP4291B
- SRF measured on HP8753E
- DCR measured on HP4338B

## DIMENSIONS in inches [millimeters]



## DESCRIPTION

<b>IMC-0402</b>	<b>10 nH</b>	<b><math>\pm 5</math> %</b>	<b>ER</b>	<b>e3</b>
MODEL	INDUCTANCE VALUE	INDUCTANCE TOLERANCE	PACKAGE CODE	JEDEC LEAD (Pb)-FREE STANDARD

## GLOBAL PART NUMBER

<b>I</b> <b>M</b> <b>C</b>	<b>0</b> <b>4</b> <b>0</b> <b>2</b>	<b>E</b> <b>R</b>	<b>1</b> <b>0</b> <b>N</b>	<b>J</b>
PRODUCT FAMILY	SIZE	PACKAGE CODE	INDUCTANCE VALUE	TOL.



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.