

Inductors, Subminiature, Shielded, Axial Leaded



ELECTRICAL SPECIFICATIONS

Inductance Tolerance: $\pm 10\%$ on Q-meter

Dielectric Strength: 700 V_{RMS} at sea level

Operating Temperature: - 55 °C to + 125 °C

Self-Resonant Frequency: Minimum SRF measured with full length leads on grid-dip meter

Rating: Maximum current based on 1/3 W dissipation

MECHANICAL SPECIFICATIONS

Terminal Strength: Meets 5 lb pull test

FEATURES

- Classification is grade 2, class B
- Inductance range is 0.10 μ H to 1000 μ H
- High inductance-to-size ratio
- 0.133" [3.38 mm] diameter by 0.335" [8.51 mm] length
- Subminiature shielded inductor
- Solves special problems in density circuit application
- Compliant to RoHS directive 2002/95/EC




RoHS
COMPLIANT

DENSITY SPECIFICATIONS

Weight: 0.50 g maximum

Shielding: Less than 3 % coupling with two units mounted side by side at 1000 cycles

DIMENSIONS in inches [millimeters]



STANDARD ELECTRICAL SPECIFICATIONS

MODEL	IND. (μ H)	TOL. (%)	Q MIN.	TEST FREQUENCY (MHz)	SRF MIN. (MHz)	DCR MAX. (Ω)	RATED DC CURRENT (mA)	INCREMENTAL CURRENT (mA) ⁽¹⁾	
IMS-2WWD-40	0.10	± 10	42	25	> 400	0.112	1720	> 1720	PHENOLIC
IMS-2WWD-40	0.12	± 10	42	25	> 400	0.126	1630	> 1630	
IMS-2WWD-40	0.15	± 10	42	25	> 400	0.138	1550	> 1550	
IMS-2WWD-40	0.18	± 10	42	25	366	0.165	1420	> 1420	
IMS-2WWD-40	0.22	± 10	42	25	331	0.198	1330	> 1330	
IMS-2WWD-40	0.27	± 10	42	25	298	0.220	1230	> 1230	
IMS-2WWD-40	0.33	± 10	42	25	288	0.258	1140	> 1140	
IMS-2WWD-40	0.39	± 10	42	25	271	0.292	1060	> 1060	
IMS-2WWD-40	0.47	± 10	41	25	247	0.360	960	> 960	
IMS-2WWD-40	0.56	± 10	39	25	236	0.397	915	> 915	
IMS-2WWD-40	0.68	± 10	36	25	216	0.472	840	> 840	
IMS-2WWD-40	0.82	± 10	35	25	200	0.638	720	> 720	
IMS-2WWD-40	1.0	± 10	42	25	136	0.208	1260	> 1260	IRON
IMS-2WWD-40	1.2	± 10	38	7.9	120	0.225	1210	> 1210	
IMS-2WWD-40	1.5	± 10	38	7.9	111	0.265	1120	> 1120	
IMS-2WWD-40	1.8	± 10	38	7.9	103	0.285	1080	> 1080	
IMS-2WWD-40	2.2	± 10	36	7.9	94	0.330	1000	> 1000	
IMS-2WWD-40	2.7	± 10	38	7.9	85	0.381	935	> 935	
IMS-2WWD-40	3.3	± 10	38	7.9	78	0.432	875	> 875	
IMS-2WWD-40	3.9	± 10	40	7.9	73	0.576	755	> 755	
IMS-2WWD-40	4.7	± 10	42	7.9	66	0.787	650	> 650	
IMS-2WWD-40	5.6	± 10	42	7.9	62	1.04	565	> 565	
IMS-2WWD-40	6.8	± 10	45	7.9	54	1.40	485	> 485	
IMS-2WWD-40	8.2	± 10	47	7.9	50	1.68	440	> 440	
IMS-2WWD-40	10	± 10	51	7.9	44	2.58	355	> 355	
IMS-2WWD-40	12	± 10	51	2.5	39	3.65	300	> 300	

Note

⁽¹⁾ Incremental Current: The DC current required to cause a 5 % reduction in the nominal inductance value

STANDARD ELECTRICAL SPECIFICATIONS								
MODEL	IND. (μH)	TOL. (%)	Q MIN.	TEST FREQUENCY (MHz)	SRF MIN. (MHz)	DCR MAX. (Ω)	RATED DC CURRENT (mA)	INCREMENTAL CURRENT (mA) ⁽¹⁾
IMS-2WWD-40	15	± 10	45	2.5	44	0.862	620	200
IMS-2WWD-40	18	± 10	43	2.5	40	1.02	570	175
IMS-2WWD-40	22	± 10	42	2.5	36	1.12	545	160
IMS-2WWD-40	27	± 10	37	2.5	33	1.28	510	155
IMS-2WWD-40	33	± 10	46	2.5	30	1.70	440	150
IMS-2WWD-40	39	± 10	38	2.5	26	1.99	405	145
IMS-2WWD-40	47	± 10	42	2.5	23	2.41	370	140
IMS-2WWD-40	56	± 10	41	2.5	22	2.85	340	130
IMS-2WWD-40	68	± 10	46	2.5	18	3.21	320	120
IMS-2WWD-40	82	± 10	46	2.5	17	3.57	305	115
IMS-2WWD-40	100	± 10	43	2.5	15	4.10	280	100
IMS-2WWD-40	120	± 10	50	0.79	13	5.97	235	80
IMS-2WWD-40	150	± 10	49	0.79	12	7.05	215	68
IMS-2WWD-40	180	± 10	56	0.79	11	8.12	200	64
IMS-2WWD-40	220	± 10	53	0.79	10	14.8	150	60
IMS-2WWD-40	270	± 10	57	0.79	9	16.8	140	58
IMS-2WWD-40	330	± 10	57	0.79	8.5	18.6	130	56
IMS-2WWD-40	390	± 10	57	0.79	8	21.1	120	54
IMS-2WWD-40	470	± 10	50	0.79	7	32.2	100	52
IMS-2WWD-40	560	± 10	50	0.79	6	36.4	95	50
IMS-2WWD-40	680	± 10	56	0.79	5.5	41.1	90	48
IMS-2WWD-40	820	± 10	49	0.79	5	45.0	85	47
IMS-2WWD-40	1000	± 10	49	0.79	4.5	52.0	80	45

FERRITE

Note

⁽¹⁾ Incremental Current: The DC current required to cause a 5 % reduction in the nominal inductance value

MARKING
- Color coded

ORDERING INFORMATION				
IMS-2WWD-40	0.10 μH	10 %	ER	e2
MODEL	INDUCTANCE VALUE	INDUCTANCE TOLERANCE	PACKAGE CODE	JEDEC LEAD (Pb)-FREE STANDARD

GLOBAL PART NUMBER															
I	M	S	0	2	W	W	D	E	R	R	1	0	K	4	0
MODEL							PACKAGE CODE		INDUCTANCE VALUE			INDUCTANCE TOLERANCE		SERIES	



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.