

## Surface Mount Transformers/Inductors, Gapped and Ungapped, Custom Configurations Available



**ELECTRICAL SPECIFICATIONS**

**Inductance Range:** 10  $\mu$ H to 3900  $\mu$ H, measured at 0.10 V RMS at 10 kHz without DC current, using an HP 4263A or 4284A impedance analyzer


**DC Resistance Range:** 0.06  $\Omega$  to 18.0  $\Omega$ , measured at + 25 °C  $\pm$  5 °C

**Rated Current Range:** 1.00 amps to 0.06 amps

**Dielectric Withstanding Voltage:** 500 V RMS, 60 Hz, 5 seconds



**RoHS COMPLIANT**



**NOTE:** Pad layout guidelines per MIL-STD-275E (printed wiring for electronic equipment).  
Tolerances: xx  $\pm$  0.01" [ $\pm$  0.25 mm]. xxx  $\pm$  0.005" [ $\pm$  0.12 mm]

| STANDARD ELECTRICAL SPECIFICATIONS |                 |            |                  |                 |                               |                             |
|------------------------------------|-----------------|------------|------------------|-----------------|-------------------------------|-----------------------------|
| MODEL                              | IND. ( $\mu$ H) | IND. TOL.  | SCHEMATIC LETTER | DCR MAX. (Ohms) | MAX. RATED* DC CURRENT (Amps) | SATURATING CURRENT** (Amps) |
| <b>Ungapped Models (A)</b>         |                 |            |                  |                 |                               |                             |
| LPE3325ER100NU                     | 10              | $\pm$ 30 % | A                | 0.06            | 1.01                          | N/A                         |
| LPE3325ER150NU                     | 15              | $\pm$ 30 % | A                | 0.08            | 0.91                          | N/A                         |
| LPE3325ER220NU                     | 22              | $\pm$ 30 % | A                | 0.09            | 0.83                          | N/A                         |
| LPE3325ER330NU                     | 33              | $\pm$ 30 % | A                | 0.11            | 0.75                          | N/A                         |
| LPE3325ER470NU                     | 47              | $\pm$ 30 % | A                | 0.14            | 0.69                          | N/A                         |
| LPE3325ER680NU                     | 68              | $\pm$ 30 % | A                | 0.16            | 0.63                          | N/A                         |
| LPE3325ER101NU                     | 100             | $\pm$ 30 % | A                | 0.20            | 0.57                          | N/A                         |
| LPE3325ER151NU                     | 150             | $\pm$ 30 % | A                | 0.76            | 0.29                          | N/A                         |
| LPE3325ER221NU                     | 220             | $\pm$ 30 % | A                | 0.92            | 0.26                          | N/A                         |
| LPE3325ER331NU                     | 330             | $\pm$ 30 % | A                | 1.13            | 0.24                          | N/A                         |
| LPE3325ER471NU                     | 470             | $\pm$ 30 % | A                | 1.35            | 0.22                          | N/A                         |
| LPE3325ER681NU                     | 680             | $\pm$ 30 % | A                | 1.62            | 0.20                          | N/A                         |
| LPE3325ER102NU                     | 1000            | $\pm$ 30 % | A                | 1.97            | 0.18                          | N/A                         |
| LPE3325ER152NU                     | 1500            | $\pm$ 30 % | A                | 2.41            | 0.16                          | N/A                         |
| LPE3325ER222NU                     | 2200            | $\pm$ 30 % | A                | 3.00            | 0.15                          | N/A                         |
| LPE3325ER332NU                     | 3300            | $\pm$ 30 % | A                | 5.96            | 0.10                          | N/A                         |
| LPE3325ER392NU                     | 3900            | $\pm$ 30 % | A                | 7.00            | 0.10                          | N/A                         |
| <b>Gapped Models (B)</b>           |                 |            |                  |                 |                               |                             |
| LPE3325ER100MG                     | 10              | $\pm$ 20 % | A                | 0.22            | 0.54                          | 1.480                       |
| LPE3325ER150MG                     | 15              | $\pm$ 20 % | A                | 0.27            | 0.48                          | 1.240                       |
| LPE3325ER220MG                     | 22              | $\pm$ 20 % | A                | 0.42            | 0.39                          | 1.050                       |
| LPE3325ER330MG                     | 33              | $\pm$ 20 % | A                | 0.65            | 0.31                          | 0.872                       |
| LPE3325ER470MG                     | 47              | $\pm$ 20 % | A                | 0.97            | 0.26                          | 0.740                       |
| LPE3325ER680MG                     | 68              | $\pm$ 20 % | A                | 1.45            | 0.21                          | 0.622                       |
| LPE3325ER101MG                     | 100             | $\pm$ 20 % | A                | 2.22            | 0.17                          | 0.518                       |
| LPE3325ER151MG                     | 150             | $\pm$ 20 % | A                | 3.55            | 0.13                          | 0.426                       |
| LPE3325ER221MG                     | 220             | $\pm$ 20 % | A                | 4.31            | 0.12                          | 0.354                       |
| LPE3325ER331MG                     | 330             | $\pm$ 20 % | A                | 6.72            | 0.10                          | 0.290                       |
| LPE3325ER471MG                     | 470             | $\pm$ 20 % | A                | 9.83            | 0.08                          | 0.244                       |
| LPE3325ER681MG                     | 680             | $\pm$ 20 % | A                | 14.8            | 0.07                          | 0.204                       |
| LPE3325ER102MG                     | 1000            | $\pm$ 20 % | A                | 18.0            | 0.06                          | 0.169                       |

\* DC current that will create a maximum temperature rise of 30 °C when applied at + 25 °C ambient. \*\* DC current that will typically reduce the initial inductance by 20 %.

**UNGAPPED MODELS:** Highest possible inductance with the lowest DCR and highest Q capability. Beneficial in filter, impedance matching and line coupling devices.

**GAPPED MODELS:** Capable of handling large amounts of DC current, tighter inductance tolerance with better temperature stability than ungapped models. Beneficial in DC to DC converters or other circuits carrying DC currents or requiring inductance stability over a temperature range.

| DESCRIPTION        |      |                  |                      |      |              |                               |   |                  |   |   |      |      |   |
|--------------------|------|------------------|----------------------|------|--------------|-------------------------------|---|------------------|---|---|------|------|---|
| LPE                | 3325 | 1000 $\mu$ H     | $\pm$ 30 %           | A    | ER           | e2                            |   |                  |   |   |      |      |   |
| MODEL              | SIZE | INDUCTANCE VALUE | INDUCTANCE TOLERANCE | CORE | PACKAGE CODE | JEDEC LEAD (Pb)-FREE STANDARD |   |                  |   |   |      |      |   |
| GLOBAL PART NUMBER |      |                  |                      |      |              |                               |   |                  |   |   |      |      |   |
| L                  | P    | E                | 3                    | 3    | 2            | 5                             | E | R                | 1 | 0 | 2    | N    | U |
| PRODUCT FAMILY     |      |                  | SIZE                 |      |              | PACKAGE CODE                  |   | INDUCTANCE VALUE |   |   | TOL. | CORE |   |

NOTE Series is also available with SnPb terminations by using package code RY for tape and reel (in place of ER) or SM for bulk (in place of EB).

**SCHEMATIC (TOP VIEW)**

**Schematic A**



**NOTE:** Schematic A for both Gapped and Ungapped LPE Series

**ENVIRONMENTAL PERFORMANCE**

| TEST                  | CONDITIONS                         |
|-----------------------|------------------------------------|
| Thermal Cycling       | Withstands - 55 °C to + 125 °C     |
| Operating Temperature | - 55 °C to + 125 °C*               |
| High Humidity         | 85 %                               |
| Soldering Heat        | Tested to + 230 °C                 |
| Mechanical Shock      | Per MIL-STD-202, Method 213 (100G) |
| Vibration             | Per MIL-STD-202, Method 204 (20G)  |
| Solderability         | Per industry standards             |

\* Must be checked in end use application

**PART MARKING**

- Vishay Dale
- Date code
- Marking code (Suffix of model #)
- Pin 1 indicator

**PACKAGING**

**TAPE SPECIFICATIONS:**

Carrier Tape Type: Conductive  
Cover Tape Type: Anti-static  
Cover Tape Adhesion to Carrier: 40 ± 30 grams


**REEL SPECIFICATIONS:**

Diameter (flange): 13" [330.2 mm]  
Maximum Width (over flanges): 1.197" [30.4 mm]

**STANDARDS:** All embossed carrier tape packaging will be accomplished in compliance with latest revision of EIA-481 "Taping of Surface Mount Components for Automatic Placement".

| MODEL    | TAPE WIDTH | COMPONENT PITCH | UNITS PER 13 INCH REEL |
|----------|------------|-----------------|------------------------|
| LPE-3325 | 24 mm      | 12 mm           | 1000                   |

**Tape and Reel Orientation**



**NOTE:** Top view shown with cover tape removed



## Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.