


# Vertical and Horizontal Mount, Through-Hole Toroid Inductors, High Temperature 125 °C, Radial Leaded



## FEATURES

- Seven sizes available from 16.5 mm to 67.6 mm (dia.)
- Wide range of inductance and current ratings
- Toroid design reduces EMI
- Vertical or horizontal mounting options <sup>(1)</sup>
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



RoHS COMPLIANT

## APPLICATION

- Switching power supplies
- EMI / RFI filtering
- output chokes

## Note

<sup>(1)</sup> For horizontal mounting configuration, replace 1U code in the part number with 2U

DIMENSIONS in inches [millimeters]									
VERTICAL MOUNT (MOUNTING CODE - 1U)					HORIZONTAL MOUNT (MOUNTING CODE - 2U)				
MODEL	DIAMETER (D) (max.)	HEIGHT (H) (max.)	NOM. LEAD SPACING (Ls)	NOM. LEAD DIAMETER (Ld)	MODEL	DIAMETER (D) (max.)	HEIGHT (H) (max.)	NOM. LEAD SPACING (Ls)	NOM. LEAD DIAMETER (Ld)
TJ3	0.65 [16.5]	0.30 [7.6]	0.26 ± 0.04 [6.60 ± 1.02]	see TJ3 data	TJ3	0.66 [16.8]	0.32 [8.1]	0.58 ± 0.08 [14.7 ± 2.03]	see TJ3 data
TJ4	0.88 [22.4]	0.40 [10.2]	0.31 ± 0.09 [7.87 ± 2.29]	see TJ4 data	TJ4	0.88 [22.4]	0.40 [10.2]	0.78 ± 0.10 [19.8 ± 2.54]	see TJ4 data
TJ5	1.00 [25.4]	0.45 [11.4]	0.37 ± 0.08 [9.40 ± 2.03]	see TJ5 data	TJ5	1.00 [25.4]	0.45 [11.4]	0.90 ± 0.10 [22.9 ± 2.54]	see TJ5 data
TJ6	1.38 [35.1]	0.83 [21.1]	0.73 ± 0.10 [18.5 ± 2.54]	see TJ6 data	TJ6	1.38 [35.1]	0.83 [21.1]	1.22 ± 0.16 [31.0 ± 4.06]	see TJ6 data
TJ7	1.65 [41.9]	0.75 [19.1]	0.62 ± 0.13 [15.8 ± 3.30]	see TJ7 data	TJ7	1.65 [41.9]	0.75 [19.1]	1.48 ± 0.17 [37.6 ± 4.32]	see TJ7 data
TJ8	1.92 [48.8]	1.00 [25.4]	0.82 ± 0.18 [20.8 ± 4.57]	see TJ8 data	TJ8	1.94 [49.3]	1.00 [25.4]	1.76 ± 0.18 [44.7 ± 4.57]	see TJ8 data
TJ9	2.66 [67.6]	1.42 [36.1]	1.25 ± 0.17 [31.8 ± 4.32]	see TJ9 data	TJ9	2.72 [69.1]	1.42 [36.1]	2.49 ± 0.23 [63.2 ± 5.84]	see TJ9 data

## Notes

- On larger units and units with finer wire, additional mechanical mounting is recommended.
- <sup>(2)</sup> Leads stripped to within 0.062" [1.58 mm] of the coil.



ENVIRONMENTAL PERFORMANCE		
TEST	CONDITIONS	SPECIFICATIONS
Thermal Shock	Test condition B1	MIL-STD-202, method 107
Resistance to Soldering Heat	-	MIL-STD-202, method 210
Solderability	-	MIL-STD-202, method 208

ELECTRICAL SPECIFICATION RANGES			
MODEL	INDUCTANCE RANGE (μH) <sup>(1)</sup>	DC RESISTANCE RANGE (Ω) <sup>(2)</sup>	RATED CURRENT RANGE (A) <sup>(3)</sup>
TJ3	1.2 to 1500	0.006 to 1.476	10.0 to 0.5
TJ4	1.2 to 1500	0.006 to 0.952	10.7 to 0.9
TJ5	1.2 to 1500	0.006 to 0.539	10.1 to 1.3
TJ6	1.2 to 2700	0.004 to 0.499	16.0 to 2.0
TJ7	1.2 to 2700	0.005 to 0.359	16.0 to 2.7
TJ8	1.5 to 3900	0.005 to 0.304	18.5 to 3.2
TJ9	1.5 to 5600	0.004 to 0.224	20.0 to 5.0

**Notes**

- Operating temperature range: -55 °C to +125 °C
- <sup>(3)</sup> Measured at 0.25 V<sub>RMS</sub> at 10 kHz
- <sup>(4)</sup> DC resistance measured at + 25 °C ± 5 °C
- <sup>(5)</sup> Maximum continuous operating current based on a calculated temperature rise of 40 °C

STANDARD ELECTRICAL SPECIFICATIONS in inches [millimeters]														
PART NUMBER	IND. (μH)	TOL. (%)	DCR NOM. (Ω)	RATED DC CURRENT (A)	IND. NOM. AT 0 DCA (μH)	INDUCTANCE SHIFT WITH DC CURRENT <sup>(1)</sup>								LEAD DIAMETER "A"
						10 % DRO P (A)	IND. MIN. (μH)	20 % DRO P (A)	IND. MIN. (μH)	30 % DRO P (A)	IND. MIN. (μH)	40 % DRO P (A)	IND. MIN. (μH)	
TJ31UEB1R2M	1.2	± 20	0.006	10.0	1.19	5.50	0.91	8.88	0.81	12.69	0.71	16.50	0.61	0.032 [0.813]
TJ31UEB1R5M	1.5	± 20	0.006	9.5	1.62	4.71	1.24	7.62	1.10	10.88	0.96	14.14	0.82	0.032 [0.813]
TJ31UEB2R2L	2.2	± 15	0.007	9.0	2.11	4.13	1.62	6.66	1.44	9.52	1.26	12.38	1.08	0.032 [0.813]
TJ31UEB2R7L	2.7	± 15	0.008	8.4	2.67	3.67	2.04	5.92	1.82	8.46	1.59	11.00	1.36	0.032 [0.813]
TJ31UEB3R3L	3.3	± 15	0.008	8.2	3.30	3.30	2.52	5.33	2.24	7.62	1.96	9.90	1.68	0.032 [0.813]
TJ31UEB3R9L	3.9	± 15	0.009	7.9	3.99	3.00	3.05	4.85	2.72	6.92	2.38	9.00	2.04	0.032 [0.813]
TJ31UEB4R7L	4.7	± 15	0.010	7.5	4.75	2.75	3.64	4.44	3.23	6.35	2.83	8.25	2.42	0.032 [0.813]
TJ31UEB5R6L	5.6	± 15	0.011	7.3	5.58	2.54	4.27	4.10	3.79	5.86	3.32	7.62	2.84	0.032 [0.813]
TJ31UEB6R8L	6.8	± 15	0.011	7.1	6.47	2.36	4.95	3.81	4.40	5.44	3.85	7.07	3.30	0.032 [0.813]
TJ31UEB8R2L	8.2	± 15	0.013	6.6	8.45	2.06	6.46	3.33	5.74	4.76	5.03	6.19	4.31	0.032 [0.813]
TJ31UEB100L	10.0	± 15	0.013	6.5	9.54	1.94	7.30	3.14	6.49	4.48	5.67	5.82	4.86	0.032 [0.813]
TJ31UEB120L	12.0	± 15	0.015	6.1	11.91	1.74	9.11	2.81	8.10	4.01	7.09	5.21	6.08	0.032 [0.813]
TJ31UEB150L	15.0	± 15	0.016	5.9	14.55	1.57	11.13	2.54	9.90	3.63	8.66	4.71	7.42	0.032 [0.813]
TJ31UEB180L	18.0	± 15	0.017	5.6	17.46	1.43	13.35	2.32	11.87	3.31	10.39	4.30	8.90	0.032 [0.813]
TJ31UEB220L	22.0	± 15	0.024	4.6	22.31	1.27	17.07	2.05	15.17	2.93	13.27	3.81	11.38	0.029 [0.737]
TJ31UEB270L	27.0	± 15	0.026	4.4	27.75	1.14	21.23	1.84	18.87	2.63	16.51	3.41	14.15	0.029 [0.737]
TJ31UEB330L	33.0	± 15	0.029	4.3	33.79	1.03	25.85	1.67	22.98	2.38	20.11	3.09	17.23	0.029 [0.737]
TJ31UEB390L	39.0	± 15	0.038	3.7	38.15	0.97	29.18	1.57	25.94	2.24	22.70	2.91	19.46	0.025 [0.635]
TJ31UEB470L	47.0	± 15	0.043	3.5	47.65	0.87	36.45	1.40	32.40	2.00	28.35	2.61	24.30	0.025 [0.635]
TJ31UEB560L	56.0	± 15	0.057	3.1	55.47	0.80	42.44	1.30	37.72	1.86	33.01	2.41	28.29	0.023 [0.584]
TJ31UEB680L	68.0	± 15	0.063	3.0	66.83	0.73	51.12	1.18	45.44	1.69	39.76	2.20	34.08	0.023 [0.584]
TJ31UEB820L	82.0	± 15	0.087	2.6	82.50	0.66	63.11	1.07	56.10	1.52	49.09	1.98	42.08	0.020 [0.508]
TJ31UEB101L	100.0	± 15	0.097	2.4	99.83	0.60	76.37	0.97	67.88	1.38	59.40	1.80	50.91	0.020 [0.508]
TJ31UEB121L	120.0	± 15	0.107	2.3	118.80	0.55	90.88	0.89	80.78	1.27	70.69	1.65	60.59	0.020 [0.508]

**Note**

- The DC current values listed are typical values that drop the nominal inductance by the percent listed



STANDARD ELECTRICAL SPECIFICATIONS in inches [millimeters]														
PART NUMBER	IND. (μH)	TOL. (%)	DCR NOM. (Ω)	RATED DC CURRENT (A)	IND. NOM. AT 0 DCA (μH)	INDUCTANCE SHIFT WITH DC CURRENT (1)								LEAD DIAMETER "A"
						10 % DRO P (A)	IND. MIN. (μH)	20 % DRO P (A)	IND. MIN. (μH)	30 % DRO P (A)	IND. MIN. (μH)	40 % DRO P (A)	IND. MIN. (μH)	
TJ31UEB151L	150.0	± 15	0.146	1.9	148.14	0.49	113.32	0.80	100.73	1.14	88.14	1.48	75.55	0.018 [0.457]
TJ31UEB181L	180.0	± 15	0.164	1.8	180.71	0.45	138.24	0.72	122.88	1.03	107.52	1.34	92.16	0.018 [0.457]
TJ31UEB221L	220.0	± 15	0.225	1.5	221.89	0.40	169.75	0.65	150.89	0.93	132.03	1.21	113.16	0.016 [0.406]
TJ31UEB271L	270.0	± 15	0.250	1.4	267.30	0.37	204.48	0.59	181.76	0.85	159.04	1.10	136.32	0.016 [0.406]
TJ31UEB331L	330.0	± 15	0.342	1.2	330.00	0.33	252.45	0.53	224.40	0.76	196.35	0.99	168.30	0.014 [0.356]
TJ31UEB391L	390.0	± 15	0.378	1.1	392.07	0.30	299.94	0.49	266.61	0.70	233.28	0.91	199.96	0.014 [0.356]
TJ31UEB471L	470.0	± 15	0.510	1.0	467.31	0.28	357.49	0.45	317.77	0.64	278.05	0.83	238.33	0.013 [0.330]
TJ31UEB561L	560.0	± 15	0.565	0.9	557.70	0.25	426.64	0.41	379.24	0.59	331.83	0.76	284.43	0.013 [0.330]
TJ31UEB681L	680.0	± 15	0.637	0.8	684.29	0.23	523.48	0.37	465.32	0.53	407.15	0.69	348.99	0.013 [0.330]
TJ31UEB821L	820.0	± 15	0.849	0.7	823.81	0.21	630.22	0.34	560.19	0.48	490.17	0.63	420.14	0.011 [0.279]
TJ31UEB102L	1000.0	± 15	0.951	0.7	999.11	0.19	764.32	0.31	679.39	0.44	594.47	0.57	509.55	0.011 [0.279]
TJ31UEB122L	1200.0	± 15	1.298	0.6	1203.87	0.17	920.96	0.28	818.63	0.40	716.30	0.52	613.98	0.010 [0.254]
TJ31UEB152L	1500.0	± 15	1.476	0.5	1497.18	0.15	1145.34	0.25	1018.08	0.36	890.82	0.46	763.56	0.010 [0.254]
TJ41UEB1R2M	1.2	± 20	0.006	10.7	1.09	8.75	0.83	14.14	0.74	20.20	0.65	26.26	0.55	0.032 [0.813]
TJ41UEB1R5M	1.5	± 20	0.006	10.2	1.57	7.29	1.20	11.78	1.06	16.83	0.93	21.88	0.80	0.032 [0.813]
TJ41UEB2R2L	2.2	± 15	0.007	9.7	2.13	6.25	1.63	10.10	1.45	14.43	1.27	18.75	1.09	0.032 [0.813]
TJ41UEB2R7L	2.7	± 15	0.008	9.5	2.78	5.47	2.13	8.84	1.89	12.62	1.66	16.41	1.42	0.032 [0.813]
TJ41UEB3R3M	3.3	± 20	0.009	8.8	3.52	4.86	2.70	7.85	2.40	11.22	2.10	14.59	1.80	0.032 [0.813]
TJ41UEB4R7M	4.7	± 20	0.010	8.5	4.35	4.38	3.33	7.07	2.96	10.10	2.59	13.13	2.22	0.032 [0.813]
TJ41UEB5R6M	5.6	± 20	0.010	8.3	5.26	3.98	4.03	6.43	3.58	9.18	3.13	11.93	2.68	0.032 [0.813]
TJ41UEB6R8M	6.8	± 20	0.011	8.1	6.26	3.65	4.79	5.89	4.26	8.42	3.73	10.94	3.19	0.032 [0.813]
TJ41UEB8R2L	8.2	± 15	0.013	7.8	8.53	3.13	6.52	5.05	5.80	7.21	5.07	9.38	4.35	0.032 [0.813]
TJ41UEB100L	10.0	± 15	0.013	7.4	9.79	2.92	7.49	4.71	6.66	6.73	5.82	8.75	4.99	0.032 [0.813]
TJ41UEB120M	12.0	± 20	0.015	7.1	12.57	2.57	9.62	4.16	8.55	5.94	7.48	7.72	6.41	0.032 [0.813]
TJ41UEB150M	15.0	± 20	0.017	6.8	15.70	2.30	12.01	3.72	10.68	5.31	9.34	6.91	8.01	0.032 [0.813]
TJ41UEB180L	18.0	± 15	0.017	6.7	17.40	2.19	13.31	3.53	11.83	5.05	10.35	6.56	8.87	0.032 [0.813]
TJ41UEB220L	22.0	± 15	0.019	6.5	21.05	1.99	16.11	3.21	14.32	4.59	12.53	5.97	10.74	0.032 [0.813]
TJ41UEB270L	27.0	± 15	0.021	6.1	27.19	1.75	20.80	2.83	18.49	4.04	16.18	5.25	13.87	0.032 [0.813]
TJ41UEB330L	33.0	± 15	0.024	5.8	34.10	1.56	26.09	2.52	23.19	3.61	20.29	4.69	17.39	0.032 [0.813]
TJ41UEB390L	39.0	± 15	0.025	5.7	39.15	1.46	29.95	2.36	26.62	3.37	23.29	4.38	19.97	0.032 [0.813]
TJ41UEB470L	47.0	± 15	0.028	5.5	47.37	1.33	36.24	2.14	32.21	3.06	28.19	3.98	24.16	0.032 [0.813]
TJ41UEB560L	56.0	± 15	0.031	5.2	56.38	1.22	43.13	1.96	38.34	2.81	33.54	3.65	28.75	0.032 [0.813]
TJ41UEB680L	68.0	± 15	0.040	4.6	66.16	1.12	50.62	1.81	44.99	2.59	39.37	3.37	33.74	0.029 [0.737]
TJ41UEB820L	82.0	± 15	0.045	4.4	80.43	1.02	61.53	1.64	54.69	2.35	47.86	3.05	41.02	0.029 [0.737]
TJ41UEB101L	100.0	± 15	0.062	3.7	100.22	0.91	76.67	1.47	68.15	2.10	59.63	2.73	51.11	0.025 [0.635]
TJ41UEB121L	120.0	± 15	0.070	3.5	122.19	0.83	93.48	1.33	83.09	1.91	72.70	2.48	62.32	0.025 [0.635]
TJ41UEB151L	150.0	± 15	0.079	3.3	151.42	0.74	115.84	1.20	102.97	1.71	90.10	2.23	77.23	0.025 [0.635]
TJ41UEB181L	180.0	± 15	0.105	2.9	178.18	0.68	136.30	1.10	121.16	1.58	106.01	2.05	90.87	0.023 [0.584]
TJ41UEB221L	220.0	± 15	0.118	2.7	219.28	0.62	167.75	1.00	149.11	1.42	130.47	1.85	111.83	0.023 [0.584]
TJ41UEB271L	270.0	± 15	0.162	2.3	271.48	0.55	207.68	0.89	184.61	1.28	161.53	1.66	138.46	0.020 [0.508]
TJ41UEB331L	330.0	± 15	0.181	2.2	329.25	0.50	251.88	0.81	223.89	1.16	195.90	1.51	167.92	0.020 [0.508]
TJ41UEB391L	390.0	± 15	0.243	1.9	392.59	0.46	300.33	0.74	266.96	1.06	233.59	1.38	200.22	0.018 [0.457]
TJ41UEB471L	470.0	± 15	0.269	1.8	470.50	0.42	359.93	0.68	319.94	0.97	279.95	1.26	239.95	0.018 [0.457]
TJ41UEB561L	560.0	± 15	0.297	1.7	555.45	0.39	424.92	0.63	377.71	0.89	330.49	1.16	283.28	0.018 [0.457]
TJ41UEB681L	680.0	± 15	0.406	1.4	679.69	0.35	519.96	0.57	462.19	0.81	404.41	1.05	346.64	0.016 [0.406]
TJ41UEB821L	820.0	± 15	0.452	1.3	816.45	0.32	624.59	0.52	555.19	0.74	485.79	0.96	416.39	0.016 [0.406]
TJ41UEB102L	1000.0	± 15	0.617	1.1	1005.02	0.29	768.84	0.47	683.42	0.66	597.99	0.86	512.56	0.014 [0.356]
TJ41UEB122L	1200.0	± 15	0.684	1.0	1198.69	0.26	916.99	0.43	815.11	0.61	713.22	0.79	611.33	0.014 [0.356]
TJ41UEB152L	1500.0	± 15	0.952	0.9	1504.93	0.24	1151.27	0.38	1023.35	0.54	895.43	0.71	767.51	0.013 [0.330]

Note

- The DC current values listed are typical values that drop the nominal inductance by the percent listed



STANDARD ELECTRICAL SPECIFICATIONS in inches [millimeters]														
PART NUMBER	IND. (μH)	TOL. (%)	DCR NOM. (Ω)	RATED DC CURRENT (A)	IND. NOM. AT 0 DCA (μH)	INDUCTANCE SHIFT WITH DC CURRENT (1)								LEAD DIAMETER "A"
						10 % DRO P (A)	IND. MIN. (μH)	20 % DRO P (A)	IND. MIN. (μH)	30 % DRO P (A)	IND. MIN. (μH)	40 % DRO P (A)	IND. MIN. (μH)	
TJ51UEB1R2M	1.2	± 20	0.006	10.1	1.15	10.63	0.88	17.18	0.78	24.54	0.68	31.90	0.59	0.032 [0.813]
TJ51UEB1R5V	1.5	± 25	0.007	9.5	1.66	8.86	1.27	14.32	1.13	20.45	0.99	26.59	0.84	0.032 [0.813]
TJ51UEB2R2L	2.2	± 15	0.008	9.0	2.25	7.60	1.72	12.27	1.53	17.53	1.34	22.79	1.15	0.032 [0.813]
TJ51UEB2R7V	2.7	± 25	0.009	8.6	2.94	6.65	2.25	10.74	2.00	15.34	1.75	19.94	1.50	0.032 [0.813]
TJ51UEB3R9L	3.9	± 15	0.010	8.2	3.73	5.91	2.85	9.54	2.53	13.63	2.22	17.72	1.90	0.032 [0.813]
TJ51UEB4R7L	4.7	± 15	0.010	7.9	4.60	5.32	3.52	8.59	3.13	12.27	2.74	15.95	2.35	0.032 [0.813]
TJ51UEB5R6L	5.6	± 15	0.011	7.7	5.57	4.83	4.26	7.81	3.78	11.16	3.31	14.50	2.84	0.032 [0.813]
TJ51UEB6R8L	6.8	± 15	0.012	7.5	6.62	4.43	5.07	7.16	4.50	10.23	3.94	13.29	3.38	0.032 [0.813]
TJ51UEB8R2L	8.2	± 15	0.013	7.3	7.77	4.09	5.95	6.61	5.29	9.44	4.63	12.27	3.96	0.032 [0.813]
TJ51UEB100L	10.0	± 15	0.015	7.0	10.35	3.54	7.92	5.73	7.04	8.18	6.16	10.63	5.28	0.032 [0.813]
TJ51UEB120L	12.0	± 15	0.016	6.9	11.78	3.32	9.01	5.37	8.01	7.67	7.01	9.97	6.01	0.032 [0.813]
TJ51UEB150L	15.0	± 15	0.017	6.6	14.90	2.95	11.40	4.77	10.13	6.82	8.87	8.86	7.60	0.032 [0.813]
TJ51UEB180L	18.0	± 15	0.019	6.4	18.40	2.66	14.08	4.29	12.51	6.14	10.95	7.98	9.38	0.032 [0.813]
TJ51UEB220L	22.0	± 15	0.021	6.2	22.26	2.42	17.03	3.90	15.14	5.58	13.25	7.25	11.35	0.032 [0.813]
TJ51UEB270L	27.0	± 15	0.023	6.0	26.50	2.22	20.27	3.58	18.02	5.11	15.77	6.65	13.51	0.032 [0.813]
TJ51UEB330L	33.0	± 15	0.025	5.7	33.53	1.97	25.65	3.18	22.80	4.54	19.95	5.91	17.10	0.032 [0.813]
TJ51UEB390L	39.0	± 15	0.027	5.5	38.69	1.83	29.59	2.96	26.31	4.23	23.02	5.50	19.73	0.032 [0.813]
TJ51UEB470L	47.0	± 15	0.029	5.3	47.10	1.66	36.03	2.68	32.03	3.83	28.03	4.99	24.02	0.032 [0.813]
TJ51UEB560L	56.0	± 15	0.032	5.2	56.35	1.52	43.11	2.45	38.32	3.51	33.53	4.56	28.74	0.032 [0.813]
TJ51UEB680L	68.0	± 15	0.035	5.1	66.42	1.40	50.81	2.26	45.17	3.23	39.52	4.20	33.88	0.032 [0.813]
TJ51UEB820L	82.0	± 15	0.038	5.0	81.14	1.27	62.08	2.05	55.18	2.92	48.28	3.80	41.38	0.032 [0.813]
TJ51UEB101L	100.0	± 15	0.042	4.9	97.34	1.16	74.46	1.87	66.19	2.67	57.91	3.47	49.64	0.032 [0.813]
TJ51UEB121L	120.0	± 15	0.047	4.8	119.65	1.04	91.53	1.68	81.36	2.41	71.19	3.13	61.02	0.032 [0.813]
TJ51UEB151L	150.0	± 15	0.054	4.7	149.45	0.93	114.33	1.51	101.63	2.15	88.93	2.80	76.22	0.032 [0.813]
TJ51UEB181L	180.0	± 15	0.060	4.6	182.57	0.84	139.67	1.36	124.15	1.95	108.63	2.53	93.11	0.032 [0.813]
TJ51UEB221L	220.0	± 15	0.067	4.2	219.01	0.77	167.54	1.24	148.92	1.78	130.31	2.31	111.69	0.032 [0.813]
TJ51UEB271L	270.0	± 15	0.092	3.7	272.73	0.69	208.64	1.12	185.46	1.59	162.28	2.07	139.09	0.029 [0.737]
TJ51UEB331L	330.0	± 15	0.104	3.5	332.35	0.63	254.25	1.01	226.00	1.44	197.75	1.88	169.50	0.029 [0.737]
TJ51UEB391L	390.0	± 15	0.138	2.9	389.34	0.58	297.85	0.93	264.75	1.33	231.66	1.73	198.57	0.025 [0.635]
TJ51UEB471L	470.0	± 15	0.154	2.8	469.25	0.53	358.97	0.85	319.09	1.21	279.20	1.58	239.32	0.025 [0.635]
TJ51UEB561L	560.0	± 15	0.205	2.3	556.60	0.48	425.80	0.78	378.49	1.12	331.18	1.45	283.87	0.023 [0.584]
TJ51UEB681L	680.0	± 15	0.232	2.2	684.66	0.44	523.77	0.70	465.57	1.01	407.38	1.31	349.18	0.023 [0.584]
TJ51UEB821L	820.0	± 15	0.260	2.1	825.98	0.40	631.87	0.64	561.66	0.92	491.46	1.19	421.25	0.023 [0.584]
TJ51UEB102L	1000.0	± 15	0.349	1.7	994.01	0.36	760.42	0.58	675.93	0.83	591.44	1.09	506.95	0.020 [0.508]
TJ51UEB122L	1200.0	± 15	0.393	1.6	1207.22	0.33	923.53	0.53	820.91	0.76	718.30	0.98	615.68	0.020 [0.508]
TJ51UEB152L	1500.0	± 15	0.539	1.3	1507.01	0.29	1152.86	0.47	1024.76	0.68	896.67	0.88	768.57	0.018 [0.457]
TJ61UEB1R2M	1.2	± 20	0.004	16.0	1.12	22.38	0.85	36.15	0.76	51.65	0.66	67.14	0.57	0.045 [1.14]
TJ61UEB2R2M	2.2	± 20	0.005	16.0	1.98	16.78	1.52	27.11	1.35	38.73	1.18	50.35	1.01	0.045 [1.14]
TJ61UEB3R3M	3.3	± 20	0.006	16.0	3.10	13.43	2.37	21.69	2.11	30.99	1.84	40.28	1.58	0.045 [1.14]
TJ61UEB4R7L	4.7	± 15	0.007	16.0	4.46	11.19	3.41	18.08	3.04	25.82	2.66	33.57	2.28	0.045 [1.14]
TJ61UEB5R6V	5.6	± 25	0.007	16.0	6.08	9.59	4.65	15.49	4.13	22.13	3.62	28.77	3.10	0.045 [1.14]
TJ61UEB8R2L	8.2	± 15	0.008	15.2	7.94	8.39	6.07	13.56	5.40	19.37	4.72	25.18	4.05	0.045 [1.14]
TJ61UEB100L	10.0	± 15	0.009	14.5	10.04	7.46	7.68	12.05	6.83	17.22	5.98	22.38	5.12	0.045 [1.14]
TJ61UEB120L	12.0	± 15	0.010	13.9	12.40	6.71	9.49	10.85	8.43	15.49	7.38	20.14	6.32	0.045 [1.14]
TJ61UEB150L	15.0	± 15	0.011	13.3	15.00	6.10	11.48	9.86	10.20	14.09	8.93	18.31	7.65	0.045 [1.14]
TJ61UEB180L	18.0	± 15	0.012	12.7	17.86	5.59	13.66	9.04	12.14	12.91	10.62	16.78	9.11	0.045 [1.14]
TJ61UEB220L	22.0	± 15	0.012	12.5	20.96	5.16	16.03	8.34	14.25	11.92	12.47	15.49	10.69	0.045 [1.14]
TJ61UEB270L	27.0	± 15	0.014	11.8	27.90	4.48	21.34	7.23	18.97	10.33	16.60	13.43	14.23	0.045 [1.14]
TJ61UEB330L	33.0	± 15	0.015	11.5	31.74	4.20	24.28	6.78	21.59	9.68	18.89	12.59	16.19	0.045 [1.14]

Note

- The DC current values listed are typical values that drop the nominal inductance by the percent listed



STANDARD ELECTRICAL SPECIFICATIONS in inches [millimeters]														
PART NUMBER	IND. (μH)	TOL. (%)	DCR NOM. (Ω)	RATED DC CURRENT (A)	IND. NOM. AT 0 DCA (μH)	INDUCTANCE SHIFT WITH DC CURRENT <sup>(1)</sup>								LEAD DIAMETER "A"
						10 % DRO P (A)	IND. MIN. (μH)	20 % DRO P (A)	IND. MIN. (μH)	30 % DRO P (A)	IND. MIN. (μH)	40 % DRO P (A)	IND. MIN. (μH)	
TJ61UEB390L	39.0	± 15	0.017	11.0	40.18	3.73	30.73	6.03	27.32	8.61	23.90	11.19	20.49	0.045 [1.14]
TJ61UEB470L	47.0	± 15	0.017	10.7	44.76	3.53	34.24	5.71	30.44	8.15	26.63	10.60	22.83	0.045 [1.14]
TJ61UEB560L	56.0	± 15	0.019	10.4	54.68	3.20	41.83	5.16	37.19	7.38	32.54	9.59	27.89	0.045 [1.14]
TJ61UEB680L	68.0	± 15	0.021	10.0	65.60	2.92	50.18	4.72	44.61	6.74	39.03	8.76	33.45	0.045 [1.14]
TJ61UEB820L	82.0	± 15	0.023	9.5	83.82	2.58	64.13	4.17	57.00	5.96	49.88	7.75	42.75	0.045 [1.14]
TJ61UEB101L	100.0	± 15	0.025	9.2	97.22	2.40	74.37	3.87	66.11	5.53	57.84	7.19	49.58	0.045 [1.14]
TJ61UEB121L	120.0	± 15	0.027	8.8	119.16	2.17	91.16	3.50	81.03	5.00	70.90	6.50	60.77	0.045 [1.14]
TJ61UEB151L	150.0	± 15	0.031	8.6	151.90	1.92	116.20	3.10	103.29	4.43	90.38	5.75	77.47	0.045 [1.14]
TJ61UEB181L	180.0	± 15	0.033	8.5	179.06	1.77	136.98	2.85	121.76	4.08	106.54	5.30	91.32	0.045 [1.14]
TJ61UEB221L	220.0	± 15	0.037	8.4	218.74	1.60	167.33	2.58	148.74	3.69	130.15	4.80	111.56	0.045 [1.14]
TJ61UEB271L	270.0	± 15	0.058	7.4	273.92	1.43	209.55	2.31	186.26	3.30	162.98	4.29	139.70	0.040 [1.02]
TJ61UEB331L	330.0	± 15	0.065	7.0	335.30	1.29	256.50	2.09	228.00	2.98	199.50	3.87	171.00	0.040 [1.02]
TJ61UEB391L	390.0	± 15	0.070	6.7	388.86	1.20	297.48	1.94	264.43	2.77	231.37	3.60	198.32	0.040 [1.02]
TJ61UEB471L	470.0	± 15	0.101	5.5	476.66	1.08	364.64	1.75	324.13	2.50	283.61	3.25	243.09	0.036 [0.914]
TJ61UEB561L	560.0	± 15	0.110	5.3	556.64	1.00	425.83	1.62	378.51	2.31	331.20	3.01	283.88	0.036 [0.914]
TJ61UEB681L	680.0	± 15	0.129	4.4	679.02	0.91	519.45	1.47	461.74	2.09	404.02	2.72	346.30	0.032 [0.813]
TJ61UEB821L	820.0	± 15	0.143	4.2	813.56	0.83	622.38	1.34	553.22	1.91	484.07	2.49	414.92	0.032 [0.813]
TJ61UEB102L	1000.0	± 15	0.160	4.0	1004.40	0.75	768.37	1.21	682.99	1.72	597.62	2.24	512.24	0.032 [0.813]
TJ61UEB122L	1200.0	± 15	0.209	3.3	1190.90	0.69	911.04	1.11	809.81	1.58	708.58	2.06	607.36	0.029 [0.737]
TJ61UEB152L	1500.0	± 15	0.238	3.1	1500.40	0.61	1147.81	0.99	1020.27	1.41	892.74	1.83	765.20	0.029 [0.737]
TJ61UEB182L	1800.0	± 15	0.323	2.6	1785.60	0.56	1365.98	0.90	1214.21	1.29	1062.43	1.68	910.66	0.025 [0.635]
TJ61UEB222L	2200.0	± 15	0.363	2.5	2193.44	0.50	1677.98	0.82	1491.54	1.16	1305.09	1.51	1118.65	0.025 [0.635]
TJ61UEB272L	2700.0	± 15	0.499	2.0	2716.10	0.45	2077.81	0.73	1846.95	1.05	1616.08	1.36	1385.21	0.023 [0.584]
TJ71UEB1R2M	1.2	± 20	0.005	16.0	1.30	21.41	0.99	34.59	0.88	49.42	0.77	64.24	0.66	0.045 [1.14]
TJ71UEB2R2M	2.2	± 20	0.006	16.0	2.03	17.13	1.55	27.67	1.38	39.53	1.20	51.39	1.03	0.045 [1.14]
TJ71UEB2R7M	2.7	± 20	0.007	16.0	2.92	14.28	2.23	23.06	1.98	32.95	1.74	42.83	1.49	0.045 [1.14]
TJ71UEB3R9L	3.9	± 15	0.008	16.0	3.97	12.24	3.04	19.77	2.70	28.24	2.36	36.71	2.02	0.045 [1.14]
TJ71UEB5R6M	5.6	± 20	0.009	16.0	5.18	10.71	3.97	17.30	3.53	24.71	3.08	32.12	2.64	0.045 [1.14]
TJ71UEB6R8L	6.8	± 15	0.010	16.0	6.56	9.52	5.02	15.37	4.46	21.96	3.90	28.55	3.35	0.045 [1.14]
TJ71UEB8R2L	8.2	± 15	0.010	15.5	8.10	8.57	6.20	13.84	5.51	19.77	4.82	25.70	4.13	0.045 [1.14]
TJ71UEB100L	10.0	± 15	0.011	14.9	9.80	7.79	7.50	12.58	6.66	17.97	5.83	23.36	5.00	0.045 [1.14]
TJ71UEB120L	12.0	± 15	0.012	14.4	11.66	7.14	8.92	11.53	7.93	16.47	6.94	21.41	5.95	0.045 [1.14]
TJ71UEB150M	15.0	± 20	0.013	13.5	15.88	6.12	12.15	9.88	10.80	14.12	9.45	18.36	8.10	0.045 [1.14]
TJ71UEB180L	18.0	± 15	0.014	13.0	18.23	5.71	13.94	9.22	12.39	13.18	10.84	17.13	9.29	0.045 [1.14]
TJ71UEB220M	22.0	± 20	0.015	12.8	20.74	5.35	15.86	8.65	14.10	12.35	12.34	16.06	10.58	0.045 [1.14]
TJ71UEB270L	27.0	± 15	0.016	12.2	26.24	4.76	20.08	7.69	17.85	10.98	15.62	14.28	13.38	0.045 [1.14]
TJ71UEB330L	33.0	± 15	0.018	11.6	32.40	4.28	24.79	6.92	22.03	9.88	19.28	12.85	16.52	0.045 [1.14]
TJ71UEB390L	39.0	± 15	0.019	11.2	39.20	3.89	29.99	6.29	26.66	8.99	23.33	11.68	19.99	0.045 [1.14]
TJ71UEB470L	47.0	± 15	0.020	10.8	46.66	3.57	35.69	5.77	31.73	8.24	27.76	10.71	23.79	0.045 [1.14]
TJ71UEB560L	56.0	± 15	0.022	10.5	54.76	3.29	41.89	5.32	37.23	7.60	32.58	9.88	27.93	0.045 [1.14]
TJ71UEB680L	68.0	± 15	0.024	10.0	68.12	2.95	52.11	4.77	46.32	6.82	40.53	8.86	34.74	0.045 [1.14]
TJ71UEB820L	82.0	± 15	0.026	9.6	82.94	2.68	63.45	4.32	56.40	6.18	49.35	8.03	42.30	0.045 [1.14]
TJ71UEB101L	100.0	± 15	0.027	9.2	99.23	2.45	75.91	3.95	67.47	5.65	59.04	7.34	50.60	0.045 [1.14]
TJ71UEB121L	120.0	± 15	0.030	8.9	116.96	2.25	89.48	3.64	79.54	5.20	69.59	6.76	59.65	0.045 [1.14]
TJ71UEB151L	150.0	± 15	0.033	8.6	149.77	1.99	114.57	3.22	101.84	4.60	89.11	5.98	76.38	0.045 [1.14]
TJ71UEB181L	180.0	± 15	0.036	8.5	178.93	1.82	136.88	2.94	121.67	4.21	106.46	5.47	91.25	0.045 [1.14]
TJ71UEB221L	220.0	± 15	0.040	8.4	219.02	1.65	167.55	2.66	148.94	3.80	130.32	4.94	111.70	0.045 [1.14]
TJ71UEB271L	270.0	± 15	0.046	8.3	272.48	1.48	208.45	2.39	185.29	3.41	162.13	4.43	138.97	0.045 [1.14]
TJ71UEB331L	330.0	± 15	0.051	8.2	331.78	1.34	253.81	2.16	225.61	3.09	197.41	4.02	169.21	0.045 [1.14]

Note

- The DC current values listed are typical values that drop the nominal inductance by the percent listed





STANDARD ELECTRICAL SPECIFICATIONS in inches [millimeters]														
PART NUMBER	IND. (μH)	TOL. (%)	DCR NOM. (Ω)	RATED DC CURRENT (A)	IND. NOM. AT 0 DCA (μH)	INDUCTANCE SHIFT WITH DC CURRENT (1)							LEAD DIAMETER "A"	
						10 % DRO P (A)	IND. MIN. (μH)	20 % DRO P (A)	IND. MIN. (μH)	30 % DRO P (A)	IND. MIN. (μH)	40 % DRO P (A)		IND. MIN. (μH)
TJ71UEB391L	390.0	± 15	0.053	7.9	385.64	1.24	295.02	2.01	262.24	2.86	229.46	3.72	196.68	0.045 [1.14]
TJ71UEB471L	470.0	± 15	0.060	7.5	467.86	1.13	357.91	1.82	318.14	2.60	278.37	3.38	238.61	0.045 [1.14]
TJ71UEB561L	560.0	± 15	0.066	7.2	558.01	1.03	426.88	1.67	379.45	2.38	332.02	3.10	284.58	0.045 [1.14]
TJ71UEB681L	680.0	± 15	0.090	5.9	685.58	0.93	524.47	1.50	466.20	2.15	407.92	2.79	349.65	0.040 [1.02]
TJ71UEB821L	820.0	± 15	0.101	5.6	826.28	0.85	632.10	1.37	561.87	1.96	491.64	2.54	421.40	0.040 [1.02]
TJ71UEB102L	1000.0	± 15	0.136	4.7	998.00	0.77	763.47	1.25	678.64	1.78	593.81	2.32	508.98	0.036 [0.914]
TJ71UEB122L	1200.0	± 15	0.152	4.4	1205.60	0.70	922.29	1.13	819.81	1.62	717.33	2.11	614.86	0.036 [0.914]
TJ71UEB152L	1500.0	± 15	0.174	4.2	1498.18	0.63	1146.10	1.02	1018.76	1.45	891.41	1.89	764.07	0.036 [0.914]
TJ71UEB182L	1800.0	± 15	0.233	3.5	1798.28	0.57	1375.68	0.93	1222.83	1.33	1069.98	1.72	917.12	0.032 [0.813]
TJ71UEB222L	2200.0	± 15	0.263	3.3	2205.23	0.52	1687.00	0.84	1499.55	1.20	1312.11	1.56	1124.66	0.032 [0.813]
TJ71UEB272L	2700.0	± 15	0.359	2.7	2712.61	0.47	2075.15	0.76	1844.57	1.08	1614.00	1.40	1383.43	0.029 [0.737]
TJ81UEB1R5M	1.5	± 20	0.005	18.5	1.60	26.12	1.22	42.20	1.09	60.28	0.95	78.36	0.82	0.051 [1.30]
TJ81UEB2R7M	2.7	± 20	0.006	18.5	2.50	20.90	1.91	33.76	1.70	48.22	1.49	62.69	1.28	0.051 [1.30]
TJ81UEB3R9M	3.9	± 20	0.007	18.5	3.60	17.41	2.75	28.13	2.45	40.19	2.14	52.24	1.84	0.051 [1.30]
TJ81UEB4R7L	4.7	± 15	0.008	18.5	4.90	14.93	3.75	24.11	3.33	34.45	2.92	44.78	2.50	0.051 [1.30]
TJ81UEB6R8M	6.8	± 20	0.009	18.5	6.40	13.06	4.90	21.10	4.35	30.14	3.81	39.18	3.26	0.051 [1.30]
TJ81UEB8R2L	8.2	± 15	0.010	18.5	8.10	11.61	6.20	18.75	5.51	26.79	4.82	34.83	4.13	0.051 [1.30]
TJ81UEB100L	10.0	± 15	0.011	18.5	10.00	10.45	7.65	16.88	6.80	24.11	5.95	31.35	5.10	0.051 [1.30]
TJ81UEB120L	12.0	± 15	0.012	18.0	12.10	9.50	9.26	15.34	8.23	21.92	7.20	28.50	6.17	0.051 [1.30]
TJ81UEB150M	15.0	± 20	0.013	17.3	14.40	8.71	11.02	14.07	9.79	20.09	8.57	26.12	7.34	0.051 [1.30]
TJ81UEB180M	18.0	± 20	0.014	16.6	16.90	8.04	12.93	12.98	11.49	18.55	10.06	24.11	8.62	0.051 [1.30]
TJ81UEB220L	22.0	± 15	0.015	15.5	22.50	6.97	17.21	11.25	15.30	16.07	13.39	20.90	11.48	0.051 [1.30]
TJ81UEB270L	27.0	± 15	0.016	15.0	25.60	6.53	19.58	10.55	17.41	15.07	15.23	19.59	13.06	0.051 [1.30]
TJ81UEB330L	33.0	± 15	0.017	14.1	32.40	5.80	24.79	9.38	22.03	13.40	19.28	17.41	16.52	0.051 [1.30]
TJ81UEB390L	39.0	± 15	0.019	13.4	40.00	5.22	30.60	8.44	27.20	12.06	23.80	15.67	20.40	0.051 [1.30]
TJ81UEB470L	47.0	± 15	0.021	12.8	48.40	4.75	37.03	7.67	32.91	10.96	28.80	14.25	24.68	0.051 [1.30]
TJ81UEB560L	56.0	± 15	0.022	12.2	57.60	4.35	44.06	7.03	39.17	10.05	34.27	13.06	29.38	0.051 [1.30]
TJ81UEB680L	68.0	± 15	0.024	11.7	67.60	4.02	51.71	6.49	45.97	9.27	40.22	12.06	34.48	0.051 [1.30]
TJ81UEB820L	82.0	± 15	0.025	11.1	84.10	3.60	64.34	5.82	57.19	8.31	50.04	10.81	42.89	0.051 [1.30]
TJ81UEB101L	100.0	± 15	0.027	10.6	102.40	3.27	78.34	5.27	69.63	7.53	60.93	9.80	52.22	0.051 [1.30]
TJ81UEB121L	120.0	± 15	0.029	10.1	122.50	2.99	93.71	4.82	83.30	6.89	72.89	8.96	62.48	0.051 [1.30]
TJ81UEB151L	150.0	± 15	0.032	9.6	152.10	2.68	116.36	4.33	103.43	6.18	90.50	8.04	77.57	0.051 [1.30]
TJ81UEB181L	180.0	± 15	0.034	9.2	176.40	2.49	134.95	4.02	119.95	5.74	104.96	7.46	89.96	0.051 [1.30]
TJ81UEB221L	220.0	± 15	0.036	8.7	220.90	2.22	168.99	3.59	150.21	5.13	131.44	6.67	112.66	0.051 [1.30]
TJ81UEB271L	270.0	± 15	0.040	8.3	270.40	2.01	206.86	3.25	183.87	4.64	160.89	6.03	137.90	0.051 [1.30]
TJ81UEB331L	330.0	± 15	0.044	7.9	324.90	1.83	248.55	2.96	220.93	4.23	193.32	5.50	165.70	0.051 [1.30]
TJ81UEB391L	390.0	± 15	0.047	7.6	384.40	1.69	294.07	2.72	261.39	3.89	228.72	5.06	196.04	0.051 [1.30]
TJ81UEB471L	470.0	± 15	0.053	7.2	476.10	1.51	364.22	2.45	323.75	3.49	283.28	4.54	242.81	0.051 [1.30]
TJ81UEB561L	560.0	± 15	0.058	6.9	562.50	1.39	430.31	2.25	382.50	3.21	334.69	4.18	286.88	0.051 [1.30]
TJ81UEB681L	680.0	± 15	0.064	6.6	672.40	1.27	514.39	2.06	457.23	2.94	400.08	3.82	342.92	0.051 [1.30]
TJ81UEB821L	820.0	± 15	0.071	6.2	828.10	1.15	633.50	1.85	563.11	2.65	492.72	3.44	422.33	0.051 [1.30]
TJ81UEB102L	1000.0	± 15	0.077	6.0	1000.0	1.04	765.00	1.69	680.00	2.41	595.00	3.13	510.00	0.051 [1.30]
TJ81UEB122L	1200.0	± 15	0.104	5.1	1210.00	0.95	925.65	1.53	822.80	2.19	719.95	2.85	617.10	0.045 [1.14]
TJ81UEB152L	1500.0	± 15	0.118	4.9	1488.40	0.86	1138.63	1.38	1012.11	1.98	885.60	2.57	759.08	0.045 [1.14]
TJ81UEB182L	1800.0	± 15	0.159	4.2	1795.60	0.78	1373.63	1.26	1221.01	1.80	1068.38	2.34	915.76	0.040 [1.02]
TJ81UEB222L	2200.0	± 15	0.179	4.0	2190.40	0.71	1675.66	1.14	1489.47	1.63	1303.29	2.12	1117.10	0.040 [1.02]
TJ81UEB272L	2700.0	± 15	0.203	3.9	2689.60	0.64	2057.54	1.03	1828.93	1.47	1600.31	1.91	1371.70	0.040 [1.02]
TJ81UEB332L	3300.0	± 15	0.277	3.3	3312.40	0.57	2533.99	0.93	2252.43	1.32	1970.88	1.72	1689.32	0.036 [0.914]
TJ81UEB392	3900.0	± 15	0.304	3.2	3880.90	0.53	2968.89	0.86	2639.01	1.22	2309.14	1.59	1979.26	0.036 [0.914]

Note

- The DC current values listed are typical values that drop the nominal inductance by the percent listed



STANDARD ELECTRICAL SPECIFICATIONS in inches [millimeters]														
PART NUMBER	IND. (μH)	TOL. (%)	DCR NOM. (Ω)	RATED DC CURRENT (A)	IND. NOM. AT 0 DCA (μH)	INDUCTANCE SHIFT WITH DC CURRENT (1)							LEAD DIAMETER "A"	
						10 % DRO P (A)	IND. MIN. (μH)	20 % DRO P (A)	IND. MIN. (μH)	30 % DROP (A)	IND. MIN. (μH)	40 % DROP (A)		IND. MIN. (μH)
TJ91UEB1R5L	1.5	± 15	0.004	20.0	1.44	50.35	1.10	81.33	0.98	116.18	0.86	151.04	0.73	0.064 [1.63]
TJ91UEB2R7L	2.7	± 15	0.005	20.0	2.56	37.76	1.96	61.00	1.74	87.14	1.52	113.28	1.31	0.064 [1.63]
TJ91UEB3R9L	3.9	± 15	0.006	20.0	4.00	30.21	3.06	48.80	2.72	69.71	2.38	90.62	2.04	0.064 [1.63]
TJ91UEB5R6L	5.6	± 15	0.007	20.0	5.76	25.17	4.41	40.66	3.92	58.09	3.43	75.52	2.94	0.064 [1.63]
TJ91UEB8R2L	8.2	± 15	0.008	20.0	7.84	21.58	6.00	34.85	5.33	49.79	4.66	64.73	4.00	0.064 [1.63]
TJ91UEB100L	10.0	± 15	0.009	20.0	10.24	18.88	7.83	30.50	6.96	43.57	6.09	56.64	5.22	0.064 [1.63]
TJ91UEB120M	12.0	± 20	0.010	20.0	12.96	16.78	9.91	27.11	8.81	38.73	7.71	50.35	6.61	0.064 [1.63]
TJ91UEB150M	15.0	± 20	0.011	20.0	16.00	15.10	12.24	24.40	10.88	34.85	9.52	45.31	8.16	0.064 [1.63]
TJ91UEB180M	18.0	± 20	0.012	20.0	19.36	13.73	14.81	22.18	13.16	31.69	11.52	41.19	9.87	0.064 [1.63]
TJ91UEB220M	22.0	± 20	0.013	20.0	23.04	12.59	17.63	20.33	15.67	29.05	13.71	37.76	11.75	0.064 [1.63]
TJ91UEB270L	27.0	± 15	0.014	20.0	27.04	11.62	20.69	18.77	18.39	26.81	16.09	34.85	13.79	0.064 [1.63]
TJ91UEB330L	33.0	± 15	0.015	20.0	31.36	10.79	23.99	17.43	21.32	24.90	18.66	32.37	15.99	0.064 [1.63]
TJ91UEB390M	39.0	± 20	0.016	20.0	40.96	9.44	31.33	15.25	27.85	21.78	24.37	28.32	20.89	0.064 [1.63]
TJ91UEB470L	47.0	± 15	0.017	20.0	46.24	8.88	35.37	14.35	31.44	20.50	27.51	26.65	23.58	0.064 [1.63]
TJ91UEB560L	56.0	± 15	0.018	19.9	57.76	7.95	44.19	12.84	39.28	18.34	34.37	23.85	29.46	0.064 [1.63]
TJ91UEB680L	68.0	± 15	0.019	19.0	70.56	7.19	53.98	11.62	47.98	16.60	41.98	21.58	35.99	0.064 [1.63]
TJ91UEB820L	82.0	± 15	0.020	18.3	84.64	6.57	64.75	10.61	57.56	15.15	50.36	19.70	43.17	0.064 [1.63]
TJ91UEB101L	100.0	± 15	0.021	17.6	100.00	6.04	76.50	9.76	68.00	13.94	59.50	18.12	51.00	0.064 [1.63]
TJ91UEB121L	120.0	± 15	0.022	17.0	116.64	5.59	89.23	9.04	79.32	12.91	69.40	16.78	59.49	0.064 [1.63]
TJ91UEB151L	150.0	± 15	0.025	15.9	153.76	4.87	117.63	7.87	104.56	11.24	91.49	14.62	78.42	0.064 [1.63]
TJ91UEB181L	180.0	± 15	0.028	15.3	184.96	4.44	141.49	7.18	125.77	10.25	110.05	13.33	94.33	0.064 [1.63]
TJ91UEB221L	220.0	± 15	0.030	14.7	219.04	4.08	167.57	6.59	148.95	9.42	130.33	12.25	111.71	0.064 [1.63]
TJ91UEB271L	270.0	± 15	0.033	14.0	268.96	3.68	205.75	5.95	182.89	8.50	160.03	11.05	137.17	0.064 [1.63]
TJ91UEB331L	330.0	± 15	0.036	13.4	324.00	3.36	247.86	5.42	220.32	7.75	192.78	10.07	165.24	0.064 [1.63]
TJ91UEB391L	390.0	± 15	0.038	12.9	384.16	3.08	293.88	4.98	261.23	7.11	228.58	9.25	195.92	0.064 [1.63]
TJ91UEB471L	470.0	± 15	0.042	12.4	466.56	2.80	356.92	4.52	317.26	6.45	277.60	8.39	237.95	0.064 [1.63]
TJ91UEB561L	560.0	± 15	0.043	11.9	556.96	2.56	426.07	4.14	378.73	5.91	331.39	7.68	284.05	0.064 [1.63]
TJ91UEB681L	680.0	± 15	0.048	11.3	676.00	2.32	517.14	3.75	459.68	5.36	402.22	6.97	344.76	0.064 [1.63]
TJ91UEB821L	820.0	± 15	0.054	10.7	829.44	2.10	634.52	3.39	564.02	4.84	493.52	6.29	423.01	0.064 [1.63]
TJ91UEB102L	1000.0	± 15	0.059	10.3	998.56	1.91	763.90	3.09	679.02	4.41	594.14	5.74	509.27	0.064 [1.63]
TJ91UEB122L	1200.0	± 15	0.082	9.8	1211.04	1.74	926.45	2.80	823.51	4.01	720.57	5.21	617.63	0.057 [1.45]
TJ91UEB152L	1500.0	± 15	0.091	9.3	1505.44	1.56	1151.66	2.52	1023.70	3.59	895.74	4.67	767.77	0.057 [1.45]
TJ91UEB182L	1800.0	± 15	0.118	8.9	1797.76	1.42	1375.29	2.30	1222.48	3.29	1069.67	4.27	916.86	0.051 [1.30]
TJ91UEB222L	2200.0	± 15	0.131	8.4	2190.24	1.29	1675.53	2.09	1489.36	2.98	1303.19	3.87	1117.02	0.051 [1.30]
TJ91UEB272L	2700.0	± 15	0.147	8.0	2704.00	1.16	2068.56	1.88	1838.72	2.68	1608.88	3.49	1379.04	0.051 [1.30]
TJ91UEB332L	3300.0	± 15	0.165	7.6	3317.76	1.05	2538.09	1.69	2256.08	2.42	1974.07	3.15	1692.06	0.051 [1.30]
TJ91UEB392L	3900.0	± 15	0.181	5.2	3893.76	0.97	2978.73	1.56	2647.76	2.23	2316.79	2.90	1985.82	0.051 [1.30]
TJ91UEB472L	4700.0	± 15	0.201	5.1	4678.56	0.88	3579.10	1.43	3181.42	2.04	2783.74	2.65	2386.07	0.051 [1.30]
TJ91UEB562L	5600.0	± 15	0.224	5.0	5595.04	0.81	4280.21	1.30	3804.63	1.86	3329.05	2.42	2853.47	0.051 [1.30]

Note

- The DC current values listed are typical values that drop the nominal inductance by the percent listed

MARKING
- Vishay Dale
- Model number
- Date code



ORDERING INFORMATION					
TJ5	1U	330 $\mu$ H	$\pm 15\%$	EB	e2
MODEL	MOUNTING CODE	INDUCTANCE VALUE	INDUCTANCE TOLERANCE	PACKAGE CODE	JEDEC® LEAD (Pb)-FREE STANDARD

GLOBAL PART NUMBER				
T J 5	1 U	E B	3 3 1	L
MODEL	MOUNTING CODE	PACKAGE CODE	INDUCTANCE VALUE	INDUCTANCE TOLERANCE
	1U = vertical mount 2U = horizontal mount		331 = 330 $\mu$ H	L = $\pm 15\%$





## **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.