

## Half Size Clock Oscillator Enable/Disable



The XOSM-52 series oscillator is half size, has Tri-state enable/disable controlled function. The metal package with pin#4 case ground acts as shielding to minimize EMI radiation.

### FEATURES

- Tri-state enable/disable
- 8 pin half size
- Industry standard
- Wide frequency range
- Low cost
- Resistance weld package
- 5 V
- Lead (Pb)-free and RoHS compliant





STANDARD ELECTRICAL SPECIFICATIONS			
PARAMETER	SYMBOL	CONDITION	XOSM-52
Frequency Range	$F_O$		1 MHz ~ 100.00 MHz
Frequency Stability*		All Condition*	$\pm 25$ ppm, $\pm 50$ ppm, $\pm 100$ ppm
Operating Temperature Range	$T_{OPR}$		0 °C ~ 70 °C (- 40 °C ~ + 85 °C option)
Storage Temperature Range	$T_{STG}$		- 55 °C ~ + 125 °C
Power Supply Voltage	$V_{DD}$		5.0 V $\pm 10$ %
Aging (First Year)		25 °C $\pm 3$ °C	$\pm 5$ ppm
Supply Current	$I_{DD}$	1 MHz to 23.999 MHz	20 mA Max
		24.000 MHz to 49.999 MHz	30 mA Max
		50.000 MHz to 69.999 MHz	40 mA Max
		70.000 MHz to 100.000 MHz	60 mA Max
Output Symmetry	Sym	At 1/2 $V_{DD}$	40/60 % (45/55 % Option)
Rise Time	$T_r$	20 % $V_{DD}$ ~ 80 % $V_{DD}$	10 ns Max
Fall Time	$T_f$	80 % $V_{DD}$ ~ 20 % $V_{DD}$	10 ns Max
Output Voltage	$V_{OH}$		90 % $V_{DD}$ Min
	$V_{OL}$		10 % $V_{DD}$ Max
Output Load	TTL Load		1 ~ 10 TTL
		HCMOS Load	~ 50 M : 50 pF
			~ 70 M : 30 pF
		~ 100 M : 15 pF	
Start-up Time		$T_s$	10 ms Max
Pin 1, tri-state function			Pin 1 = H or open... Output active at pin 5

\* Include: 25 °C tolerance, operating temperature range, input voltage change, aging, load change, shock and vibration.


### DIMENSIONS in inches [millimeters]

STANDARD PIN ORIENTATION




PIN	CONNECTION
#1	N.C.
#4	GND
#5	OUTPUT
#8	$V_{DD}$

ENABLE/DISABLE FUNCTION	
INPUT (PIN 1)	OUTPUT (PIN 5)
OPEN	ENABLE
$V_{DD}$	ENABLE




HCMOS OUTPUT WAVEFORM



### ORDERING INFORMATION

XOSM-52 MODEL	B FREQUENCY STABILITY	R OTR	E ENABLE/DISABLE	40 M FREQUENCY/MHZ	e2 JEDEC LEAD (Pb)-FREE STANDARD
	AA = 0.0025 % (25 ppm) A = 0.005 % (50 ppm) B = 0.01 % (100 ppm) Standard	Blank = 0 °C to 70 °C R = - 40 °C to + 85 °C	Blank = Pin 1 open E = Disable to Tristate		

### GLOBAL PART NUMBER





GLOBAL PART NUMBERING						
MODEL NUMBER	FREQUENCY STABILITY	OPERATING TEMPERATURE (OTR)	ENABLE/DISABLE	PACKAGE CODE	OPTIONS	FREQUENCY
X O 5 2 XO53 = XO-53 XO54 = XO-54 XO34 = XO-543 XO52 = XO-52 XO32 = XO-523 XO56 = XO-56 XOVC = XOVC-23 XO5M = XOSM-52 XO63 = XOSM-533 XO62 = XOSM-532 XO61 = XOSM-531 XO57 = XOSM-57 XO37 = XOSM-573 XO27 = XOSM-572 XO17 = XOSM-571 XO55 = XOSM-55 XO35 = XOSM-553	C C = 0.01 % (100 ppm) D = 0.005 % (50 ppm) E = 0.0025 % (25 ppm)	T T = 0 °C to +70 °C R = -40 °C to +85 °C	E F = Pin 1 Open E = Disable to Tristate	L TAPE AND REEL H = RF7  BULK A = B04 (XO63, XO62, XO61) C = D06 (XO57, XO37, XO27, XO17) D = D07 (XO53, XO54, XO34, XO56, XOVC, XO55, XO35) L = D08 (XO52, XO32, XO5M)	N A NA = No Additional Options 60 = 45/55 Symmetry  Contact factory for all other options	4 0 M 4M = 4 MHz 40M = 40 MHz 100M = 100 MHz 12M288 = 12.288 MHz  M is used as decimal place holder in frequency
Example: XO52CTELNA40M						



## Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.