

Plasma Panel Displays

Dual Linear Bar Graph



PBG-12201 PBG-12203 ⁽¹⁾ PBG-12205 PBG-16101

Note

(1) The PBG-12203 is offered on a limited basis. It is not a drop in replacement for a similar bargraph originally designed and manufactured by Burroughs in the 1970's and 1980's. The VISHAY product has tighter recommended operating parameters.

It is up to each customer to determine suitability of the PBG-12203 in their specific application.

FEATURES

- Two separate bar graphs, each including reset for 1/2 % or 1 % resolution (see chart)
- At normal viewing distances glow blends into continuous, but precisely controlled bar length
- Unique scanning technique minimizes the number of drivers required
- PBG-12203 bars may be scanned from either direction or both directions simultaneously
- PBG-12203 can display four separate columns of information, providing combined total of information does not exceed 201 clock counts per bar

ENVIRONMENTAL SPECIFICATIONS

Altitude: 0 ft to 70 000 ft

Operating Temperature: 0 °C to + 55 °C

Storage Temperature: - 55 °C to + 85 °C

Relative Humidity (No Condensation): 85 % maximum

Vibration: 0.018" DA, 10 Hz to 50 Hz, 2 G, 50 Hz to 2000 Hz

Shock: 50 G, 1/2 sine wave, 11 ms duration

ELECTRICAL SPECIFICATIONS

OPERATING PARAMETERS	PBG-12201				PBG-12203				PBG-12205				PBG-12205			
	Min.	Max.	Rec.	Units	Min.	Max.	Rec.	Units	Min.	Max.	Rec.	Units	Min.	Max.	Rec.	Units
Anode Supply Voltage	235	265	250	V	245	265	250	V	235	265	250	V	235	265	250	V
Cathode Off Bias Voltage	68	76	72	V	70	76	72	V	68	76	72	V	68	76	72	V
Anode Off Bias Voltage	80	120	100	V	80	110	100	V	80	120	100	V	80	120	100	V
Anode Sustaining Voltage (Typical)	-	-	150	V	-	-	150	V	-	-	150	V	-	-	150	V
Refresh Rate	-	-	70	Hz	-	-	70	Hz	-	-	70	Hz	-	-	70	Hz
Keep Alive Anode Resistor	-	-	1M	Ω	-	-	1M	Ω	-	-	1M	Ω	-	-	1M	Ω
Keep Alive Cathode Resistor	-	-	1M	Ω	-	-	1M	Ω	-	-	1M	Ω	-	-	1M	Ω
Keep Alive Current (Typical)	-	-	50	μA	-	-	50	μA	-	-	50	μA	-	-	50	μA
Display Anode Resistor	-	-	36k	Ω	-	-	24k	Ω	-	-	24k	Ω	-	-	20k	Ω
Display Peak Anode Current	2.5	3.0	2.8	mA	4.0	4.5	4.2	mA	3.5	5.0	4.0	mA	4.0	6.0	5.0	mA
Scan Time per Cathode	70	90	70	μs	70	80	70	μs	60	90	70	μs	120	180	140	μs
Applied Reset Pulse Width	140	180	140	μs	140	160	140	μs	70	180	140	μs	120	180	140	μs

OPTICAL SPECIFICATIONS

	PBG-12201	PBG-12203	PBG-12205	PBG-16101
Elements	201	203	201	101
Resolution	1/2 %	1/2 %	1/2 %	1 %
Segment Length	0.100"	0.150"	0.100"	0.100"
Segment Width	0.011"	0.010"	0.011"	0.020"
Segment Spacing	0.020"	0.020"	0.020"	0.050"
Drivers Required	6	12	8	6
Luminance	35 fl	30 fl	70 fl	60 fl
Viewing Angle	120°	120°	120°	120°
Color	Neon Orange	Neon Orange	Neon Orange	Neon Orange



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.