

Plasma Panel Display Modules

DC Character Module with Drive Electronics
TTL Level Data Interface and Integrated DC Converter



The APD-016A070 DC Plasma display offers viewing qualities designers seek such as high contrast, viewing angle of 150° minimum, and long distance readability. It is bright (50 foot lamberts minimum) characters are presented in a pleasing neon orange color against a black background. Plasma is much more readable and eye-pleasing than liquid crystal or vacuum fluorescent displays and is filterable to red, amber or neutral density.

These plasma display panels are driven by refreshing all 14 segments, the decimal point and the comma much like a CRT display. Each character segments are serially entered from segment A thru R (no I, L, O or Q segments) plus the decimal point and comma. Then a latch pulse advances the character, latches the data and turns on the outputs. The designer need only supply TTL level signals for SEGMENT DATA, SEGMENT CLOCK, CHARACTER LATCH and ANODE DATA. The SEGMENT DATA is entered, with the SEGMENT CLOCK up to frequencies as high as 8MHz. After all 14 segments, 1 period and 1 comma have been entered, the CHARACTER LATCH signal is toggled and the SEGMENT DATA is latched. At the time the data is latched, the display is briefly disabled and the character is advanced by the CHARACTER LATCH signal. Once each frame the ANODE DATA must be asserted to synchronize the character location with the SEGMENT DATA. The recommended scanning frequency is approximately 70Hz, but may be as high as 200Hz.

FEATURES

- TTL level interface.
- + 5 VDC only option available.
- High brightness and contrast.
- Large characters.
- On board DC converter.

ELECTRICAL SPECIFICATIONS

Voltage Required: Vdd: + 8 VDC to + 24 VDC.

Power Required: Typical = 4 watts. Maximum = 9 watts.

OPTICAL SPECIFICATIONS

Viewing Area: 10.70" [271.78mm] W x 0.70" [17.78mm] H.

Character Array: 1 x 16.

Character Size: 0.70" [17.78mm] W x 0.44" [11.18mm] H.


Luminance: 50 foot lamberts minimum.


STANDARD ELECTRICAL SPECIFICATIONS*

DESCRIPTION	SYMBOL	MIN.	TYP.	MAX.	UNITS
Display supply	Vdd	+ 8	+ 18 ± 5%	+ 25	VDC
Logic 1 Input	Vih	2.0	—	—	VDC
Logic 0 Input	Vil	—	—	0.8	VDC

*Recommended operating voltages. All maximums are absolute maximum.

DIMENSIONS in inches [millimeters]





PIN DESCRIPTION

P3, POWER CONNECTOR
 AMP #640445-5 or equivalent.
 (Mates with AMP 640428-5, MOLEX 09-50-3051 or equivalent.)

PIN	SIGNAL	DESCRIPTION
1	GND	Logic and Power
2	—	—
3	Vdd	Display Supply
4	KEY	Used to key connector
5	GND	Logic and Power

P2, DATA CONNECTOR
 AMP #103309-2 or equivalent.
 (Mates with AMP 746195-2, MOLEX 39-27-1146 or equivalent.)

PIN	DESCRIPTION	PIN	DESCRIPTION
1	—	2	GROUND
3	ANODE DATA	4	GROUND
5	—	6	GROUND
7	CHARACTER LATCH	8	GROUND
9	SEGMENT CLOCK	10	GROUND
11	SEGMENT DATA	12	GROUND
13	No connect	14	GROUND

ORDERING INFORMATION

DESCRIPTION	PART NUMBER
Display Module with Drivers and TTL Interface	APD-016A070
Data Connector Kit	280105-05
Power Connector Kit	280108-13



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.