


Resin-Coated, Radial-Leaded Solid Tantalum Capacitors



FEATURES

- RoHS Compliant design available
- Flame retardant encapsulation
- Very high temperature range
- Improved humidity class
- Low leakage current
- Very high CV product
- Low failure rate



RoHS*
COMPLIANT

MECHANICAL SPECIFICATIONS

Color: Gold

Laser Marked: Capacity and voltage in clear text;
Plus pole marked


Leads: Standard (Tin/Lead), RoHS compliant (100 % Tin)

Tantalum capacitors with sintered anode and solid semiconductor electrolyte with flame retardant fluidized bed coating. The type ETPW is characterized by very favorable electrical values even at higher ambient temperatures. The capacitors comply with DIN 45910 part 146 and they are also available as a radially taped version.

ORDERING INFORMATION

P1A TYPE	686 CAPACITANCE	603 DC VOLTAGE RATING AT + 85 °C	M CAPACITANCE TOLERANCE	00 LEAD STYLE AND PACKAGING	D	E3 RoHS COMPLIANT
ETPW 1A ETPW 6R	Expressed in picofarads. The first two digits are significant figures. The third is the number of zeros following	Expressed by zeros if needed to complete the 3 digit block. A decimal point is indicated by an "0" (603 = 6.3 Volts)	M = ± 20 % K = ± 10 %	See Lead styles and packaging table		E3 = 100 % tin termination (RoHS compliant design) Blank = SnPb termination (standard design)

DIMENSIONS in millimeters



MODEL	D MAX.	H MAX.	RM ± 0.5	Ø D ± 0.05	FORM DS		FORM L	
					H ₂ MAX.	RM	H ₂ MAX.	RM
ETPW - 1 A, B	4.0	7.1	2.5	0.5	10.5	5	10.5	5
ETPW - 2 C, D	4.5	8.0	2.5	0.5	11.0	5	11.0	5
ETPW - 2 E	5.0	9.5	2.5	0.5	12.5	5	12.5	5
ETPW - 3 F	5.0	9.5	2.5	0.5	12.5	5	12.5	5
ETPW - 3 G	5.5	10.0	2.5	0.5	13.0	5	13.0	5
ETPW - 4 H	6.0	10.0	2.5	0.5	13.0	5	13.0	5
ETPW - 5 J, K ⁽¹⁾	8.6	12.5	2.5	0.5	15.5	5	15.5	5
ETPW - 5 J, K, L	8.6	12.5	5.0	0.5	15.5	5	-	-
ETPW - 6 M, N	9.5	15.0	5.0	0.5	18.0	5	-	-
ETPW - 6 P, R	9.5	16.0	5.0	0.5	19.0	5	-	-

Note: ⁽¹⁾ J,K with RM 2.5 mm : 100 µF - 6.3 V, 68 µF - 10 V, 47 µF - 16 V, 22 µF - 25 V

* Pb containing terminations are not RoHS compliant, exemptions may apply



STANDARD RATINGS AND CASE CODES							
C _R μF	RATED VOLTAGE U _R at + 85 °C						
	3.0 V	6.3 V	10 V	16 V	25 V	35 V	50 V
0.10						1A	1A
0.15						1A	1A
0.22						1A	1A
0.33						1A	1B
0.47						1A	1B
0.68						1A	2C
1.0					1A	1A	2D
1.5					1A	1B	2E
2.2				1A	1B	2C	3F
3.3			1A	1B	2C	2D	3G
4.7		1A	1B	2C	2D	2E	4H
6.8	1A	1B	2C	2D	2E	3F	5J
10	1A	2C	2D	2E	3F	3G	5L
15	1B	2D	2E	3F	4H	5J	6M
22	2C	2E	3F	3G	5J	5L	6P
33	2D	3F	3G	4H	5K	6M	
47	2E	3G	4H	5K	6M	6P	
68	3F	4H	5J	5L	6N		
100	3G	5J	5L	6N			
150	4H	5L	6N	6R			
220	5J	6M	6P				
330	5L	6P					
470							

STANDARD RATINGS										
C _R (μF)	CASE CODE	PART NUMBER	DIMENSIONS					MAX. DCL AT + 20 °C, (μA)	MAX. Z AT 100 kHz (Ω)	MAX. DF AT 120 Hz + 20 °C
			D MAX. (mm)	H MAX. (mm)	H ₂ MAX. (mm)	RM ± 0.05	d ± 0.05			
U _R = 3 V AT + 85 °C, Surge = 3.9 V . . . U _C = 2 V AT + 125 °C										
6.8	1A	P1A685003(*)__D	4.0	7.1	10.5	2.5	0.5	0.5	6.0	0.06
10	1A	P1A106003(*)__D	4.0	7.1	10.5	2.5	0.5	0.5	5.0	0.08
15	1B	P1B156003(*)__D	4.0	7.1	10.5	2.5	0.5	0.5	4.0	0.08
22	2C	P2C226003(*)__D	4.5	8.0	11.0	2.5	0.5	0.7	3.2	0.08
33	2D	P2D336003(*)__D	4.5	8.0	11.0	2.5	0.5	1.0	2.5	0.08
47	2E	P2E476003(*)__D	5.0	9.5	12.5	2.5	0.5	1.4	2.0	0.08
68	3F	P3F686003(*)__D	5.0	9.5	12.5	2.5	0.5	2.0	1.6	0.08
100	3G	P3G107003(*)__D	5.5	10.0	13.0	2.5	0.5	3.0	1.2	0.10
150	4H	P4H157003(*)__D	6.0	10.0	13.0	2.5	0.5	4.5	1.0	0.10
220	5J	P5J227003(*)__D	8.6	12.5	15.5	5.0	0.5	6.6	0.8	0.10
330	5L	P5L337003(*)__D	8.6	12.5	15.5	5.0	0.5	9.9	0.6	0.10

Note: (*) Insert M for ± 20 % tolerance or K for ± 10 %
 __ Lead style and packaging code, see lead style and packaging

STANDARD RATINGS										
C _R (μF)	CASE CODE	PART NUMBER	DIMENSIONS					MAX. DCL AT + 20 °C, (μA)	MAX. Z AT 100 kHz (Ω)	MAX. DF AT 120 Hz + 20 °C
			D MAX. (mm)	H MAX. (mm)	H ₂ MAX. (mm)	RM ± 0.05	d ± 0.05			
U_R = 6.3 V AT + 85 °C, Surge = 7.8 V . . . U_C = 4 V AT + 125 °C										
4.7	1A	P1A475603(*)_D	4.0	7.1	10.5	2.5	0.5	0.5	6.0	0.06
6.8	1B	P1B685603(*)_D	4.0	7.1	10.5	2.5	0.5	0.5	5.0	0.06
10	2C	P2C106603(*)_D	4.5	8.0	11.0	2.5	0.5	0.6	4.0	0.08
15	2D	P2D156603(*)_D	4.5	8.0	11.0	2.5	0.5	0.9	3.2	0.08
22	2E	P2E226603(*)_D	5.0	9.5	12.5	2.5	0.5	1.4	2.5	0.08
33	3F	P3F336603(*)_D	5.0	9.5	12.5	2.5	0.5	2.1	2.0	0.08
47	3G	P3G476603(*)_D	5.5	10.0	13.0	2.5	0.5	3.0	1.6	0.08
68	4H	P4H686603(*)_D	6.0	10.0	13.0	2.5	0.5	4.3	1.2	0.08
100	5J	P5J107603(*)_D	8.6	12.5	15.5	2.5	0.5	6.3	1.0	0.10
150	5L	P5L157603(*)_D	8.6	12.5	15.5	5.0	0.5	9.5	0.8	0.10
220	6M	P6M227603(*)_D	9.5	15.0	18.0	5.0	0.5	13.9	0.6	0.10
330	6P	P6P337603(*)_D	9.5	16.0	19.0	5.0	0.5	20.8	0.5	0.10
U_R = 10 V AT + 85 °C, Surge = 13 V . . . U_C = 6.3 V AT + 125 °C										
3.3	1A	P1A335010(*)_D	4.0	7.1	10.5	2.5	0.5	0.5	6.5	0.06
4.7	1B	P1B475010(*)_D	4.0	7.1	10.5	2.5	0.5	0.5	5.0	0.06
6.8	2C	P2C685010(*)_D	4.5	8.0	11.0	2.5	0.5	0.7	4.0	0.06
10	2D	P2D106010(*)_D	4.5	8.0	11.0	2.5	0.5	1.0	3.2	0.08
15	2E	P2E156010(*)_D	5.0	9.5	12.5	2.5	0.5	1.5	2.5	0.08
22	3F	P3F226010(*)_D	5.0	9.5	12.5	2.5	0.5	2.2	2.0	0.08
33	3G	P3G336010(*)_D	5.5	10.0	13.0	2.5	0.5	3.3	1.6	0.08
47	4H	P4H476010(*)_D	6.0	10.0	13.0	2.5	0.5	4.7	1.2	0.08
68	5J	P5J686010(*)_D	8.6	12.5	15.5	2.5	0.5	6.8	1.0	0.08
100	5L	P5L107010(*)_D	8.6	12.5	15.5	5.0	0.5	10.0	0.8	0.10
150	6N	P6N157010(*)_D	9.5	15.0	18.0	5.0	0.5	15.0	0.6	0.10
220	6P	P6P227010(*)_D	9.5	16.0	19.0	5.0	0.5	22.0	0.5	0.10
U_R = 16 V AT + 85 °C, Surge = 20.8 V . . . U_C = 10 V AT + 125 °C										
2.2	1A	P1A225016(*)_D	4.0	7.1	10.5	2.5	0.5	0.5	7.0	0.06
3.3	1B	P1B335016(*)_D	4.0	7.1	10.5	2.5	0.5	0.5	6.0	0.06
4.7	2C	P2C475016(*)_D	4.5	8.0	11.0	2.5	0.5	0.8	4.5	0.06
6.8	2D	P2D685016(*)_D	4.5	8.0	11.0	2.5	0.5	1.1	3.2	0.06
10	2E	P2E106016(*)_D	5.0	9.5	12.5	2.5	0.5	1.6	2.5	0.08
15	3F	P3F156016(*)_D	5.0	9.5	12.5	2.5	0.5	2.4	2.0	0.08
22	3G	P3G226016(*)_D	5.5	10.0	13.0	2.5	0.5	3.5	1.6	0.08
33	4H	P4H336016(*)_D	6.0	10.0	13.0	2.5	0.5	5.3	1.2	0.08
47	5K	P5K476016(*)_D	8.6	12.5	15.5	2.5	0.5	7.5	1.0	0.08
68	5L	P5L686016(*)_D	8.6	12.5	15.5	5.0	0.5	10.9	0.8	0.08
100	6N	P6N107016(*)_D	9.5	15.0	18.0	5.0	0.5	16.0	0.6	0.10
150	6R	P6R157016(*)_D	9.5	16.0	19.0	5.0	0.5	24.0	0.5	0.10
U_R = 25 V AT + 85 °C, Surge = 32.5 V . . . U_C = 16 V AT + 125 °C										
1	1A	P1A105025(*)_D	4.0	7.1	10.5	2.5	0.5	0.5	8.5	0.04
1.5	1A	P1A155025(*)_D	4.0	7.1	10.5	2.5	0.5	0.5	7.5	0.04
2.2	1B	P1B225025(*)_D	4.0	7.1	10.5	2.5	0.5	0.6	6.0	0.06
3.3	2C	P2C335025(*)_D	4.5	8.0	11.0	2.5	0.5	0.8	4.5	0.06
4.7	2D	P2D475025(*)_D	4.5	8.0	11.0	2.5	0.5	1.2	3.2	0.06
6.8	2E	P2E685025(*)_D	5.0	9.5	12.5	2.5	0.5	1.7	2.5	0.06
10	3F	P3F106025(*)_D	5.0	9.5	12.5	2.5	0.5	2.5	2.0	0.08
15	4H	P4H156025(*)_D	6.0	10.0	13.0	2.5	0.5	3.8	1.6	0.08
22	5J	P5J226025(*)_D	8.6	12.5	15.5	2.5	0.5	5.5	1.2	0.08
33	5K	P5K336025(*)_D	8.6	12.5	15.5	5.0	0.5	8.3	1.0	0.08
47	6M	P6M476025(*)_D	9.5	15.0	18.0	5.0	0.5	11.8	0.8	0.08
68	6N	P6N686025(*)_D	9.5	15.0	18.0	5.0	0.5	17.0	0.6	0.08

Note:

(*) Insert M for ± 20 % tolerance or K for ± 10 %

_ _ Lead style and packaging code, see lead style and packaging



Resin-Coated, Radial-Leaded
Solid Tantalum Capacitors

Vishay Sprague

STANDARD RATINGS										
C _R (μF)	CASE CODE	PART NUMBER	DIMENSIONS					MAX. DCL AT + 20 °C, (μA)	MAX. Z AT 100 kHz (OHMS)	MAX. DF AT 120 Hz + 20 °C
			D MAX. (mm)	H MAX. (mm)	H ₂ MAX. (mm)	RM ± 0.05	d ± 0.05			
U_R = 35 V AT + 85 °C, Surge = 45.5 V . . . U_C = 23 V AT + 125 °C										
0.1	1A	P1A104035(*)__D	4.0	7.1	10.5	2.5	0.5	0.5	38.0	0.04
0.15	1A	P1A154035(*)__D	4.0	7.1	10.5	2.5	0.5	0.5	30.0	0.04
0.22	1A	P1A224035(*)__D	4.0	7.1	10.5	2.5	0.5	0.5	23.0	0.04
0.33	1A	P1A334035(*)__D	4.0	7.1	10.5	2.5	0.5	0.5	18.0	0.04
0.47	1A	P1A474035(*)__D	4.0	7.1	10.5	2.5	0.5	0.5	14.0	0.04
0.68	1A	P1A684035(*)__D	4.0	7.1	10.5	2.5	0.5	0.5	10.0	0.04
1.0	1A	P1A105035(*)__D	4.0	7.1	10.5	2.5	0.5	0.5	8.0	0.04
1.5	1B	P1B155035(*)__D	4.0	7.1	10.5	2.5	0.5	0.5	6.5	0.04
2.2	2C	P2C225035(*)__D	4.5	8.0	11.0	2.5	0.5	0.8	5.0	0.06
3.3	2D	P2D335035(*)__D	4.5	8.0	11.0	2.5	0.5	1.2	3.5	0.06
4.7	2E	P2E475035(*)__D	5.0	9.5	12.5	2.5	0.5	1.6	2.5	0.06
6.8	3F	P3F685035(*)__D	5.0	9.5	12.5	2.5	0.5	2.4	2.0	0.06
10	3G	P3G106035(*)__D	5.5	10.0	13.0	2.5	0.5	3.5	1.6	0.08
15	5J	P5J156035(*)__D	8.6	12.5	15.5	5.0	0.5	5.3	1.2	0.08
22	5L	P5L226035(*)__D	8.6	12.5	15.5	5.0	0.5	7.7	1.0	0.08
33	6M	P6M336035(*)__D	9.5	15.0	18.0	5.0	0.5	11.6	0.8	0.08
47	6P	P6P476035(*)__D	9.5	16.0	19.0	5.0	0.5	16.5	0.8	0.08
U_R = 50 V AT + 85 °C, Surge = 65 V . . . U_C = 33 V AT + 125 °C										
0.1	1A	P1A104050(*)__D	4.0	7.1	10.5	2.5	0.5	0.5	38.0	0.04
0.15	1A	P1A154050(*)__D	4.0	7.1	10.5	2.5	0.5	0.5	30.0	0.04
0.22	1A	P1A224050(*)__D	4.0	7.1	10.5	2.5	0.5	0.5	23.0	0.04
0.33	1B	P1B334050(*)__D	4.0	7.1	10.5	2.5	0.5	0.5	18.0	0.04
0.47	1B	P1B474050(*)__D	4.0	7.1	10.5	2.5	0.5	0.5	14.0	0.04
0.68	2C	P2C684050(*)__D	4.5	8.0	11.0	2.5	0.5	0.5	10.0	0.04
1.0	2D	P2D105050(*)__D	4.5	8.0	11.0	2.5	0.5	0.5	8.0	0.04
1.5	2E	P2E155050(*)__D	5.0	9.5	12.5	2.5	0.5	0.8	6.5	0.04
2.2	3F	P3F225050(*)__D	5.0	9.5	12.5	2.5	0.5	1.1	5.0	0.06
3.3	3G	P3G335050(*)__D	5.5	10.0	13.0	2.5	0.5	1.7	3.5	0.06
4.7	4H	P4H475050(*)__D	6.0	10.0	13.0	2.5	0.5	2.4	2.5	0.06
6.8	5J	P5J685050(*)__D	8.6	12.5	15.5	5.0	0.5	3.4	2.0	0.06
10	5L	P5L106050(*)__D	8.6	12.5	15.5	5.0	0.5	5.0	1.6	0.08
15	6M	P6M156050(*)__D	9.5	15.0	18.0	5.0	0.5	7.5	1.2	0.08
22	6P	P6P226050(*)__D	9.5	16.0	19.0	5.0	0.5	11.0	1.0	0.08

Note:

(*) Insert M for ± 20 % tolerance or K for ± 10 %
 __ Lead style and packaging code, see lead style and packaging

PERFORMANCE CHARACTERISTICS

- Climatic Category:** 55/125/56 acc. to IEC
- Temperature Range:** - 55 °C up to + 125 °C with linear voltage derating to category voltage UC
- Rated Voltage, Category Voltage:** 3 V to 50 V;
2 V to 33 V
- Surge Voltage:** 1.3 times of rated voltage at + 85 °C
- Reverse Voltage (Temporary):**
15 % of the rated DC voltage at + 20 °C
10 % of the rated DC voltage at + 55 °C
5 % of the rated DC voltage at + 85 °C
- Rated Capacitance:** 0.1 μF to 330 μF
- Capacitance Tolerance:** ± 20 %, ± 10 %,
- Leakage Current in μA:** Measured at + 20 °C after 5 minutes: ≤ 0.01 x CR x UR or 0.5 μA, whichever is greater
- Dissipation Factor:** at 120 Hz and + 20 °C
See table
- Impedance:** Measured at 100 kHz and + 20 °C
See table
- Permissible AC Voltage Stress:** The highest permissible AC voltage for the respective frequency may be taken from the brochure "General information".

The values apply for + 20 °C For higher temperatures, the values have to be multiplied with the following factors:

TEMPERATURE	FACTOR
+ 50 °C	0.7
+ 85 °C	0.5
+ 125 °C	0.3

Intermediate values can be obtained by linear interpolation.

For further notes on AC voltage stress: See general information

- Characteristics at high and low temperatures** (the values shall not exceed the following limits)

TEST TEMPERATURE	- 55 °C	+ 20 °C	+ 85 °C	+ 125 °C
$\Delta C/C < \tan\delta$	- 10 %	-	+ 12 %	+ 15 %
≤ 1.5 μF	0.04	0.04	0.04	0.06
< 10 μF	0.06	0.06	0.06	0.08
< 100 μF	0.08	0.08	0.08	0.08
≥ 100 μF	0.10	0.10	0.10	0.10
Leakage current IR	-	≤ 0.01 x CR x UR or 0.5 μA whichever is greater	≤ 0.1 x CR x UR or 10 μA whichever is greater	≤ 0.125 x CR x UR or 12.5 μA whichever is greater ⁽¹⁾

Note:

⁽¹⁾ Measured at category voltage

- Service life:** > 300 000 h ⁽²⁾
- Failure percentage:** ≤ 0.6 % within 100 000 h ⁽²⁾
- Failure rate (λ):** ≤ 0.6 10⁻⁷/h = ≤ 60 fit ⁽²⁾
- Failure criteria:** Catastrophic failure: Short circuit or interruption
Drift failure: DC/C > + 5 - 15 %
Z > 3 times initial limit value
IR > 5 times initial value + 5 μA

Note: ⁽²⁾ related to UR, + 40 °C and a circuit resistance of ≥ 3 W/V


LEAD STYLES AND PACKAGING				
CASE SIZE	CODE	RM in mm ± 0.5	SPECIFICATION	REMARKS
1 - 6	00	2.5 / 5	Bulk	Reel with positive pole in tape run direction in front is standard
1 - 4 ⁽¹⁾	C0	5	Form L, Bulk	
1 - 6	V0	5	Form DS, Bulk	
1 - 4 ⁽¹⁾	W0	2.5	Reel, positive pole in front of unreeling direction	
1 - 4 ⁽¹⁾	T0	2.5	Reel, negative pole in front of unreeling direction	
1 - 4 ⁽¹⁾	H0	2.5	Ammo	
1 - 5	V2	5	Reel, positive pole in front of unreeling direction	
1 - 5	R0	5	Reel, negative pole in front of unreeling direction	
1 - 5	08	5	Ammo	

Note:
⁽¹⁾ 100 µF - 6.3 V, 68 µF - 10 V, 47 µF - 16 V, 22 µF - 25 V

CASE SIZE	BULK 00, V0, C0	REEL W0, T0, V2, R0	AMMO H0, O8
ETPW 1 A,B	500	2500	2500
ETPW 2 C,D,E	500	2000	2000
ETPW 3 F,G	500	1500	1500
ETPW 4 H	500	1500	1500
ETPW 5 J,K,L	100	500	500
ETPW 6 M,N,P, R	100	-	-

TAPING ACCORDING TO IEC 286-2

(meets IEC 286-2)



Dimensions for components on tape and tolerances:

DESIGNATION	SYMBOL	DIMENSIONS (mm)
Holding tape width	W	18.0 (+ 1/- 0.5)
Adhesive tape width	W ₀	Min. 5.0
Distance of components	P	12.7 ± 1
Hole center to component center	P ₂	6.35 ± 1.3
Hole center to lead	P ₁	5.1/3.8 ± 0.7
Distance of body to hole center	H ⁽¹⁾	18.0 (+ 2/- 0)
Distance of lead to hole center	H ₀	16.0 ± 0.5
Component upper edge to hole center	H ₁	Max. 32.0
Adhesive tape location	W ₂	Max. 3.0
Hole location	W ₁	9.0 (+ 0.75/- 0.5)
Distance of holes	P ₀	12.7 ± 0.3
Hole diameter	D ₀	4.0 ± 0.3
Lead diameter	d	0.5 ± 0.05
Component alignment	Δh	Max. ± 2.0
Pitch	F	2.5/5.0 (+ 0.6/- 0.1)
Holding tape thickness	t	0.5 ± 0.2
Component alignment	ΔP	Max. ± 1.3
Length of snapped leads	L	Max. 11.0

Note:⁽¹⁾ also available: 16 mm and 20 mm taping according to DIN-IEC 286 part 2



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.