




# THIN/THICK FILM CHIP RESISTORS

Vishay Dale



## Solutions for a Wide Range of Industries



### INTRODUCTION

Vishay Dale Thin Film's chip resistors are manufactured in an ISO 9001 registered facility to ensure the highest quality products. In addition to state of the art manufacturing methods, Vishay employs additional processes to ensure the highest quality and reliability over competitive product offerings. Key features of our resistors include:

- Special Passivation Method (SPM) – The majority of our chip resistor series undergo an SPM coating process. SPM is Vishay's proprietary coating blend to add an additional protective layer over the resistive film to prevent corrosion.
- Moisture Resistant Tantalum Nitride Film - Our versatile line of chip resistors are also available with tantalum nitride resistive film. Tantalum nitride is a self passivating film with superior moisture resistance characteristics under extremely humid operating conditions.
- Stable Thin Film Performance – Our chip resistors typically show established stable thin film performance over an extended period of time and generally outperform competitive products in reliability characteristics.
- Custom Orders - In addition to the standard values, custom values are also available.
- Quick Chip – Our Quick Chip program is another resource that can be utilized to expedite standard chip orders.

### RESOURCES

- For technical questions contact [thinfilm@vishay.com](mailto:thinfilm@vishay.com)

One of the World's Largest Manufacturers of  
Discrete Semiconductors and Passive Components





# THIN/THICK FILM CHIP RESISTORS

Vishay Dale



## Performance Specifications

Resistors - Vishay Dale Thin Film Chip Overview

	<b>L-NS</b>	<b>FC</b>	<b>PHP</b>	<b>PLT</b>	<b>PLTT</b>	<b>PTN</b>	<b>PNM</b>	<b>PAT</b>	<b>E/H</b>	<b>P-NS</b>	<b>M-</b>
<b>Description</b>	Industrial Low-Value	Precision High-Frequency	Precision High-Power	Precision Low-TCR	Precision High-Temperature, Low-TCR	Precision Moisture-Resistant	Precision Non-Magnetic	Precision Automotive AEC-Q200 Qualified	Precision QPL MIL-PRF-55342 Qualified	Precision Industrial	Industrial Thick Film Chip Resistor
<b>Resistor Material</b>	Nickel Alloy	Passivated Nichrome	Passivated Nichrome	Passivated Nichrome	Passivated Nichrome	Tantalum Nitride	Tantalum Nitride	Tantalum Nitride	Passivated Nichrome	Passivated Nichrome	Ruthenium
<b>Resistance Range</b>	0.03 Ω to 10 Ω	10 Ω to 1 kΩ	10 Ω to 30 kΩ	100 Ω to 775 kΩ	250 Ω to 3 MΩ	10 Ω to 3 MΩ	10 Ω to 3 MΩ	10 Ω to 3 MΩ	10 Ω to 6.19 MΩ	10 Ω to 6.19 MΩ	10 Ω to 25 MΩ
<b>TCR: Absolute (±ppm/°C)</b>	300 to 500	25 to 100	25 to 100	5	5	25 to 100	25 to 100	25 to 100	25 to 300	10 to 100	100 to 300
<b>Tolerance: Absolute (±%)</b>	1 to 20	0.1 to 5	0.1 to 5	0.01 to 0.1	0.02 to 0.1	0.1 to 5	0.1 to 5	0.1 to 5	0.1 to 10	0.02 to 5	1 to 10
<b>Power Rating (W)</b>	0.125 to 2	0.05 to 0.33	1 to 2.5	0.15 to 0.4	0.25 to 0.40	0.05 to 1	0.05 to 1	0.05 to 1	0.05 to 0.1	0.05 to 1	0.1 to 2
<b>Working Voltage Range (V)</b>	$\sqrt{P \times R}$	30 to 75	100 to 200	75 to 200	75 to 200	75 to 200	75 to 200	75 to 200	40 to 200	75 to 200	25 to 200
<b>Noise (dB)</b>	< - 35	< - 35	< - 30	< - 35	< - 35	< - 30	< - 30	< - 30	< - 25	< - 35	< - 35
<b>Case Size</b>	0505 0603 0705 0805 1005 1010 1206 1505 2208 2010 2512	0402 0603 0805 1005 1206	1206 2512	0603 0705 0805 1206	0805 1206	0402 0502 0505 0603 0705 0805 1005 1010 1206 1505 2208 2010 2512	0402 0502 0505 0603 0705 0805 1005 1010 1206 1505 2208 2010 2512	0402 0603 0805 1206 1505 2208 2010 2512	M55342/ 01 -12 D55342/07 (07 size only)	0402 0502 0505 0603 0705 0805 1005 1010 1206 1505 2208 2010 2512	0402 0502 0504 0505 0603 0705 0805 1005 1010 1206 1505 2208 2010 2512
<b>Operating Temperature (°C)</b>	- 55 to + 125	- 55 to + 125	- 55 to + 125	- 55 to + 125	- 55 to + 215	- 55 to + 125	- 55 to + 125	- 55 to + 125	- 55 to + 125	- 55 to + 125	- 55 to + 125
<b>Storage Temperature (°C)</b>	- 55 to + 150	- 55 to + 150	- 55 to + 150	- 55 to + 150	- 55 to + 230	- 55 to + 150	- 55 to + 150	- 55 to + 150	- 55 to + 150	- 55 to + 150	- 55 to + 150
<b>Lead Term</b>	X	X	X	X		X	X		X	X	X
<b>Lead-Free Term</b>	X	X	X	X		X	X	X		X	X
<b>Gold Term</b>	X	X			X	X				X	



# THIN/THICK FILM CHIP RESISTORS

Vishay Dale



## Product Highlights

Resistors - Vishay Dale Thin Film Chip Overview

Series Type	Key Features	Applications
<a href="#">L-NS</a>	Moisture resistant nickel alloy film	Current sense circuits
	Small case size	Current limit circuits
	Stable film performance of 0.4 % $\Delta R$ at 2000 h at 70 °C	Measurement systems
<a href="#">FC</a>	Small size (20 mm x 40 mm min)	Low-noise amplifiers
	Frequency response up to 20 GHz	High-speed routers
	Tolerances down to 0.1 %	Attenuation circuitry
<a href="#">PHP</a>	Termination solder (lead or lead (Pb)-free), ribbon- or wire bondable	High-frequency line termination
	High power ratings from 1.0 W to 2.5 W	High-precision medical imaging
	Stable film and performance characteristics of 0.1 % $\Delta R$ at + 70 °C for 2000 h	Power supply
	Available in the 1206 and 2512 case sizes	Power measurement
<a href="#">PLT</a>	Wide wraparound terminations to enhance heat dissipation	Test and measurement equipment
	Extremely tight tolerance to 0.01 %	Medical
	Low TCR of 5 ppm/°C	Military
<a href="#">PLTT</a>	Stable film: 0.02 % $\Delta R$ at 2000 h at 70 °C	Industrial
	Stable film and performance characteristics: < 0.05 % at 2000 h at 215 °C at 25 % rated power	Oil/Gas precision applications
	Extremely low TCR of $\pm 5$ ppm/°C over wide temperature range	Down hole exploration
	Highly suitable for high temperature industrial applications	Automotive under the hood applications
<a href="#">PTN</a>	Tight tolerance to 0.02 %	Aircraft controls
	Moisture resistant tantalum nitride film	Military and aerospace
	High power rating per case size over traditional chip resistors	Industrial/Test and measurement equipment
<a href="#">PNM</a>	Wide resistance range available: 10 $\Omega$ to 3 M $\Omega$	Telecommunications
	All non magnetic materials	Medical imaging
	Stable film and performance characteristics: 0.03 % $\Delta R$ at 70 °C, 10 000 h	High-end audio equipment
<a href="#">PAT</a>	Tolerances down to 0.1 %	Measurement sensing
	AEC-Q200-compliant	Automotive equipment
	AEC-Q200 ESD-rated Class 1C (2 kV), power rating up to 1 W	Telecommunications
	Moisture-resistant tantalum nitride resistor film on high-purity alumina substrate	Industrial equipment
<a href="#">E/H MIL-PRF-55342</a>	Stable film and performance characteristics: < 0.05 % at 2000 h at 70 °C	Test and measurement equipment
	Established reliability "R" and "T" failure rate level	Military
	Military QPL listed	Aerospace
<a href="#">P-NS</a>	Wide resistance range available: 10 $\Omega$ to 6.19 M $\Omega$	Radar and satellite systems
	Wide selection of case sizes	Precision reference
	Wide resistance range available : 10 $\Omega$ to 6.19 M $\Omega$	Low-noise instrumentation
<a href="#">M-</a>	Stable film performance characteristics: 0.05 % $\Delta R$ at 10 000 h, + 70 °C	Automated test equipment
	High power rating per case size	Military
	Wide resistance range available: 10 $\Omega$ to 25 M $\Omega$	Aerospace
	Stable film performance characteristics: 0.15 % $\Delta R$ at 2000 h, 70 °C	Industrials



# THIN/THICK FILM CHIP RESISTORS


Vishay Dale



Resistors - Vishay Dale Thin Film Chip Overview

## Mechanical Specifications

Layers	L-NS	FC	PLT	PTN	PNM	PAT	P-NS	E/H	M-	PHP
Substrate	High Purity Alumina									
Resistive Film	Nickel Alloy	Passivated Nichrome	Nichrome	Tantalum Nitride	Tantalum Nitride	Tantalum Nitride	Passivated Nichrome	Passivated Nichrome	Ruthenium	Nichrome
Passivation	Epoxy	SPM	Silicon Nitride and SPM	Epoxy	Epoxy	Silicon Nitride and Epoxy	SPM	SPM	Glass	SPM
Barrier	Nickel	Nickel	Nickel	Nickel	Electroless Nickel	Nickel	Nickel	Nickel	Nickel	Nickel
Adhesion Layer	x	Nichrome	Titanium Tungsten	Titanium Tungsten	Titanium Tungsten	Titanium Tungsten	Nichrome	Nichrome	x	Titanium Tungsten
PAD Layer	x	Gold	Gold	Gold	Gold	Gold	Gold	Gold	Ag Pd	Gold






# THIN/THICK FILM CHIP RESISTORS

Vishay Dale



Resistors - Vishay Dale Thin Film Chip Overview




## Target Applications

Vishay Dale Thin Film's chip resistors have a track record of providing solutions to a wide range of industries, including military, aerospace, medical, automotive, industrial, and telecommunications. Our broad chip resistor portfolio covers a wide resistance range from 0.03 Ω to 25 MΩ, with exceptionally low TCR and tolerance offerings down to ± 5 ppm/°C and ± 0.01 % respectively.

Vishay's line of chip resistors are manufactured in an ISO 9001 registered facility to ensure the highest quality products. In addition to state of the art manufacturing methods, Vishay employs additional processes to ensure the highest quality and reliability over competitive product offerings. Key features of our resistors include:

- Special Passivation Method (SPM) – The majority of our chip resistor series undergo an SPM coating process. SPM is Vishay's proprietary coating blend to add an additional protective layer over the resistive film to prevent corrosion.
- Moisture Resistant Tantalum Nitride Film - Our versatile line of chip resistors are also available with tantalum nitride resistive film. Tantalum nitride is a self passivating film with superior moisture resistance characteristics under extremely humid operating conditions.
- Stable Thin Film Performance – Our chip resistors typically show established stable thin film performance over an extended period of time and generally outperform competitive products in reliability characteristics.
- Custom Orders - In addition to the standard values, custom values are also available.
- Quick Chip – Our Quick Chip program is another resource that can be utilized to expedite standard chip orders.





# THIN/THICK FILM CHIP RESISTORS

Vishay Dale



## WORLDWIDE SALES CONTACTS

### THE AMERICAS

#### UNITED STATES

VISHAY AMERICAS  
ONE GREENWICH PLACE  
SHELTON, CT 06484  
UNITED STATES  
PH: +1-402-563-6866  
FAX: +1-402-563-6296

### ASIA

#### SINGAPORE

VISHAY INTERTECHNOLOGY ASIA PTE LTD.  
37A TAMPINES STREET 92 #07-00  
SINGAPORE 528886  
PH: +65-6788-6668  
FAX: +65-6788-0988

#### P.R. CHINA

VISHAY CHINA CO., LTD.  
15D, SUN TONG INFOPORT PLAZA  
55 HUAI HAI WEST ROAD  
SHANGHAI 200030  
P.R. CHINA  
PH: +86-21-5258 5000  
FAX: +86-21-5258 7979

#### JAPAN

VISHAY JAPAN CO., LTD.  
SHIBUYA PRESTIGE BLDG. 4F  
3-12-22, SHIBUYA  
SHIBUYA-KU  
TOKYO 150-0002  
JAPAN  
PH: +81-3-5466-7150  
FAX: +81-3-5466-7160

### EUROPE

#### GERMANY

VISHAY ELECTRONIC GMBH  
GEHEIMRAT-ROSENTHAL-STR. 100  
95100 SELB  
GERMANY  
PH: +49-9287-71-0  
FAX: +49-9287-70435

#### FRANCE

VISHAY S.A.  
199, BD DE LA MADELEINE  
06003 NICE, CEDEX 1  
FRANCE  
PH: +33-4-9337-2727  
FAX: +33-4-9337-2726

#### UNITED KINGDOM

VISHAY LTD.  
SUITE 6C, TOWER HOUSE  
ST. CATHERINE'S COURT  
SUNDERLAND ENTERPRISE PARK  
SUNDERLAND SR5 3XJ  
UNITED KINGDOM  
PH: +44-191-516-8584  
FAX: +44-191-549-9556