

Surface Mount Multilayer Ceramic Chip Capacitors for Telecom Applications



FEATURES

- Replaces high voltage, leaded, film capacitors
- Rated for telecommunications voltages
- Saves board space and weight
- Surface mountable, precious metal technology, wet build process
- Wide band operation, excellent high frequency filtering



RoHS
COMPLIANT

APPLICATIONS

- Ideal for telephone line (Tip 'N Ring®) filtering
- Voice over Internet (VOI) cards

ELECTRICAL SPECIFICATIONS

Note: Electrical characteristics at + 25 °C unless otherwise specified

Operating Temperature: - 55 °C to + 125 °C

Capacitance Range: 0.033 µF to 1.0 µF

Voltage Rating: 250 Vdc

Temperature Coefficient of Capacitance (TCC):
± 15 % from - 55 °C to + 125 °C

Dissipation Factor (DF):
2.5 % maximum at 1.0 V_{rms} and 1 kHz

Aging Rate: 1 % maximum per decade

Insulation Resistance (IR):

At + 25 °C and rated voltage 100 000 MΩ minimum or 1000 ΩF, whichever is less.


At + 125 °C and rated voltage 10 000 MΩ minimum or 100 ΩF, whichever is less.

Dielectric Withstanding Voltage (DWV):

This is the maximum voltage the capacitors are tested for a 1 to 5 second period and the charge/discharge current does not exceed 50 mA

250 Vdc: DWV at 250 % of rated voltage

DIMENSIONS in inches [millimeters]



PART ORDERING NUMBER	LENGTH (L)	WIDTH (W)	MAXIMUM THICKNESS (T)	TERMINATION PAD (P)	
				MINIMUM	MAXIMUM
VJ1812 (9427, 7427)	0.177 ± 0.010 [4.50 ± 0.25]	0.126 ± 0.010 [3.20 ± 0.25]	0.086 [2.18]	0.010 [0.25]	0.030 [0.76]
VJ1825 (9174, 7174)	0.177 ± 0.010 [4.50 ± 0.25]	0.252 ± 0.010 [6.40 ± 0.25]	0.086 [2.18]	0.010 [0.25]	0.030 [0.76]
VJ2225 (9253)	0.220 ± 0.010 [5.59 ± 0.25]	0.250 ± 0.010 [6.35 ± 0.25]	0.086 [2.18]	0.010 [0.25]	0.030 [0.76]

ORDERING INFORMATION

VJ1812	Y	334	J	X	P	A	T	3T
CASE CODE	DIELECTRIC	CAPACITANCE NOMINAL CODE	CAPACITANCE TOLERANCE	TERMINATION	DC VOLTAGE RATING ⁽¹⁾	MARKING	PACKAGING	PROCESS CODE
1812 (9427, 7427)	Y = X7R	Expressed in picofarads (pF). The first two digits are significant, the third is a multiplier. Example: 334 = 330 000 pF	J = ± 5 % K = ± 10 % M = ± 20 %	X = Ni barrier with 100 % tin plated finish. F = AgPd	P = 250 V	A = Unmarked	T = 7" reel/ plastic tape R = 11 1/4" reel/ plastic tape	3T = Tip'N Ring
1825 (9174, 7174)								
2225 (9253)								

Note:

⁽¹⁾ DC voltage rating should not be exceeded in application



Surface Mount Multilayer Ceramic Chip Capacitors
for Telecom Applications

Vishay Vitramon


SELECTION CHART				
EIA TYPE		1812 ⁽¹⁾	1825 ⁽¹⁾	2225 ⁽¹⁾
PRODUCT DRAWING INFORMATION (PDI)		9427, 7427	9174, 7174	9253
VOLTAGE (Vdc)		250	250	250
CAP. CODE	CAP.			
333	0.033 μ F			•
393	0.039 μ F			•
473	0.047 μ F			•
563	0.056 μ F			•
683	0.068 μ F			•
823	0.082 μ F			•
104	0.10 μ F	•		•
124	0.12 μ F	•		•
154	0.15 μ F	•	•	•
184	0.18 μ F	•	•	•
224	0.22 μ F	•	•	•
274	0.27 μ F	•	•	•
334	0.33 μ F	•	•	•
394	0.39 μ F	•	•	•
474	0.47 μ F	•	•	•
564	0.56 μ F		•	•
684	0.68 μ F		•	•
824	0.82 μ F		•	•
105	1.0 μ F		•	•

Note:


⁽¹⁾ See soldering recommendations within this data book, or visit www.vishay.com/doc?45034

TIP'N RING® - TYPICAL PARAMETERS


CAPACITANCE COMPARISONS FILM
VS. VISHAY VITRAMON VJ1825Y474KXP TIP'N RING
0.47 µF, 250 V




X7R - DISSIPATION FACTOR VS. TEMPERATURE



IMPEDANCE VS. FREQUENCY
VISHAY VITRAMON TIP 'N RING
VJ1825Y474KXP



VOLTAGE COEFFICIENT OF CAPACITANCE
X7R TIP 'N RING



STANDARD PACKAGING QUANTITIES (1) (2) (3)

BODY SIZE	TAPE SIZE	7" REEL QUANTITIES		11 1/4" AND 13" REEL QUANTITIES		BULK QUANTITIES	
		PAPER TAPE PACKAGING CODE "C"	PLASTIC TAPE PACKAGING CODE "T"	PAPER TAPE PACKAGING CODE "P"	PLASTIC TAPE PACKAGING CODE "R"	VIAL PACKAGING CODE "B"	WAFFLE PACKAGING CODE "W"
1812 (9427, 7427)	12 mm	N/a	1000	N/a	5000	N/a	N/a
1825 (9174, 7174)	12 mm	N/a	1000	N/a	4000	N/a	N/a
2225 (9253)	12 mm	N/a	1000	N/a	4000	N/a	N/a

Notes:

- (1) Vishay Vitramon uses embossed plastic carrier tape
- (2) REFERENCE: EIA Standard RS 481 - "Taping of Surface Mount Components for Automatic Placement"
- (3) N/a = Not available



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.