





Power MOSFETs | IN A NUTSHELL

TrenchFET® AND E SERIES

Broad range of power MOSFETs in a wide selection of advanced packages

- N- and p-channel families
- Breakdown voltages: -200 V to 800 V
- Wide range of gate drive voltages starting at 1.2 V
- Commercial, automotive, and medical product grades

Breakdown Voltage and Package Selection




Application-Specific Technology Platforms

- Optimized with lowest $R_{ds(on)}$ for load switch applications



- Optimized for lowest gate charge and capacitances for fast switching



MARKETS AND APPLICATIONS



Full Range Of Leaded and Surface-Mount Packages, Including:

TO-247	D2PAK / DPAK	PowerPAK® 8x8 / 8x8L	PowerPAK® S08 to 0806	SOT, TSOP, SC Families	MICRO FOOT®