


Surface Mount Multilayer Ceramic Chip Capacitor Solutions for Boardflex Sensitive Applications



FEATURES

- Surface mountable, precious metal technology, wet build process
- OMD-Cap (Open Mode Design) reduce the risk of short or low IR because of board flex cracks
- Efficient low-power consumption, ripple current capable to 1.2 A_{rms} at 100 kHz
- High Voltage breakdown compared to standard design
- Available with 100 % voltage condition, process code "5H" (Is available for 630 V and lower. Contact mlcc@vishay.com for higher voltages.)
- Excellent reliability and thermal shock performance
- Available with polymer termination for increase resistance to board flex cracking
- Halogen-free according to IEC 61249-2-21 definition



RoHS
COMPLIANT
HALOGEN
FREE

APPLICATIONS

- Ideal for Power Supplies
- Input filter capacitor

ELECTRICAL SPECIFICATIONS

Note

Electrical characteristics at + 25 °C unless otherwise stated
Protective surface coating of high voltage capacitors maybe required to prevent surface arcing. Input side filter.

Operating Temperature: - 55 °C to + 125 °C

Capacitance Range: 100 pF to 1.8 μF

Voltage Rating: 16 Vdc to 3000 Vdc

Temperature Coefficient of Capacitance (TCC):

X7R: ± 15 % from - 55 °C to + 125 °C, with 0 Vdc applied

Dissipation Factor:

16 V, 25 V ratings: 3.5 % max. at 1.0 V_{rms} and 1 kHz

≥ 50 V ratings: 2.5 % max. at 1.0 V_{rms} and 1 kHz

Aging Rate: 1 % maximum per decade

Insulation Resistance (IR):

At + 25 °C and rated voltage 100 000 MΩ minimum or 1000 ΩF, whichever is less

At + 125 °C and rated voltage 10 000 MΩ minimum or 100 ΩF, whichever is less

Dielectric Withstanding Voltage (DWV):

This is the maximum voltage the capacitors are tested for a 1 s to 5 s period and the charge/discharge current does not exceed 50 mA

≤ 250 Vdc: DWV at 250 % of rated voltage

500 Vdc: DWV at 200 % of rated voltage

630 Vdc: DWV at 150 % of rated voltage


1000 Vdc: DWV at 150 % of rated voltage

1500 Vdc: DWV at 120 % of rated voltage

2000 Vdc: DWV at 120 % of rated voltage

3000 Vdc: DWV at 120 % of rated voltage

DIMENSIONS in inches [millimeters]



PART ORDERING NUMBER	LENGTH (L)	WIDTH (W)	MAXIMUM THICKNESS (T)	TERMINATION PAD (P)	
				MINIMUM	MAXIMUM
VJ0805	0.126 ± 0.008 [2.00 ± 0.20]	0.049 ± 0.008 [1.25 ± 0.20]	0.057 [1.45]	0.010 [0.25]	0.028 [0.71]
VJ1206	0.126 ± 0.008 [3.20 ± 0.20]	0.063 ± 0.008 [1.60 ± 0.20]	0.067 [1.70]	0.010 [0.25]	0.028 [0.71]
VJ1210	0.126 ± 0.008 [3.20 ± 0.20]	0.098 ± 0.008 [2.50 ± 0.20]	0.067 [1.70]	0.010 [0.25]	0.028 [0.71]
VJ1808	0.180 ± 0.010 [4.57 ± 0.25]	0.080 ± 0.010 [2.03 ± 0.25]	0.086 [2.18]	0.010 [0.25]	0.030 [0.76]
VJ1812	0.177 ± 0.010 [4.50 ± 0.25]	0.126 ± 0.008 [3.20 ± 0.20]	0.086 [2.18]	0.010 [0.25]	0.030 [0.76]
VJ1825	0.177 ± 0.010 [4.50 ± 0.25]	0.252 ± 0.010 [6.40 ± 0.25]	0.086 [2.18]	0.010 [0.25]	0.030 [0.76]
VJ2220	0.220 ± 0.008 [5.59 ± 0.20]	0.200 ± 0.008 [5.08 ± 0.20]	0.086 [2.18]	0.010 [0.25]	0.030 [0.76]
VJ2225	0.220 ± 0.010 [5.59 ± 0.25]	0.250 ± 0.010 [6.35 ± 0.25]	0.086 [2.18]	0.010 [0.25]	0.030 [0.76]

ORDERING INFORMATION

VJ1210	Y	474	K	X	A	A	T	## (2)
CASE SIZE	DIELECTRIC	CAPACITANCE CODE	CAPACITANCE TOLERANCE	TERMINATION	DC VOLTAGE RATING (1)	MARKING	PACKAGING	PROCESS CODE
0805 1206 1210 1808 1812 1825 2220 2225	Y = X7R	Expressed in picofarads (pF). The first two digits are significant, the third is a multiplier. Example: 474 = 470 000 pF	J = ± 5 % K = ± 10 % M = ± 20 %	X = Ni barrier 100 % tin plate matte finish F = AgPd B = Polymer 100 % tin plate matte finish	J = 16 X = 25 A = 50 V B = 100 V C = 200 V P = 250 V E = 500 V L = 630 V G = 1000 V R = 1500 V F = 2000 V H = 3000 V	A = Unmarked	C = 7" reel/paper tape T = 7" reel/plastic tape P = 11 1/4"/13" reel/paper tape R = 11 1/4"/13" reel/plastic tape O = 7" reel/flamed paper tape I = 11 1/4"/13" reel/flamed paper tape Note: "I" and "O" is used for "F" termination paper taped size 0805	4X = OMD Cap 5H = OMD Cap 100 % voltage conditioning

Notes

(1) DC voltage rating should not be exceeded in application

(2) Process code with 2 digits has to be added

Polymer plus termination "B" termination part number code length dimensions positive tolerances (including bandwidth) above are allowed to increase by the following amounts.

1206 and smaller case sizes: Length 0.002" (0.05 mm)

1210 and larger case sizes: Length 0.004" (0.1 mm)



SELECTION CHART																		
DIELECTRIC		X7R																
STYLE		VJ0805						VJ1206										
EIA TYPE		0805						1206										
VOLTAGE (Vdc)		16	25	50	100	200	500	630	16	25	50	100	200	500	630	1000	1500	2000
CAP. CODE	CAP.																	
101	100 pF																	
121	120 pF																	
151	150 pF																	
181	180 pF																	
221	220 pF																	
271	270 pF								•	•	•	•	•	•	•	•	•	•
331	330 pF								•	•	•	•	•	•	•	•	•	•
391	390 pF								•	•	•	•	•	•	•	•	•	•
471	470 pF	••	••	••	••	••	•	•	•	•	•	•	•	•	•	•	•	•
561	560 pF	••	••	••	••	••	•	•	•	•	•	•	•	•	•	•	•	•
681	680 pF	••	••	••	••	••	•	•	•	•	•	•	•	•	•	•	•	•
821	820 pF	••	••	••	••	••	•	•	•	•	•	•	•	•	•	•	•	•
102	1000 pF	••	••	••	••	••	•	•	•	•	•	•	•	•	•	•	•	•
122	1200 pF	••	••	••	••	••	•	•	•	•	•	•	•	•	•	•	•	•
152	1500 pF	••	••	••	••	••	•	•	•	•	•	•	•	•	•	•	•	•
182	1800 pF	••	••	••	••	••	•	•	•	•	•	•	•	•	•	•	•	•
222	2200 pF	••	••	••	••	••	•	•	•	•	•	•	•	•	•	•	•	•
272	2700 pF	••	••	••	••	••	•	•	•	•	•	•	•	•	•	•	•	•
332	3300 pF	••	••	••	••	••	•	•	•	•	•	•	•	•	•	•	•	•
392	3900 pF	••	••	••	••	••	•	•	•	•	•	•	•	•	•	•	•	•
472	4700 pF	••	••	••	••	••	•	•	•	•	•	•	•	•	•	•	•	•
562	5600 pF	••	••	••	••	•			•	•	•	•	•	•	•	•	•	•
682	6800 pF	••	••	••	••	•			•	•	•	•	•	•	•	•	•	•
822	8200 pF	••	••	••	••	•			•	•	•	•	•	•	•	•	•	•
103	0.010 μF	••	••	••	••	•			•	•	•	•	•	•	•	•	•	•
123	0.012 μF	••	••	••	•	•			•	•	•	•	•	•	•	•	•	•
153	0.015 μF	••	••	••	•	•			•	•	•	•	•	•	•	•	•	•
183	0.018 μF	••	••	••	•	•			•	•	•	•	•	•	•	•	•	•
223	0.022 μF	••	••	••	•	•			•	•	•	•	•	•	•	•	•	•
273	0.027 μF	•	•	•	•				•	•	•	•	•	•	•	•	•	•
333	0.033 μF	•	•	•	•				•	•	•	•	•	•	•	•	•	•
393	0.039 μF	•	•	•	•				•	•	•	•	•	•	•	•	•	•
473	0.047 μF	•	•	•	•				•	•	•	•	•	•	•	•	•	•
563	0.056 μF	•	•	•					•	•	•	•	•	•	•	•	•	•
683	0.068 μF	•	•	•					•	•	•	•	•	•	•	•	•	•
823	0.082 μF	•	•	•					•	•	•	•	•	•	•	•	•	•
104	0.10 μF	•	•	•					•	•	•	•	•	•	•	•	•	•
124	0.12 μF	•	•						•	•	•	•	•	•	•	•	•	•
154	0.15 μF	•	•						•	•	•	•	•	•	•	•	•	•
184	0.18 μF	•							•	•	•	•	•	•	•	•	•	•
224	0.22 μF	•							•	•	•	•	•	•	•	•	•	•
274	0.27 μF								•	•	•	•	•	•	•	•	•	•
334	0.33 μF								•	•	•	•	•	•	•	•	•	•
394	0.39 μF								•	•	•	•	•	•	•	•	•	•
474	0.47 μF								•	•	•	•	•	•	•	•	•	•
564	0.56 μF								•	•	•	•	•	•	•	•	•	•
684	0.68 μF								•	•	•	•	•	•	•	•	•	•
824	0.82 μF								•	•	•	•	•	•	•	•	•	•
105	1.0 μF																	
125	1.2 μF																	
155	1.5 μF																	
185	1.8 μF																	
225	2.2 μF																	

Note

(1) See soldering recommendations within this data book, or visit www.vishay.com/doc?45034

•• Paper tape • Plastic tape



SELECTION CHART																
DIELECTRIC		X7R														
STYLE		VJ1210 ⁽¹⁾										VJ1808 ⁽¹⁾				
EIA TYPE		1210										1808				
VOLTAGE (Vdc)		16	25	50	100	200	500	630	1000	1500	2000	630	1000	1500	2000	3000
CAP. CODE	CAP.															
101	100 pF															
121	120 pF															
151	150 pF															
181	180 pF															
221	220 pF															•
271	270 pF															•
331	330 pF															•
391	390 pF								•	•	•					•
471	470 pF								•	•	•	•	•	•	•	•
561	560 pF								•	•	•	•	•	•	•	•
681	680 pF								•	•	•	•	•	•	•	•
821	820 pF								•	•	•	•	•	•	•	•
102	1000 pF								•	•	•	•	•	•	•	•
122	1200 pF								•	•	•	•	•	•	•	•
152	1500 pF								•	•	•	•	•	•	•	•
182	1800 pF								•	•	•	•	•	•	•	
222	2200 pF								•	•	•	•	•	•	•	
272	2700 pF								•	•	•	•	•	•	•	
332	3300 pF								•	•	•	•	•	•	•	
392	3900 pF								•	•		•	•	•		
472	4700 pF								•	•		•	•	•		
562	5600 pF								•			•	•	•		
682	6800 pF								•			•	•	•		
822	8200 pF								•			•	•			
103	0.010 μF	•	•	•	•	•	•	•	•			•	•			
123	0.012 μF	•	•	•	•	•	•	•				•	•			
153	0.015 μF	•	•	•	•	•	•	•				•	•			
183	0.018 μF	•	•	•	•	•	•	•				•	•			
223	0.022 μF	•	•	•	•	•	•	•								
273	0.027 μF	•	•	•	•	•	•	•								
333	0.033 μF	•	•	•	•	•	•	•								
393	0.039 μF	•	•	•	•	•	•	•								
473	0.047 μF	•	•	•	•	•										
563	0.056 μF	•	•	•	•	•										
683	0.068 μF	•	•	•	•	•										
823	0.082 μF	•	•	•	•	•										
104	0.10 μF	•	•	•	•	•										
124	0.12 μF	•	•	•	•	•										
154	0.15 μF	•	•	•	•	•										
184	0.18 μF	•	•	•	•											
224	0.22 μF	•	•	•	•											
274	0.27 μF	•	•	•	•											
334	0.33 μF	•	•	•	•											
394	0.39 μF	•	•	•	•											
474	0.47 μF	•	•	•	•											
564	0.56 μF	•	•	•												
684	0.68 μF	•	•	•												
824	0.82 μF	•	•													
105	1.0 μF	•														
125	1.2 μF															
155	1.5 μF															
185	1.8 μF															
225	2.2 μF															

Note

⁽¹⁾ See soldering recommendations within this data book, or visit www.vishay.com/doc?45034



SELECTION CHART																		
DIELECTRIC		X7R																
STYLE		VJ1812 ⁽¹⁾									VJ1825 ⁽¹⁾							
EIA TYPE		1812									1825							
VOLTAGE (Vdc)		50	100	200	250	500	630	1000	1500	2000	3000	100	200	500	630	1000	1500	2000
CAP. CODE	CAP.																	
101	100 pF	•	•	•	•	•												
121	120 pF	•	•	•	•	•												
151	150 pF	•	•	•	•	•												
181	180 pF	•	•	•	•	•												
221	220 pF	•	•	•	•	•												
271	270 pF	•	•	•	•	•	•	•	•	•	•							
331	330 pF	•	•	•	•	•	•	•	•	•	•							
391	390 pF	•	•	•	•	•	•	•	•	•	•							
471	470 pF	•	•	•	•	•	•	•	•	•	•							
561	560 pF	•	•	•	•	•	•	•	•	•	•							
681	680 pF	•	•	•	•	•	•	•	•	•	•							
821	820 pF	•	•	•	•	•	•	•	•	•	•							
102	1000 pF	•	•	•	•	•	•	•	•	•	•							
122	1200 pF	•	•	•	•	•	•	•	•	•	•							
152	1500 pF	•	•	•	•	•	•	•	•	•	•							
182	1800 pF	•	•	•	•	•	•	•	•	•	•							
222	2200 pF	•	•	•	•	•	•	•	•	•	•							
272	2700 pF	•	•	•	•	•	•	•	•	•	•							
332	3300 pF	•	•	•	•	•	•	•	•	•	•							
392	3900 pF	•	•	•	•	•	•	•	•	•	•							
472	4700 pF	•	•	•	•	•	•	•	•	•	•							
562	5600 pF	•	•	•	•	•	•	•	•	•	•						•	•
682	6800 pF	•	•	•	•	•	•	•	•	•	•						•	•
822	8200 pF	•	•	•	•	•	•	•	•	•	•						•	•
103	0.010 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
123	0.012 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
153	0.015 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
183	0.018 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
203	0.020 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
223	0.022 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
273	0.027 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
333	0.033 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
393	0.039 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
473	0.047 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
563	0.056 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
683	0.068 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
823	0.082 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
104	0.10 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
124	0.12 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
154	0.15 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
184	0.18 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
224	0.22 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
274	0.27 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
334	0.33 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
394	0.39 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
474	0.47 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
564	0.56 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
684	0.68 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
824	0.82 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
105	1.0 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
125	1.2 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
155	1.5 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
185	1.8 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
225	2.2 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•

Note

⁽¹⁾ See soldering recommendations within this data book, or visit www.vishay.com/doc?45034









SELECTION CHART																	
DIELECTRIC		X7R															
STYLE		VJ2220 ⁽¹⁾									VJ2225 ⁽¹⁾						
EIA TYPE		2220									2225						
VOLTAGE (Vdc)		50	100	200	250	500	630	1000	2000	3000	100	200	500	630	1000	1500	2000
CAP. CODE	CAP.																
101	100 pF																
121	120 pF																
151	150 pF																
181	180 pF																
221	220 pF																
271	270 pF																
331	330 pF																
391	390 pF																
471	470 pF																
561	560 pF																
681	680 pF																
821	820 pF																
102	1000 pF									•							
122	1200 pF									•							
152	1500 pF									•							
182	1800 pF									•							
222	2200 pF									•							
272	2700 pF																
332	3300 pF																
392	3900 pF																
472	4700 pF																
562	5600 pF									•						•	•
682	6800 pF									•						•	•
822	8200 pF									•						•	•
103	0.010 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
123	0.012 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
153	0.015 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
183	0.018 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
203	0.020 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
223	0.022 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
273	0.027 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
333	0.033 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
393	0.039 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
473	0.047 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
563	0.056 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
683	0.068 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
823	0.082 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
104	0.10 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
124	0.12 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
154	0.15 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
184	0.18 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
224	0.22 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
274	0.27 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
334	0.33 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
394	0.39 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
474	0.47 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
564	0.56 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
684	0.68 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
824	0.82 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
105	1.0 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
125	1.2 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
155	1.5 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
185	1.8 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
225	2.2 μF	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•

Note

⁽¹⁾ See soldering recommendations within this data book, or visit www.vishay.com/doc?45034



OMD - CAPACITORS - TYPICAL PARAMETERS



BOARDFLEX SENSITIVE APPLICATIONS - SOLUTION:

A predominant failure mode in multilayer ceramic chip capacitors is cracking caused by board flexure. Cracks can then create a path for current to pass from one electrode through the dielectric to an opposing electrode or from the terminations at one end of the MLCC through the dielectric to an opposing electrode. This may subsequently result in capacitance loss, leakage - low Insulation Resistance (IR) - and/or more seriously, high current shorts. A short circuit condition in the surface mounted capacitors can cause further failures of downstream components. Vishay's Open Mode Design Capacitors (VJ OMD - Cap series) reduce the risk of these destructive conditions through MLCC designs that prevent board flexure cracks reaching the opposing electrode.


VJ OMD - Cap MLCCs reduce the risk of early field failures associated with board flex cracks. However, it is important to note that even in the open mode designs the presence of flexure related cracks can cause capacitance loss leading to localized stresses on the parts. eventually, depending on the application environment, including such factors and high voltage pulse frequency and thermal cycling this may lead to internal breakdown of the component.

POLYMER TERMINATION

Polymer termination provides additional protection against board flexure damage by absorbing greater mechanical and thermal stresses. Components can be packaged, transported, stored and handled the same standard terminated product. Wave and reflow soldering of MLCC does not require modification to equipment and/or process. Polymer termination greatly reduces the risk of mechanical cracking however it does not completely eliminate.



STANDARD TERMINATION

Exposed Electrodes = Electrical Short



OMD CAP PLUS POLYMER TERMINATION

No Exposed Electrodes = No Electrical Short





STANDARD PACKAGING QUANTITIES (1)(2)(3)					
		7" REEL QUANTITIES		11 1/4" AND 13" REEL QUANTITIES	
BODY SIZE	TAPE SIZE	PAPER TAPE PACKAGING CODE "C"/"O"	PLASTIC TAPE PACKAGING CODE "T"	PAPER TAPE PACKAGING CODE "P"/"I"	PLASTIC TAPE PACKAGING CODE "R"
0805	8 mm	3000	3000	10 000	10 000
1206 ⁽⁴⁾	8 mm	N/a	3000/2500	N/a	10 000/9000
1210 ⁽⁴⁾	8 mm	N/a	3000/2500/2000	N/a	10 000/9000
1808 ⁽⁴⁾	12 mm	N/a	3000/2500	N/a	10 000
1812 ⁽⁴⁾	12 mm	N/a	1000	N/a	5000/4000
1825	12 mm	N/a	1000	N/a	4000
2220	12 mm	N/a	1000	N/a	4000
2225	12 mm	N/a	1000	N/a	4000

Notes

- (1) Vishay Vitramon uses embossed plastic and punch paper carrier tapes. Paper tape is not available for case sizes > 1206 or for component thickness > 0.035" [0.89 mm]
- (2) REFERENCE: EIA Standard RS 481 - "Taping of Surface Mount Components for Automatic Placement"
- (3) N/a = Not available
- (4) Packaging code "C/O", "P/I" or "T/R" and lower quantities can depend from product thickness



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.