



Multilayer Ceramic Dipped Radial K10 Capacitors

DIMENSIONS



L2


Component outline for lead spacing 2.5 ± 0.8 mm (straight leads)



H5


Component outline for lead spacing 5.0 ± 0.8 mm (flat bent leads)

L2 and H5 are preferred styles



K2

Component outline for lead spacing 2.5 ± 0.8 mm (outside kink)



K5

Component outline for lead spacing 5.0 ± 0.8 mm (outside kink)


CAPACITOR DIMENSIONS AND WEIGHT in millimeter (inches)								
SIZE	Wb _{max.}	H _{max.}	T _{max.}	MAX. SEATING HEIGHT (SH)				WEIGHT (g)
				L2	H5	K2	K5	
10	3.6 (0.142)	3.6 (0.142)	2.3 (0.090)	1.58 (0.062)	2.54 (0.100)	3.50 (0.140)	3.50 (0.140)	≈ 0.10

Note


- Bulk packed types have a standard lead length L = 25.4 mm (1.0") minimum
- Thickness is defined as "T"

MARKING


SIZE 10 CAPACITANCE VALUE < 100 pF




For example



SIZE 10 CAPACITANCE VALUE ≥ 100 pF



For example



Note

- Vishay or BCcomponents logo can be marked on the products body