

Surface Mount Miniature Trimmers Single-Turn Cermet Fully Sealed



The TS5 trimming potentiometer has been designed for surface mount applications and offers volumetric efficiency (5 mm x 5 mm x 2.7 mm) with high performance and stability.

The TS5 design is suitable for both manual or automatic operation, and can withstand wave and reflow soldering techniques.





FEATURES

- 0.25 W at 70 °C
- CECC 41100
- GAM T1
- Professional grade
- Wide ohmic range (10 Ω to 1 MΩ)
- Full sealing
- Low contact resistance variation (1 % or 3 Ω)
- Small size for optimum packing density
- Suitable for both manual or automatic operation
- Compliant to RoHS directive 2002/95/EC since date code 0445





RoHS
COMPLIANT

DIMENSIONS in millimeters (± 0.25 mm)

TS5YL

TS5YJ


Cruciform screwdriver slot
 Ø 2.5, width 0.5
 Deep: 0.55
 Max. deep (center): 0.7

RECOMMENDED SOLDERING AREAS

TS5YL

TS5YJ


| ELECTRICAL SPECIFICATIONS | | | | | | | | | | | | | | | | | | | | | |
|---------------------------------------|--|--------------------------|------------------|---|------|----|------|----|------|----|------|----|------|----|------|-----|------|-----|------|-----|------|
| Resistive Element | Cermet | | | | | | | | | | | | | | | | | | | | |
| Electrical Travel | 220° ± 15° | | | | | | | | | | | | | | | | | | | | |
| Resistance Range | 10 Ω to 1 MΩ | | | | | | | | | | | | | | | | | | | | |
| Standard Series | 1 - 2 - 5 | | | | | | | | | | | | | | | | | | | | |
| Tolerance Standard | ± 10 % | | | | | | | | | | | | | | | | | | | | |
| Variation Law | <p style="text-align: center;">CIRCUIT DIAGRAM</p> <p style="text-align: center;">Linear</p> | | | | | | | | | | | | | | | | | | | | |
| Power Rating | <p style="text-align: center;">0.25 W at 70 °C</p> <table border="1"> <caption>Power Rating vs Ambient Temperature</caption> <thead> <tr> <th>Ambient Temperature (°C)</th> <th>Power Rating (W)</th> </tr> </thead> <tbody> <tr><td>0</td><td>0.25</td></tr> <tr><td>20</td><td>0.25</td></tr> <tr><td>40</td><td>0.25</td></tr> <tr><td>60</td><td>0.25</td></tr> <tr><td>70</td><td>0.25</td></tr> <tr><td>80</td><td>0.20</td></tr> <tr><td>100</td><td>0.10</td></tr> <tr><td>120</td><td>0.00</td></tr> <tr><td>125</td><td>0.00</td></tr> </tbody> </table> | Ambient Temperature (°C) | Power Rating (W) | 0 | 0.25 | 20 | 0.25 | 40 | 0.25 | 60 | 0.25 | 70 | 0.25 | 80 | 0.20 | 100 | 0.10 | 120 | 0.00 | 125 | 0.00 |
| Ambient Temperature (°C) | Power Rating (W) | | | | | | | | | | | | | | | | | | | | |
| 0 | 0.25 | | | | | | | | | | | | | | | | | | | | |
| 20 | 0.25 | | | | | | | | | | | | | | | | | | | | |
| 40 | 0.25 | | | | | | | | | | | | | | | | | | | | |
| 60 | 0.25 | | | | | | | | | | | | | | | | | | | | |
| 70 | 0.25 | | | | | | | | | | | | | | | | | | | | |
| 80 | 0.20 | | | | | | | | | | | | | | | | | | | | |
| 100 | 0.10 | | | | | | | | | | | | | | | | | | | | |
| 120 | 0.00 | | | | | | | | | | | | | | | | | | | | |
| 125 | 0.00 | | | | | | | | | | | | | | | | | | | | |
| Temperature Coefficient | See Standard Resistance Element Data | | | | | | | | | | | | | | | | | | | | |
| Limiting Element Voltage (Linear Law) | 200 V | | | | | | | | | | | | | | | | | | | | |
| Contact Resistance Variation | 1 % or 3 Ω | | | | | | | | | | | | | | | | | | | | |
| End Resistance (Typical) | 0.1 % or 3 Ω | | | | | | | | | | | | | | | | | | | | |
| Dielectric Strength (RMS) | 1000 V | | | | | | | | | | | | | | | | | | | | |
| Insulation Resistance | 1 GΩ | | | | | | | | | | | | | | | | | | | | |

| MECHANICAL SPECIFICATIONS | |
|-----------------------------|--------------|
| Mechanical Travel | 270° ± 10° |
| Operating Torque (max. Ncm) | 1.5 |
| End Stop Torque (max. Ncm) | 3.5 |
| Net Weight (max. g) | 0.15 |
| Terminals | Pure Sn (e3) |

| ENVIRONMENTAL SPECIFICATIONS | |
|------------------------------|-----------------------|
| Temperature Range | - 55 °C to + 125 °C |
| Climatic Category | 55/125/56 |
| Sealing | Sealed container IP67 |
| MSL Level | 4 |



Surface Mount Miniature Trimmers
Single-Turn Cermet Fully Sealed

Vishay Sfernice

| PERFORMANCE | | | |
|--|--|--|--|
| TESTS | CONDITIONS | TYPICAL VALUES AND DRIFTS | |
| | | $\Delta R_T/R_T$ (%) | $\Delta R_{1-2}/R_{1-2}$ (%) |
| Load Life | 1000 h at rated power 90/30' ambient temperature + 70 °C | ± 2 % Contact resistance variation: $\Delta R < 1 \% R_n$ | ± 3 % |
| Climatic Sequence | Phase A dry heat 125 °C Phase B damp heat Phase C cold - 55 °C Phase D damp heat 5 cycles | ± 2 % | ± 3 % |
| Long Term Damp Heat | Temperature 40 °C RH 93 % 56 days | ± 2 % Dielectric strength: 1000 V _{RMS} Insulation resistance: > 10 ⁴ MΩ | ± 3 % |
| Thermal Shock | 55 °C to + 125 °C 5 cycles | ± 1 % | $\Delta V_{1-2}/V_{1-3} \leq \pm 2 \%$ |
| Rotational Life (Electrical and Mechanical) | 100 cycles Rated power | ± (3 % + 5 Ω) | |
| Shock | 50 g at 11 ms 3 successive shocks in 3 directions | ± 1 % | $\Delta V_{1-2}/V_{1-3} \leq \pm 1 \%$ |
| Vibration | 10 Hz to 55 Hz 0.75 mm or 10 g during 6 h | ± 1 % | $\Delta V_{1-2}/V_{1-3} \leq \pm 1 \%$ |

| STANDARD RESISTANCE ELEMENT DATA | | | | |
|----------------------------------|---------------------|----------------------|---------------------------|--|
| STANDARD RESISTANCE VALUES | LINEAR LAW | | | TYPICAL TCR - 55 °C + 125 °C ppm/°C |
| | MAX. POWER AT 70 °C | MAX. WORKING VOLTAGE | MAX. CUR. THROUGH ELEMENT | |
| Ω | W | V | mA | |
| 10 | 0.25 | 1.58 | 158 | ± 100 |
| 20 | ↓ | 2.24 | 112 | |
| 50 | | 3.54 | 71 | |
| 100 | | 5.00 | 50 | |
| 200 | | 7.07 | 35 | |
| 500 | | 11.2 | 22 | |
| 1K | | 15.8 | 16 | |
| 2K | | 22.4 | 11 | |
| 5K | | 35.4 | 7 | |
| 10K | | 50.0 | 5 | |
| 20K | | 70.7 | 3.5 | |
| 50K | 112 | 2.2 | | |
| 100K | 0.25 | 158 | 1.6 | |
| 200K | 0.20 | 200 | 1.0 | |
| 500K | 0.08 | 200 | 0.4 | |
| 1M | 0.04 | 200 | 0.2 | |

MARKING

VISHAY trademark, ohmic value, manufacturing date.

The ohmic value is indicated by a 3 figure code, the first two are significant figures, the third one is the multiplier.

Example:
 100 = 10 Ω
 101 = 100 Ω
 102 = 1000 Ω
 503 = 50 000 Ω

SOLDERING RECOMMENDATIONS

see Application notes

CAUTION

Reflow soldering must be done within 72 h while stored under a max. temperature of 30 °C, 60 % RH after opening the dry pack envelope.

RECOMMENDED METHOD OF STORAGE

Dry box storage is recommended as soon as the hermetic bag has been opened to prevent moisture absorption. The following conditions should be observed, if dry boxes are not available:

- Storage temperature 10 °C to 30 °C
- Storage humidity ≤ 60 % RH max.



After more than 72 h under these conditions, moisture content will be too high for reflow soldering.

In case of moisture absorption, the devices will recover to the former condition by drying under the following condition:

- 192 h at 40 °C + 5 °C/- 0 °C and < 5 % RH (dry air/nitrogen) or
- 96 h at 60 °C + 5 °C and < 5 % RH for all device containers (not suitable for reel) or
- 24 h at 125 °C + 5 °C (not suitable for reel)

PACKAGING

On tape and reel of 500 pieces, code R10 (TR500) and 2000 pieces, code R20 (TR2000)




Cover tape panel strength specifications EIA 481 A and CEI 60286-3.


DRYPACK

Devices are packed in moisture barrier bags to prevent the products from moisture absorption during transportation and storage. Each bag contains a desiccant.

SAP ORDERING INFORMATION (Part Number 15 digits)



PART NUMBER DESCRIPTION (for information only)





Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.