

Dual Value Chip Resistors, Center Tap



Actual Size

The VISHAY RSK33 resistive dividers are based on a nickel-chromium thin metal film formulation on an oxidized silicon substrate and incorporate two resistors of equal ohmic value for use either as a precision voltage divider or as a four terminal resistor. The RSK33 micro dividers were developed as a low cost, temperature and time stable resistive range for hybrid circuit applications demanding miniaturization with improved parametric performances in both industrial and military environments.

Their close ratio tolerance and TCR tracking performances are particularly relevant to amplifier gain-setting and diverse attenuator and terminator applications.

FEATURES


- Economic Cost
- Low TCR < 25 ppm/°C
- Rapid Rise Time
- Low Noise < 35 dB
- Stability 0.03 % (2000 h, rated power, at + 70 °C)
- Wirebondable



TYPICAL PERFORMANCE

	ABS	TRACKING
TCR	15 ppm/°C	5 ppm/°C
	ABS	RATIO
TOL.	0.5 %	0.05 %

SCHEMATIC



STANDARD ELECTRICAL SPECIFICATIONS		
TEST	SPECIFICATIONS	CONDITIONS
SERIES	ULTRAFILM®	
Resistance range	10 Ω to 500 kΩ	(R _T = R ₁ + R ₂)
Extended ohmic range	> 500 kΩ to 1 MΩ	$R_1 = R_2 \left(R_T = \frac{R_T}{2} + \frac{R_T}{2} \right)$
		R ₁ ≠ R ₂ : Please consult
TCR:	Tracking	± 5 ppm/°C maximum - 55 °C to + 125 °C
	Absolute	± 25 ppm/°C maximum (± 15 ppm/°C typical) - 55 °C to + 125 °C
Tolerance:	Ratio	± 0.5 % (tighter on request) ⁽²⁾ R > 10 Ω
	Absolute	± 0.5 %, ± 1 %, ± 2 %
Power rating:	250 mW at 70 °C, 50 mW at + 125 °C	
Stability	300 ppm typical	2000 h Pn at + 70 °C
Voltage coefficient	< 0.01 ppm/V	
Working voltage	100 V _{DC} on R _T	
Operating temperature range	- 55 °C to + 155 °C ⁽¹⁾	
Storage temperature range	- 55 °C to + 155 °C	
Noise	< - 35 dB typical	MIL-STD-202 Method 308
Thermal EMF	< 0.01 μV/°C	
Shelf life stability	50 ppm	1 year


Notes:

⁽¹⁾ For temperature up to 200 °C, please contact factory

⁽²⁾ For tighter ratio: please consult (ohmic range may vary)

* Please see document "Vishay Green and Halogen-Free Definitions (5-2008)" <http://www.vishay.com/doc?99902>

DIMENSIONS



DIMENSION	INCHES	MILLIMETERS
A	0.029	0.76 ± 0.1
B	0.029	0.76 ± 0.1
C	0.009	0.25 to 0.4
D	0.005	0.15
E	0.004	0.1
F	0.005	0.15

MECHANICAL SPECIFICATIONS	
Resistive element	Passivated Nichrome
Passivation	Silicon Nitride
Substrate material	Silicon
Bonding pads	Aluminum

GLOBAL PART NUMBER INFORMATION																
New Global Part Numbering: RSK33N5KD25KB0016 (preferred part number format)																
R	S	K	3	3	N	5	K	D	2	5	K	B	0	0	1	6
GLOBAL MODEL		R1 VALUE		ABS. TOLERANCE			R2 VALUE		RAT. TOLERANCE			OPTION				
		Decimal R, K or M		D = ± 0.5 % F = ± 1.0 % G = ± 2.0 %			Decimal R, K or M		D = 0.5 % B = 0.1 % W = 0.05 %			leave blank if no option				
Historical Part Number example: RSK 33N 5K 25K 1% 0.1% R0016 (will continue to be accepted)																
RSK 33N		5K 25K		0.5 % 0.1 %			R0016									
HISTORICAL MODEL		R1/R2 VALUE		ABS. TOLERANCE AND RATIO TOLERANCE			OPTION									



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.