


## Thin Film Single Value Chip and Wire Capacitors




Product may not be to scale

The NC series of thin film capacitors has the advantage of increased performance and smaller size when compared with its thick film counterparts. These chips are available in sizes down to 20 mil square and in capacitances up to 1000 pF.

Parts require epoxy or eutectic die attach to substrate and one wire bond.

These chips are manufactured using Vishay Electro-Films (EFI) sophisticated Thin Film equipment and manufacturing technology. The NC's are 100 % electrically tested and visually inspected to MIL-STD-883.

### ELECTRICAL SCHEMATIC NCAA/NCBB/NCCC





### FEATURES

- Wire bondable
- Small size: 0.020 inches square to 0.060 inches square
- Substrate: Silicon with gold backing
- Dielectric: Silicon dioxide/silicon nitride
- Capacitance range: 0.5 pF to 1000 pF

### APPLICATIONS

The NC series of capacitor chips are designed for assembly in hybrid circuits using conventional wire-bonding techniques. They provide excellent stability and performance, and their small size gives the hybrid designer greater layout flexibility. They are available as MNOS or MOS capacitors. The MOS version is to be preferred when low dielectric absorption is required.

### ELECTRICAL SCHEMATIC NCDD/NCEE



### WV (DC) VALUES AND TOLERANCES

CAPACITOR MODEL	NCAA	NCBB	NCCC	NCDD	NCEE	UNIT
Case Size	0202	0303	0404	0505	0606	
Capacitance Values	0.5 to 51	33 to 100	56 to 220	150 to 510	360 to 1000	pF
Tolerance	± 2.5, ± 5, ± 10, ± 20, ± 25	± 2.5, ± 5, ± 10, ± 20	± 2.5, ± 5, ± 10, ± 20	± 2.5, ± 5, ± 10, ± 20	± 2.5, ± 5, ± 10, ± 20	%
DC Working Voltage	200	150	190	140	65	V


### STANDARD ELECTRICAL SPECIFICATIONS

PARAMETER	VALUE	UNIT
Capacitance Range	0.5 to 1000	pF
Maximum Working Voltage	200	V
Peak Voltage at + 25 °C	1.5 x working voltage	
Dissipation Factor, 1 kHz, 1 V <sub>RMS</sub> , + 25 °C	0.05 MNOS 0.1 MOS	%
Q at 1 mHz, 50 mV <sub>RMS</sub> , + 25 °C	1000 min.	
TCC, - 55 °C to + 150°C	+ 45 ± 25 MNOS + 15 ± 25 MOS	ppm/°C
Insulation Resistance at Working Voltage, + 25 °C	10 <sup>9</sup> min.	Ω
Operating Temperature Range	- 55 to + 125	°C
Thermal Shock	± 0.25 + 0.25 pF max. ΔC/C	%
Moisture Resistance, MIL-STD-202, Method 106	± 1.0 + 0.25 pF max. ΔC/C	%
Short Time Overload, + 25 °C, 5 s, 1.5 x Working Voltage	± 0.25 + 0.25 pF max.	%
High Temperature Exposure, 100 h at 150°C Ambient	± 0.25 + 0.25 pF max. ΔC/C	%
Life, MIL-STD-202, Method 108 Condition D, + 125 °C Ambient, 100 h at Working Voltage	± 0.25 + 0.25 pF max. ΔC/C	%



DC WORKING VOLTAGES VALUES AND TOLERANCES

NCAA 0.020 inches square




NA = NOT AVAILABLE

NCBB 0.030 inches square

NCCC 0.040 inches square

NCEE 0.060 inches square  
NCDD 0.055 inches square



**DIMENSIONS**

0.5 pF to 1.3 pF



1.4 pF to 3.9 pF



4 pF to 9.1 pF




10 pF to 51 pF


**NCAA**  
 0.020 ± 0.003 inches square


33 pF to 100 pF




56 pF to 220 pF



150 pF to 510 pF



360 pF to 1000 pF


**NCBB**  
 0.030 ± 0.003 inches square

**NCCC**  
 0.040 ± 0.003 inches square

**NCDD**  
 0.055 ± 0.003 inches square

**NCEE**  
 0.060 ± 0.003 inches square

**MECHANICAL SPECIFICATIONS**

PARAMETER	VALUE
Chip Size	Per diagrams
Chip Thickness	0.010" ± 0.002" (0.25 mm ± 0.05 mm)
Chip Substrate Material	Semiconductor silicon
Dielectric	Silicon dioxide/silicon nitride
Bond Pad	0.005" x 0.005" min., 10 kÅ aluminum
Backing	3 kÅ min. gold

**Options:** Gold bond pads 15 kÅ. Lower profile version is available, consult applications engineer

**GLOBAL PART NUMBER INFORMATION**

SAP Part Number: NCAA4700CKMAHWS

NCEE1000KNGKWS

SAP Description: NCAA 4.7 pF 10 % MOS Al H WS

NCEE 1000 pF 10 % MNOS Au K WS

N	C	A	A	4	7	0	0	C	K	M	A	H	W	S
---	---	---	---	---	---	---	---	---	---	---	---	---	---	---

MODEL	CAPACITANCE (pF)	CAPACITANCE MULTIPLIER CODE	TOLERANCE CODE	DIELECTRIC	TERMINATION	VISUAL CLASS	PACKAGING CODE
NCAA NCBB NCCC NCDD NCEE	First 4 digits are significant figures of capacitance	D = 0.0001 C = 0.001 B = 0.01 A = 0.1 0 = 1	D = ± 0.5 pF H = 2.5 % J = 5.0 % K = 10 % M = 20 %	M = MOS N = MNOS	G = Au A = Al	H = Class H K = Class K	WS = Waffle pack 100 min., 1 mult



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.