



Hermetic Flat Pack Thin Film Resistor, Surface Mount Network



Product may not be to scale

FEATURES

- Military/aerospace
- Hermetically sealed
- Compliant to RoHS Directive 2002/95/EC
- Halogen-free according to IEC 61249-2-21 definition




Note

* Pb containing terminations are not RoHS compliant, exemptions may apply

Vishay Dale Thin Film offers a broad line of precision resistor networks in hermetic Flat-Packs for surface mount requirements in military, space or other harsh environmental applications. These networks provide the long-term stability necessary to insure continuous specification and performance over the 20 years to 30 years life required for

space applications. The fabrication of these devices is performed under tight procedural and environmental controls to insure conformance to all 883C level H or K requirements. Custom configurations, values and tolerance combinations are available with fast turnaround.

SCHEMATICS



FP200	
Number of Resistors	7, 8
Number of Leads	14, 16
Type Connection	Isolated
Values Available	500 Ω to 100 kΩ

FP201	
Number of Resistors	12, 14
Number of Leads	14, 16
Type Connection	Series
Values Available	500 Ω to 100 kΩ

FP202	
Number of Resistors	13, 15
Number of Leads	14, 16
Type Connection	Common
Values Available	500 Ω to 100 kΩ

STANDARD ELECTRICAL SPECIFICATIONS		
TEST	SPECIFICATIONS	CONDITIONS
Material	Passivated nichrome	-
Pin/Lead Number	14, 16	-
Resistance Range	10 Ω to 1 MΩ (total)	-
TCR: Absolute	± 10 ppm/°C to 50 ppm/°C	-
TCR: Tracking	± 5 ppm/°C (standard)	-
Tolerance: Absolute	± 0.05 % to ± 1 %	-
Tolerance: Ratio	± 0.01 % to ± 0.1 %	-
Power Rating: Resistor	100 mW	-
Power Rating: Package	800 mW	70 °C
Stability: Absolute	ΔR ± 0.05 %	2000 h at + 70 °C
Stability: Ratio	ΔR ± 0.015 %	2000 h at + 70 °C
Voltage Coefficient	-	-
Working Voltage	100 V max. not to exceed $\sqrt{P \times R}$	-
Operating Temperature Range	- 55 °C to + 125 °C	-
Storage Temperature Range	- 55 °C to + 150 °C	-
Noise	-	-
Thermal EMF	-	-
Shelf Life Stability: Absolute	ΔR ± 0.01 %	1 year at + 25 °C
Shelf Life Stability: Ratio	ΔR ± 0.002 %	1 year at + 25 °C

DIMENSIONS in inches (millimeters)					
FLAT-PAK FP200	DIMENSION	14 LEAD		16 LEAD	
		MINIMUM	MAXIMUM	MINIMUM	MAXIMUM
	A	0.086 (2.18)	0.106 (2.69)	0.045 (1.14)	0.115 (2.92)
	b	0.015 (0.38)	0.019 (0.48)	0.015 (0.38)	0.019 (0.48)
	C	0.004 (0.10)	0.007 (0.18)	0.003 (0.08)	0.009 (0.23)
	D	0.373 (9.47)	0.383 (9.73)	-	0.440 (11.18)
	e	0.047 (1.19)	0.053 (1.35)	0.050 (1.27)	BSC
	E	0.250 (6.35)	0.260 (6.60)	0.245 (6.22)	0.285 (7.24)
	E ₁	-	0.290 (7.37)	-	0.315 (8.00)
	E ₂	0.158 (4.01)	0.172 (4.37)	0.130 (3.30)	-
	E ₃	0.030 (0.76)	-	0.030 (0.76)	-
	L	-	-	0.250 (6.35)	0.370 (9.40)
	Q	0.026 (0.66)	-	0.26 (0.66)	0.045 (1.14)
	S	-	0.045 (1.14)	-	0.045 (1.14)
	S ₁	0.005 (0.13)	-	0.005 (0.13)	-
	k	-	-	0.008 (0.20)	0.015 (0.38)

GLOBAL PART NUMBER INFORMATION																	
New Global Part Numbering: FP2001681001BFBCW																	
F	P	2	0	0	1	6	8	1	0	0	1	B	F	B	C	W	
F	P	2	0	2	1	6	1	3	1	0	0	1	B	F	B	C	W
GLOBAL MODEL	CASE SIZE	NUMBER OF RESISTORS (1 or 2 digits)	OHMIC VALUE	ABSOLUTE TOLERANCE	RATIO TOLERANCE	ABSOLUTE TCR	RATIO TCR	PACKAGING									
FP200	14 16	7 8	The first 3 digits are significant figures and the last digit specifies the number of zeros to follow. "R" designates the decimal point. Example: 10R0 = 10 Ω 1000 = 100 Ω 1001 = 1000 Ω	A = 0.05 % B = 0.1 % C = 0.2 % D = 0.5 % F = 1 % G = 2 % J = 5 % K = 10 % M = 20 %	B = 0.01 % C = 0.025 % D = 0.05 % F = 0.1 % H = 0.25 % J = 0.5 % K = 1 % X = Not applicable	A = 10 ppm/°C B = 25 ppm/°C D = 50 ppm/°C E = 100 ppm/°C	C = 2 ppm ⁽¹⁾ D = 3 ppm ⁽¹⁾ F = 5 ppm G = 10 ppm X = N/A	W = WAFFLE 100 min., 1 mult									
FP201	14 16	12 14															
FP202	14 16	13 16															
Historical Part Number example: FP2001681002BFBC (for reference purposes only)																	
FP200	16	8	1002	B	F	B	C										
MODEL	NUMBER OF LEADS	NUMBER OF RESISTORS	RESISTANCE	ABSOLUTE TOLERANCE	RATIO TOLERANCE	ABSOLUTE TCR	RATIO TCR										

Note

(1) Value dependent



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.