


# Thin Film Chip Resistors

## Wire Bondable Dual Value



SIZE (inches) POWER VALUE RANGE	PERFORMANCE	FILM	MODEL
0.030 x 0.030 250 mW 1 Ω - 9.9 Ω		Ta <sub>2</sub> N	CTR (LOW VALUE)
0.030 x 0.030 250 mW 100 Ω - 500 kΩ		Ta <sub>2</sub> N	Dual Resistor Networks
0.030 x 0.030 250 mW 10 Ω - 1 MΩ		NiCr	CTN
0.030 x 0.030 250 mW 10 Ω - 1 MΩ		Ta <sub>2</sub> N	CTR
0.040 x 0.040 40 mW 200 kΩ - 10 MΩ		Ta <sub>2</sub> N	CTM

Performance Key			
TCR ± 10 ppm/°C TOL ± 0.05 %	TCR ± 25 ppm/°C TOL ± 0.1 %	TCR ± 50 ppm/°C TOL ± 0.5 %	TCR ± 100 ppm/°C TOL ± 1 %