

### Z-Foil Surface Mount Flip Chip Voltage Divider TCR Tracking of 0.1 ppm/°C, Absolute TCR ± 0.05 ppm/°C, with Resistance Ratio Stability of 0.005 % (50 ppm)



Bottom View

#### INTRODUCTION

Bulk Metal® Z-foil (BMZF) technology out-performs all other resistor technologies available today for applications that require ultra high precision and ultra high stability.


The new Z-foil technology provides a significant reduction of the resistive element's sensitivity to changes of temperature due to ambient temperature variations (TCR) and to self heating when power is applied (power coefficient).

Model **VFCD1505** offers low TCR (both absolute and tracking), excellent load life stability, tight tolerance, excellent ratio stability, low thermal EMF and low current noise, all in one package. 0.05 ppm/°C absolute TCR removes errors due to temperature gradients.


The **VFCD1505** surface mount divider provides tight tolerance matching and TCR tracking between 2 resistors simultaneously etched on one piece of foil on a common substrate. The electrical specifications of this integrated construction offers improved performances and better real estate utilization over discrete resistors and matched pairs.

Our application engineering department is available to advise and make recommendations for non-standard technical requirements and special applications, please contact us.

**FIGURE 1 - POWER DERATING CURVE**



**FIGURE 2 - SCHEMATIC**



#### FEATURES


- Temperature coefficient of resistance (TCR): absolute: (table 1) ± 0.05 ppm/°C (typical 0 °C to + 60 °C) ± 0.2 ppm/°C (typical - 55 °C to + 125 °C, + 25 °C ref.) Tracking: (table 1) 0.1 ppm/°C typical
- Resistance range: 1K to 10K
- Vishay Foil resistors are not restricted to standard values/ ratios, we can supply specific "as required" values/ratios at no extra cost or delivery (e.g 2K234/5K456)
- Power coefficient tracking: "ΔR due to self heating" 5 ppm at rated power
- Short time overload: ± 0.005 %
- Tolerance: absolute and resistance ratio: to 0.01 %
- Load life stability (0.1 W at 70 °C, 2000 h) Absolute: 0.01 % Ratio: 0.005 %
- Electrostatic discharge (ESD) up to 25 000 V
- Power rating at 70 °C: entire package: 0.1 W, divided between the two resistors proportionally to their value
- Non-inductive, non-capacitive design
- Thermal EMF: 0.05 μV/°C typical
- Current noise: < - 40 dB
- Rise time: 1 ns effectively no ringing
- Non inductive: < 0.08 μH
- Voltage coefficient: < 0.1 ppm/V
- Non hot spot design
- Terminal finishes available: lead (Pb)-free tin/lead alloy
- For better performances please contact us



Available  
**RoHS\***  
COMPLIANT

#### APPLICATIONS

- Instrumentation amplifiers
- Bridge networks
- Differential amplifiers
- Ratio arms in bridge circuits
- Medical and test equipment
- Military
- Airborne etc.



\* Pb containing terminations are not RoHS compliant, exemptions may apply

# VFCD1505 (Z-Foil Technology)



Vishay Foil Resistors

Z-Foil Surface Mount Flip Chip Voltage Divider  
 TCR Tracking of  $0.1 \text{ ppm}/^\circ\text{C}$ , Absolute TCR  $\pm 0.05 \text{ ppm}/^\circ\text{C}$ ,  
 with Resistance Ratio Stability of  $0.005 \%$  (50 ppm)

**TABLE 1 - RESISTANCE VALUES/RATIO AND TCR CHARACTERISTICS**

POPULAR VALUES	VCODES	ABSOLUTE TCR (- 55 °C TO + 125 °C, + 25 °C REF.)		TCR TRACKING		TOLERANCE MATCHING
		TYPICAL	MAXIMUM	TYPICAL	MAXIMUM	
10K/10K	V0001	$\pm 0.2 \text{ ppm}/^\circ\text{C}$	$\pm 1 \text{ ppm}/^\circ\text{C}$	0.1 ppm/°C	0.5 ppm/°C	0.01 %
5K/5K	V0002					
1K/1K	V0004					
2K/2K	V0059	$\pm 0.2 \text{ ppm}/^\circ\text{C}$	$\pm 1 \text{ ppm}/^\circ\text{C}$	0.4 ppm/°C	1.0 ppm/°C	0.01 %
5K/10K	V0005					
2.5K/10K	V0060					
1K/9K	V0056	$\pm 0.2 \text{ ppm}/^\circ\text{C}$	$\pm 1 \text{ ppm}/^\circ\text{C}$	0.4 ppm/°C	1.0 ppm/°C	0.02 %
1K/10K	V0064					

**Note**

- Additional ratios are available. For the relevant VCODES for ordering, please contact application engineering using the footer below


**TABLE 2 - TYPICAL PERFORMANCE SPECIFICATIONS**

TEST	MIL-PRF-55342H CHARACTERISTIC $\Delta R$ LIMITS <sup>1)</sup>	VFCD1505 $\Delta$ RATIO
Thermal shock	0.10 %	0.005 % (50 ppm)
Low temperature operation	0.10 %	0.005 % (50 ppm)
Short time overload	0.10 %	0.005 % (50 ppm)
High temperature exposure	0.10 %	0.01 % (100 ppm)
Resistance to soldering heat	0.20 %	0.01 % (100 ppm)
Moisture resistance	0.20 %	0.005 % (50 ppm)
Load life (ratio stability)	-	0.005 % (50 ppm)
Maximum working voltage for each element	22 V	
Weight	10 mg	
Packaging	Waffle pack standard, tape and reel available	

**Note**

1.  $\Delta R$ 's plus additional  $0.01 \Omega$  for measurement error

**FIGURE 3 - MODEL VFCD1505 DIMENSIONS AND LAND PATTERN** in inches (millimeters)







# VFCD1505 (Z-Foil Technology)

Z-Foil Surface Mount Flip Chip Voltage Divider  
 Vishay Foil Resistors  
 TCR Tracking of  $0.1 \text{ ppm}/^\circ\text{C}$ , Absolute TCR  $\pm 0.05 \text{ ppm}/^\circ\text{C}$ ,  
 with Resistance Ratio Stability of  $0.005 \%$  (50 ppm)

**FIGURE 4 - TRIMMING TO VALUES**  
 (Conceptual Illustration)




**FIGURE 5 - TYPICAL TCR CURVE Z-FOIL**  
 (for more details see table 1)



**TABLE 3 - GLOBAL PART NUMBER INFORMATION**

NEW GLOBAL PART NUMBER: Y1685V0001QQ9R (preferred part number format)



FOR EXAMPLE: ABOVE GLOBAL ORDER Y1685 V0001 Q Q 9 R:

TYPE: VFCD1505  
 VALUES: 10K/10K  
 ABSOLUTE TOLERANCE:  $\pm 0.02 \%$   
 TOLERANCE MATCH:  $0.02 \%$   
 TERMINATION: lead (Pb)-free  
 PACKAGING: tape and reel

HISTORICAL PART NUMBER: VFCD1505 10K/10K TCR0.2 Q Q S T (will continue to be used)

<b>VFCD1505</b>	<b>10K/10K</b>	<b>TCR0.2</b>	<b>Q</b>	<b>Q</b>	<b>S</b>	<b>T</b>
MODEL <b>VFCD1505</b>	OHMIC VALUE <b>R<sub>1</sub> = 10 kΩ R<sub>2</sub> = 10 kΩ</b>	TCR CHARACTERISTIC	ABSOLUTE TOLERANCE <b>T = ± 0.01 % Q = ± 0.02 % A = ± 0.05 % B = ± 0.1 % C = ± 0.25 % D = ± 0.5 % F = ± 1.0 %</b>	TOLERANCE MATCH <b>T = 0.01 % Q = 0.02 % A = 0.05 %</b>	TERMINATION <b>S = lead (Pb)-free B = tin/lead alloy</b>	PACKAGING <b>T = tape and reel W = waffle pack</b>

**Notes**

- \* Application engineering release: for non-standard requests, please contact application engineering
- \*\* For examples of VCODES see table 1



## Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.