


TDFN8 2.0 x 2.0 CARRIER TAPE



SECTION A-A

$$A_0 = 2.25 \pm 0.05$$

$$B_0 = 2.25 \pm 0.05$$

$$K_0 = 0.80 \pm 0.05$$

Notes

1. Measured from centerline of sprocket hole to centerline of pocket.
2. Cumulative tolerance of 10 sprocket hole is ± 0.20 mm.
3. Measured from centerline of sprocket hole to centerline of pocket.
4. Other material available. All dimensions in mm unless otherwise stated.
5. Camber can not exceed 1 mm in 100 mm, also can not exceed 1 cm in 1 m actually.
6. Vishay part number must be labeled at all reels of carrier tape.
7. Surface resistivity - 10^5 max. Ω/sq .

ECN: C10-1048-Rev. C, 01-Nov-10
 DWG: 93-5277-X