





CARRIER TAPE FOR MICRO FOOT® 1 mm x 1 mm DIE SIZE



Section A-A

$A_0 = 1.13 \pm 0.05$
 $B_0 = 1.13 \pm 0.05$
 $K_0 = 0.72 \pm 0.05$



Section B-B

Notes

- (1) 10 sprocket hole pitch cumulative tolerance.
- (2) Camber not to exceed 1 mm in 100 mm, also not to exceed 1 cm in 1 m actually.
- (3) Pocket position relative to sprocket hole measured as true position of pocket, not pocket hole.
- (4) Material: black conductive polycarbonate.
- (5) All sizes in mm unless specified.
- (6) Vishay part number must be labeled at all reels of cover and carrier tape.
- (7) Surface resistivity - 10^5 max. Ω /sq.

QUANTITY PER REEL	
T2	3000

ECN: C15-1433-Rev. C, 02-Nov-15 DWG: 93-5265-X
