


# Thick Film Chip Resistors, High Voltage



## FEATURES

- High voltage up to 3000 V
- Outstanding stability < 0.5 %
- Flow solderable
- Custom sizes available
- Automatic placement capability
- Available with either wraparound terminations or as a single termination flip chip
- Tape and reel packaging available
- Internationally standardized sizes
- Suitable for solderable, epoxy bondable, or wire bondable applications
- Termination: Gold, palladium silver, platinum gold, platinum silver, platinum palladium gold or solder-coated nickel barrier available
- Multiple styles, termination materials and configurations, allow wide design flexibility
- Non-magnetic terminations available
- Compliant to RoHS Directive 2002/95/EC
- Halogen-free according to IEC 61249-2-21 definition



Available  
**RoHS\***  
COMPLIANT  
HALOGEN  
**FREE**

### Note

\* Pb containing terminations are not RoHS compliant, exemptions may apply

STANDARD ELECTRICAL SPECIFICATIONS						
GLOBAL MODEL	CASE SIZE	POWER RATING $P_{70^{\circ}\text{C}}$ W	MAXIMUM WORKING VOLTAGE (1) V	RESISTANCE RANGE (2) $\Omega$	TOLERANCE (3) $\pm \%$	TEMPERATURE COEFFICIENT (4) (- 55 °C to + 150 °C) $\pm \text{ppm}/^{\circ}\text{C}$
CRHV1206	1206	0.30	1500	2M to 1G	1, 2, 5, 10, 20	100
				1.1G to 8G	2, 5, 10, 20	
CRHV1210	1210	0.45	1750	4M to 1G	1, 2, 5, 10, 20	100
				1.1G to 10G	2, 5, 10, 20	
CRHV2010	2010	0.50	2000	6M to 1G	1, 2, 5, 10, 20	100
				1.1G to 10G	2, 5, 10, 20	
				11G to 35G	5, 10, 20	
CRHV2510	2510	0.60	2500	10M to 1G	1, 2, 5, 10, 20	100
				1.1G to 10G	2, 5, 10, 20	
				11G to 40G	5, 10, 20	
CRHV2512	2512	0.70	3000	12M to 1G	1, 2, 5, 10, 20	100
				1.1G to 10G	2, 5, 10, 20	
				11G to 50G	5, 10, 20	

### Notes

- For non-standard sizes, lower values or higher power rating requirement, contact factory.
- (1) Continuous working voltage shall be  $\sqrt{P \times R}$  or maximum working voltage, whichever is less.
- (2) Resistance values are calibrated at 100 V<sub>DC</sub>. Calibration at other voltages available upon request.
- (3) Contact factory for tighter tolerances.
- (4) Reference only; Not for all values specified. Consult factory for your size and value.

GLOBAL PART NUMBER INFORMATION																	
New Global Part Numbering: CRHV1206AF100MFKFB (preferred part number format)																	
C	R	H	V	1	2	0	6	A	F	1	0	0	M	F	K	F	B
GLOBAL MODEL	SIZE	TERM STYLE	TERM MATERIAL	RESISTANCE VALUE	TOLERANCE	TCR	SOLDER TERMINATION	PACKAGING									
CRHV	1206 1210 2010 2510 2512	A = 3-sided B = Top only C = 5-sided	F = Nickel barrier A = Palladium silver B = Platinum gold C = Gold D = Platinum silver E = Platinum palladium gold	M = M $\Omega$ G = G $\Omega$ 4M70 = 4.7 M $\Omega$ 10M0 = 10 M $\Omega$ 1G00 = 1 G $\Omega$	F = $\pm 1 \%$ G = $\pm 2 \%$ J = $\pm 5 \%$ K = $\pm 10 \%$ M = $\pm 20 \%$	K = 100 ppm L = 150 ppm N = 200 ppm R = 250 ppm M = 300 ppm W = 350 ppm P = 500 ppm	D = Sn95/Ag5, HSD E = Sn100 F = Sn95/Ag5 N = No solder S = Sn62/Pb36/Ag2, HSD T = Sn90/Pb10	B = Bulk F = T/R (full reel) 1 = T/R (1000 pcs) 5 = T/R (500 pcs) T = T/R (250 pcs min.) W = Waffle									
Historical Part Numbering: CRHV1206AF100F100e2 (will continue to be accepted)																	
CRHV	1206	A	F	1006	F	100	e2										
HISTORICAL MODEL	SIZE	TERM STYLE	TERM MATERIAL	RESISTANCE VALUE	TOLERANCE	TCR	SOLDER TERMINATION										

MECHANICAL SPECIFICATIONS	
Resistive element	Ruthenium oxide
Encapsulation	Glass
Substrate	96 % alumina
Termination	Solder-coated nickel barrier standard. Gold, palladium silver, platinum gold, platinum silver, platinum palladium gold terminations available.
Solder finish	Pure tin or tin/lead solder alloys standard. Tin/silver or tin/lead/silver solder alloys available.




**ENVIRONMENTAL SPECIFICATIONS**
**Operating Temperature:** - 55 °C to + 150 °C


**Life:** Less than 0.5 % change when tested at full rated power

**Short Time Overload:** Less than 0.5 %  $\Delta R$ 

(Reference only: Not for all values specified. Consult factory for your size and value.)

VOLTAGE COEFFICIENT OF RESISTANCE CHART			
SIZE	VALUE ( $\Omega$ )	VCR (ppm/V)	FURTHER INSTRUCTIONS
CRHV1206	2M to 199M	25	Values over 200M, consult factory
CRHV1210	4M to 200M	25	Values over 200M, consult factory
CRHV2010	6M to 99M	15	Values over 1G, consult factory
	100M to 1G	20	
CRHV2510	10M to 99M	10	Values over 1G, consult factory
	100M to 1G	15	
CRHV2512	12M to 999M	10	Values over 5G, consult factory
	1G to 5G	25	

DIMENSIONS in inches (millimeters)				
<b>Termination Style A</b> (3-sided wraparound) 	<b>Termination Style B</b> (Top conductor only) 			
<b>Termination Style C</b> (5-sided wraparound) 	<b>MODEL</b>	<b>LENGTH (L)</b> $\pm 0.006$ (0.152)	<b>WIDTH (W)</b> $\pm 0.006$ (0.152)	<b>THICKNESS (T)</b> $\pm 0.002$ (0.051)
	CRHV1206	0.125	0.063	0.025
	CRHV1210	0.125	0.100	0.025
	CRHV2010	0.200	0.100	0.025
	CRHV2510	0.250	0.100	0.025
	CRHV2512	0.250	0.126	0.025



(Reference only: Not for all values specified. Consult factory for your size and value.)



TYPE	TERMINATION MATERIAL	TERMINATION STYLE	TERMINATION STYLE/ MATERIAL CODE	SOLDER TERMINATION CODE
Solderable	Nickel barrier	3-sided (wraparound)	AF	E or T (standard); D, F or S (optional) <sup>(3)</sup>
		Top only (flip chip)	BF	
Wire bondable/ Solderable	Platinum palladium gold	3-sided (wraparound)	AE	N (standard); D or S (optional) <sup>(1)</sup>
		Top only (flip chip)	BE	
		5-sided (wraparound)	CE	
Wire bondable/ Epoxy bondable	Gold	3-sided (wraparound)	AC	N
		Top only (flip chip)	BC	
		5-sided (wraparound)	CC	
Epoxy bondable	Palladium silver <sup>(2)</sup>	3-sided (wraparound)	AA	N
		Top only (flip chip)	BA	
		5-sided (wraparound)	CA	
	Platinum gold	3-sided (wraparound)	AB	
		Top only (flip chip)	BB	
		5-sided (wraparound)	CB	
	Platinum silver	3-sided (wraparound)	AD	
		Top only (flip chip)	BD	
		5-sided (wraparound)	CD	

**Notes**

- <sup>(1)</sup> Use solder termination N for applications requiring wire bondable mounting, and solder terminations D or S for applications requiring solderable mounting.
- <sup>(2)</sup> While not recommended, palladium silver terminations could be used for solderable applications when using a solder alloy containing silver.
- <sup>(3)</sup> Standard solder plating for the nickel barrier parts are solder terminations E or T. Plated termination F and hot solder dipped terminations D or S are also available.



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.