



Si5933CDC vs. Si5933DC

Description: Dual N-Channel 20-V (D-S) MOSFET

Package: 1206-8 ChipFET®

Pin Out: Identical

Part Number Replacements: Si5933CDC-T1-E3 replaces Si5933DC-T1-E3
Si5933CDC-T1-E3 replaces Si5933DC-T1

ABSOLUTE MAXIMUM RATINGS $T_A = 25\text{ }^\circ\text{C}$, unless otherwise noted				
PARAMETER	SYMBOL	Si5933CDC	Si5933DC	UNIT
Drain-Source Voltage	V_{DS}	- 20	- 20	V
Gate-Source Voltage	V_{GS}	± 8	± 8	
Continuous Drain Current	$T_A = 25\text{ }^\circ\text{C}$	- 2.5	- 3.6	A
	$T_A = 70\text{ }^\circ\text{C}$	- 2.0	- 2.6 ^a	
Pulsed Drain Current	I_{DM}	- 10	- 10	
Continuous Source Current (MOSFET Diode Conduction)	I_S	- 1.1	- 1.8	
Power Dissipation	$T_A = 25\text{ }^\circ\text{C}$	1.3	2.1	W
	$T_A = 70\text{ }^\circ\text{C}$	0.8	1.1 ^a	
Operating Junction and Storage Temperature Range	T_J and T_{stg}	- 55 to 150	- 55 to 150	$^\circ\text{C}$
Maximum Junction-to-Ambient	R_{thJA}	99	50	$^\circ\text{C/W}$

Note

a. T_A for Si5933DC is 85 $^\circ\text{C}$.

SPECIFICATIONS $T_J = 25\text{ }^\circ\text{C}$, unless otherwise noted								
PARAMETER	SYMBOL	Si5933CDC			Si5933DC			UNIT
		MIN.	TYP.	MAX.	MIN.	TYP.	MAX.	
Static								
Gate-Threshold Voltage	$V_{GS(th)}$	- 0.45		- 1.0	- 0.45		- 1.0	V
Gate-Body Leakage	I_{GSS}			± 100			± 100	nA
Zero Gate Voltage Drain Current	I_{DSS}			- 1			- 1	μA
On-State Drain Current	$V_{GS} = - 4.5\text{ V}$ $I_{D(on)}$	- 10			- 10			A
Drain-Source On-Resistance	$V_{GS} = - 4.5\text{ V}$		0.120	0.144		0.095	0.110	Ω
	$V_{GS} = - 2.5\text{ V}$		0.150	0.180		0.137	0.160	
	$V_{GS} = - 1.8\text{ V}$		0.185	0.222		0.205	0.240	
Forward Transconductance	g_{fs}		18			7		S
Diode Forward Voltage	V_{SD}		- 0.8	- 1.2		- 0.8	- 1.2	V
Dynamic								
Total Charge	Q_g		4.1	6.2		5.1	7.7	nC
Gate-Source Charge	Q_{gs}		0.6			1.2		
Gate-Drain Charge	Q_{gd}		1.0			1.0		
Gate Resistance	R_g		5.5			NS		

Note

NS denotes not specified in original datasheet

Specification comparisons are supplied as a courtesy to compare two devices and do not constitute a commercial product datasheet or any guarantee of identical performance. Designers should refer to the appropriate datasheets of the same number for guaranteed specification limits.