




## PowerPAIR® 6 x 3.7 Carrier Tape



$A_0 = 6.35$   
 $B_0 = 4.03$   
 $K_0 = 1.30$

### Notes

- (1) 10 sprocket hole pitch cumulative tolerance  $\pm 0.2$  mm.
- (2) Camber not to exceed 1 mm in 100 mm, also not to exceed 1.5 cm in 1 m actually.
- (3) Pocket position relative to sprocket hole measured as true position of pocket, not pocket hole.
- (4) Material: PS and C.
- (5) Tolerance will be  $\pm 0.1$  mm unless specified.
- (6) Vishay part number must be labeled at all reels of cover and carrier tape.
- (7) Surface resistivity:  $10^4$  to  $10^{11}$   $\Omega$ .

QUANTITY PER REEL	
T1	3000

ECN: C15-1433-Rev. E, 02-Nov-15  
 DWG: 93-5264-X