

Quad SPST CMOS Analog Switches

APPLICATIONS

- Audio switching
- Battery powered systems
- Data acquisition
- Sample-and-hold circuits
- Telecommunication systems
- Automatic test equipment
- Single supply circuits
- Hard disk drives


DESCRIPTION

The DG444, DG445 monolithic quad analog switches are designed to provide high speed, low error switching of analog signals. The DG444 has a normally closed function. The DG445 has a normally open function. Combining low power (22 nW, typ.) with high speed (t_{ON} : 120 ns, typ.), the DG444, DG445 are ideally suited for upgrading DG211, DG212 sockets. Charge injection has been minimized on the drain for use in sample-and-hold circuits.

To achieve high-voltage ratings and superior switching performance, the DG444, DG445 are built on Vishay Siliconix's high-voltage silicon-gate process. An epitaxial layer prevents latchup.

Each switch conducts equally well in both directions when on, and blocks input voltages to the supply levels when off.

FUNCTIONAL BLOCK DIAGRAM AND PIN CONFIGURATION



FEATURES

- Low on-resistance: 50 Ω
- Low leakage: 80 pA
- Low power consumption: 22 nW
- Fast switching action - t_{ON} : 120 ns
- Low charge injection
- DG211, DG212 upgrades
- TTL/CMOS logic compatible

BENEFITS

- Low signal errors and distortion
- Reduced power supply requirements
- Faster throughput
- Improved reliability
- Reduced pedestal errors
- Simple interfacing
- Wide supply ranges
 - Single supply: +5 V to 36 V
 - Dual supplies: ± 5 V to ± 20 V

TRUTH TABLE

| LOGIC | DG444 | DG445 |
|-------|-------|-------|
| 0 | On | Off |
| 1 | Off | On |

Note

- Logic "0" ≤ 0.8 V
- Logic "1" ≥ 2.4 V

ORDERING INFORMATION

| TEMP. RANGE | PACKAGE | PART NUMBER |
|-----------------|--------------------|-------------|
| -40 °C to 85 °C | 16-pin plastic DIP | DG444DJ |
| | | DG445DJ |
| | 16-pin narrow SOIC | DG444DY |
| | | DG445DY |



| ABSOLUTE MAXIMUM RATINGS (T _A = 25 °C, unless otherwise noted) | | | |
|---|--|-----|------|
| PARAMETER | LIMIT | | UNIT |
| V ₊ to V ₋ | 44 | | V |
| GND to V ₋ | 25 | | |
| V _L | (GND - 0.3) to (V ₊) +0.3 | | |
| Digital Inputs ^a , V _S , V _D | (V ₋) -2 to (V ₊) +2 or 30 mA, whichever occurs first | | |
| Continuous Current (Any Terminal) | 30 | | mA |
| Current, S or D (Pulsed at 1 ms, 10 % Duty Cycle) | 100 | | |
| Storage Temperature | -65 to 125 | | °C |
| Power Dissipation (Package) ^b | 16-Pin Plastic DIP ^c | 450 | mW |
| | 16-Pin Narrow Body SOIC ^d | 640 | |

Notes

- a. Signals on S_X, D_X, or IN_X exceeding V₊ or V₋ will be clamped by internal diodes. Limit forward diode current to maximum current ratings.
- b. All leads welded or soldered to PC board.
- c. Derate 6 mW/°C above 75 °C.
- d. Derate 8 mW/°C above 75 °C.

| SPECIFICATIONS for Dual Supplies | | | | | | | | |
|---|---------------------|---|---------------------------|-----------------------------|-------------------|-------------------|------|-----|
| PARAMETER | SYMBOL | TEST CONDITIONS UNLESS OTHERWISE SPECIFIED V ₊ = 15 V, V ₋ = -15 V V _L = 5 V, V _{IN} = 2.4 V, 0.8 V ^e | TEMP. ^a | D SUFFIX -40 °C TO 85 °C | | | UNIT | |
| | | | | MIN. ^b | TYP. ^c | MAX. ^b | | |
| Analog Switch | | | | | | | | |
| Analog Signal Range ^d | V _{ANALOG} | | Full | -15 | - | 15 | V | |
| Drain-Source On-Resistanc ^e | R _{DS(on)} | I _S = -10 mA, V _D = ± 8.5 V V ₊ = 13.5 V, V ₋ = -13.5 V | Room | - | 50 | 85 | Ω | |
| | | | Full | - | - | 100 | | |
| Switch Off Leakage Current | I _{S(off)} | V ₊ = 16.5 V, V ₋ = -16.5 V V _D = ± 15.5 V, V _S = ± 15.5 V | Room | -0.5 | ± 0.01 | 0.5 | nA | |
| | | | Full | -5 | ± 0.01 | 5 | | |
| | Room | | -0.5 | ± 0.01 | 0.5 | | | |
| | Full | | -5 | ± 0.01 | 5 | | | |
| Channel On Leakage Current | I _{D(on)} | V ₊ = 16.5 V, V ₋ = -16.5 V V _S = V _D = ± 15.5 V | Room | -0.5 | ± 0.08 | 0.5 | | |
| | | | Full | -10 | ± 0.08 | 10 | | |
| Digital Control | | | | | | | | |
| Input Current V _{IN} Low | I _{IL} | V _{IN} under test = 0.8 V All Other = 2.4 V | Full | -500 | -0.01 | 500 | nA | |
| Input Current V _{IN} High | I _{IH} | V _{IN} under test = 2.4 V All Other = 0.8 V | Full | -500 | 0.01 | 500 | | |
| Dynamic Characteristics | | | | | | | | |
| Turn-On Time | t _{ON} | R _L = 1 kΩ, C _L = 35 pF V _S = ± 10 V, See Figure 2 | Room | - | 120 | 250 | ns | |
| Turn-Off Time | t _{OFF} | | DG444 | Room | - | 110 | | 140 |
| | | | DG445 | Room | - | 160 | | 210 |
| Charge Injection ^e | Q | C _L = 1 nF, V _S = 0 V V _{gen} = 0 V, R _{gen} = 0 Ω | Room | - | -1 | - | pC | |
| Off Isolation ^e | OIRR | R _L = 50 Ω, C _L = 5 pF, f = 1 MHz | Room | - | 60 | - | dB | |
| Crosstalk (Channel-to-Channel) ^d | X _{TALK} | | Room | - | 100 | - | | |
| Source Off Capacitance | C _{S(off)} | f = 1 MHz | Room | - | 4 | - | pF | |
| Drain Off Capacitance | C _{D(off)} | | Room | - | 4 | - | | |
| Channel On Capacitance | C _{D(on)} | | V _{ANALOG} = 0 V | Room | - | 16 | | - |



| SPECIFICATIONS for Dual Supplies | | | | | | | |
|----------------------------------|------------------|--|--------------------|-----------------------------|-------------------|-------------------|------|
| PARAMETER | SYMBOL | TEST CONDITIONS UNLESS OTHERWISE SPECIFIED $V_+ = 15\text{ V}$, $V_- = -15\text{ V}$ $V_L = 5\text{ V}$, $V_{IN} = 2.4\text{ V}$, 0.8 V^e | TEMP. ^a | D SUFFIX -40 °C TO 85 °C | | | UNIT |
| | | | | MIN. ^b | TYP. ^c | MAX. ^b | |
| Power Supplies | | | | | | | |
| Positive Supply Current | I ₊ | $V_+ = 16.5\text{ V}$, $V_- = -16.5\text{ V}$ $V_{IN} = 0\text{ V}$ or 5 V | Room | - | 0.001 | 1 | μA |
| | | | Full | - | - | 5 | |
| Negative Supply Current | I ₋ | | Room | -1 | -0.0001 | - | |
| | | | Full | -5 | - | - | |
| Logic Supply Current | I _L | | Room | - | 0.001 | 1 | |
| | | | Full | - | 0.001 | 5 | |
| Ground Current | I _{GND} | | Room | -1 | -0.001 | - | |
| | | | Full | -5 | -0.001 | - | |

| SPECIFICATIONS for Unipolar Supplies | | | | | | | |
|---|---------------------|--|--------------------|---------------------------|-------------------|-------------------|------|
| PARAMETER | SYMBOL | TEST CONDITIONS UNLESS OTHERWISE SPECIFIED $V_+ = 12\text{ V}$, $V_- = 0\text{ V}$ $V_L = 5\text{ V}$, $V_{IN} = 2.4\text{ V}$, 0.8 V^e | TEMP. ^a | LIMITS -40 °C TO 85 °C | | | UNIT |
| | | | | MIN. ^b | TYP. ^c | MAX. ^b | |
| Analog Switch | | | | | | | |
| Analog Signal Range ^d | V _{ANALOG} | | Full | 0 | - | 12 | V |
| Drain-Source On-Resistance ^d | R _{DS(on)} | $I_S = -10\text{ mA}$, $V_D = 3\text{ V}$, 8 V $V_+ = 10.8\text{ V}$, $V_L = 5.25\text{ V}$ | Room | - | 100 | 160 | Ω |
| | | | Full | - | - | 200 | |
| Dynamic Characteristics | | | | | | | |
| Turn-On Time | t _{ON} | $R_L = 1\text{ k}\Omega$, $C_L = 35\text{ pF}$, $V_S = 8\text{ V}$ See Figure 2 | Room | - | 300 | 450 | ns |
| Turn-Off Time | t _{OFF} | | Room | - | 60 | 200 | |
| Charge Injection | Q | $C_L = 1\text{ nF}$, $V_{gen} = 6\text{ V}$, $R_{gen} = 0\text{ }\Omega$ | Room | - | 2 | - | pC |
| Power Supplies | | | | | | | |
| Positive Supply Current | I ₊ | $V_+ = 13.2\text{ V}$, $V_{IN} = 0\text{ V}$ or 5 V | Room | - | 0.001 | 1 | μA |
| | | | Full | - | - | 5 | |
| Negative Supply Current | I ₋ | | Room | -1 | -0.0001 | - | |
| | | | Full | -5 | - | - | |
| Logic Supply Current | I _L | | Room | - | 0.001 | 1 | |
| | | | Full | - | - | 5 | |
| Ground Current | I _{GND} | | Room | -1 | -0.001 | - | |
| | | | Full | -5 | - | - | |


Notes

- a. Room = 25 °C, Full = as determined by the operating temperature suffix.
- b. The algebraic convention whereby the most negative value is a minimum and the most positive a maximum, is used in this datasheet.
- c. Typical values are for DESIGN AID ONLY, not guaranteed nor subject to production testing.
- d. Guaranteed by design, not subject to production test.
- e. V_{IN} = input voltage to perform proper function.


Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.




TYPICAL CHARACTERISTICS ($T_A = 25\text{ }^\circ\text{C}$, unless otherwise noted)




$R_{DS(on)}$ vs. V_D and Temperature




Crosstalk and Off Isolation vs. Frequency




Charge Injection vs. Source Voltage



Switching Threshold vs. Supply Voltage




Source/Drain Leakage Currents




Source/Drain Leakage Currents (Single 12-V Supply)




TYPICAL CHARACTERISTICS (T_A = 25 °C, unless otherwise noted)




Switching Time vs. Power Supply Voltage




Switching Times vs. Power Supply Voltage



Supply Current vs. Temperature



Source/Drain Capacitance vs. Analog Voltage



Switching Time vs. Input Voltage

SCHEMATIC DIAGRAM TYPICAL CHANNEL






Fig. 1

TEST CIRCUITS



C_L (includes fixture and stray capacitance)



Note: Logic input waveform is inverted for DG445.

Fig. 2 - Switching Time





Fig. 3 - Charge Injection

TEST CIRCUITS




Fig. 4 - Crosstalk




Fig. 5 - Off Isolation




Fig. 6 - Source/Drain Capacitances

APPLICATIONS




Fig. 7 - Level Shifter

APPLICATIONS




Fig. 8 - Precision-Weighted Resistor Programmable-Gain Amplifier




Fig. 9 - Precision Sample-and-Hold

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see www.vishay.com/ppg?70054.



SOIC (NARROW): 16-LEAD
JEDEC Part Number: MS-012



| Dim | MILLIMETERS | | INCHES | |
|----------------|-------------|-------|-----------|-------|
| | Min | Max | Min | Max |
| A | 1.35 | 1.75 | 0.053 | 0.069 |
| A ₁ | 0.10 | 0.20 | 0.004 | 0.008 |
| B | 0.38 | 0.51 | 0.015 | 0.020 |
| C | 0.18 | 0.23 | 0.007 | 0.009 |
| D | 9.80 | 10.00 | 0.385 | 0.393 |
| E | 3.80 | 4.00 | 0.149 | 0.157 |
| e | 1.27 BSC | | 0.050 BSC | |
| H | 5.80 | 6.20 | 0.228 | 0.244 |
| L | 0.50 | 0.93 | 0.020 | 0.037 |
| ∅ | 0° | 8° | 0° | 8° |

ECN: S-03946—Rev. F, 09-Jul-01
DWG: 5300



PDIP: 16-LEAD



| Dim | MILLIMETERS | | INCHES | |
|----------------------|-------------|-------|--------|-------|
| | Min | Max | Min | Max |
| A | 3.81 | 5.08 | 0.150 | 0.200 |
| A₁ | 0.38 | 1.27 | 0.015 | 0.050 |
| B | 0.38 | 0.51 | 0.015 | 0.020 |
| B₁ | 0.89 | 1.65 | 0.035 | 0.065 |
| C | 0.20 | 0.30 | 0.008 | 0.012 |
| D | 18.93 | 21.33 | 0.745 | 0.840 |
| E | 7.62 | 8.26 | 0.300 | 0.325 |
| E₁ | 5.59 | 7.11 | 0.220 | 0.280 |
| e₁ | 2.29 | 2.79 | 0.090 | 0.110 |
| e_A | 7.37 | 7.87 | 0.290 | 0.310 |
| L | 2.79 | 3.81 | 0.110 | 0.150 |
| Q₁ | 1.27 | 2.03 | 0.050 | 0.080 |
| S | 0.38 | 1.52 | .015 | 0.060 |

ECN: S-03946—Rev. D, 09-Jul-01
DWG: 5482

RECOMMENDED MINIMUM PADS FOR SO-16



Recommended Minimum Pads
Dimensions in Inches/(mm)

[Return to Index](#)



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.