


TO-252AA CASE OUTLINE



DIM.	MILLIMETERS		INCHES	
	MIN.	MAX.	MIN.	MAX.
A	2.21	2.38	0.087	0.094
A1	0.89	1.14	0.035	0.045
A2	0.030	0.127	0.001	0.005
b	0.71	0.88	0.028	0.035
b1	0.76	1.14	0.030	0.045
b2	5.23	5.44	0.206	0.214
C	0.46	0.58	0.018	0.023
C1	0.46	0.58	0.018	0.023
D	5.97	6.22	0.235	0.245
D1	4.10	4.45	0.161	0.175
E	6.48	6.73	0.255	0.265
E1	4.49	5.50	0.177	0.217
e	2.28 BSC		0.090 BSC	
e1	4.57 BSC		0.180 BSC	
H	9.65	10.41	0.380	0.410
L	1.40	1.78	0.055	0.070
L1	0.64	1.02	0.025	0.040
L2	0.89	1.27	0.035	0.050
L3	1.15	1.52	0.040	0.060
ECN: T11-0110-Rev. L, 18-Apr-11 DWG: 5347				

Note

- Dimension L3 is for reference only.