


SC-70: 5- AND 6-LEADS (T1 AND T3 METHODS)



Notes

1. 10 sprocket hole pitch cumulative tolerance ± 0.2 mm.
2. Camber not to exceed 1 mm in 100 mm, also not to exceed 1.5 cm in 1 m actually.
3. Material: Black conductive or black static dissipative.
4. Should be measured from: a) sprocket hole to sprocket center, and, b) sprocket hole to pocket hole.
5. All size in mm unless specified.
6. Tolerances will be ± 0.1 mm unless specified.
7. Vishay part number must be labeled at all reels of carrier tape.
8. Surface resistivity - 10^5 max. Ω/sq .

| QUANTITY PER REEL | |
|--|--------|
| T1 | 3000 |
| T3* | 10 000 |
| * Not standard offering. Please contact local sales office for availability. | |
| ECN: C10-0946-Rev. I, 04-Oct-10 | |
| DWG: 93-5213-X | |