


TSSOP-14, 16/PowerPAK TSSOP-16



A_0	=	$6.8 \text{ mm} \pm 0.1$
B_0	=	$5.4 \text{ mm} \pm 0.1$
K_0	=	$1.6 \text{ mm} \pm 0.1$
K_1	=	$1.3 \text{ mm} \pm 0.1$

Notes

- 10 sprocket hole pitch cumulative tolerance ± 0.2 .
- Camber not to exceed 1 mm in 100 mm.
- Material: static dissipative black advantek polystyrene.
- A_0 and B_0 measured on a plane 0.3 mm above the bottom of the pocket.
- K_0 measured from a plane on the inside bottom of the pocket to the top surface of the carrier.
- Pocket position relative to sprocket hole measured as true position of pocket, not pocket hole.
- All size in mm unless specific.
- Reel length: 101 m.

QUANTITY PER REEL

3000

ECN: S-80229-Rev. F, 11-Feb-08

DWG: 90-2347-x