


PowerPAIR 6 x 5 CARRIER TAPE



SECTION A - A

$$A_0 = 6.35$$

$$B_0 = 5.35$$

$$K_0 = 1.30$$

Notes

1. 10 sprocket hole pitch cumulative tolerance ± 0.2 mm.
2. Camber not to exceed 1 mm in 100 mm, also not to exceed 1.5 cm in 1 m actually.
3. Pocket position relative to sprocket hole measured as true position of pocket, not pocket hole.
4. Material: PS and C.
5. Tolerance will be ± 0.1 mm unless specified.
6. Vishay part number must be labeled at all reels of cover and carrier tape.
7. Surface resistivity - 10^5 max. Ω/sq .

ECN: C10-0947-Rev. C, 18-Oct-10
 DWG: 93-5263-X