


**MICRO FOOT® 5 x 2: 0.8 mm PITCH, 0.275 mm BUMP HEIGHT  
(Si8900EDB-T2)**



**Notes**

1. 10 sprocket hole pitch cumulative tolerance  $\pm 0.2$ .
2. Camber not to exceed 1 mm in 100 mm, also not to exceed 1 cm in 1 m actually.
3. Material: Black conductive or static dissipative polycarbonate.
4. Pocket position relative to sprocket hole measured as true position of pocket, not pocket hole.
5. All sizes in mm unless specified.
6. Use 7" lok reel with 12.4 mm width, (see rows 2 and 7, drawing of 93-5211-X).
7. Use seal tape with 9.3 mm width, (see row 7 of drawing of 92-5210-X).
6. Vishay part number must be labeled at all reels of cover and carrier tape.
7. Surface resistivity -  $10^5$  max.  $\Omega/\text{sq}$ .

Version	Reel Dia.	Length
- 1	178 mm	14 m approv.

QUANTITY PER REEL	
T2	3000
ECN C10-0948-Rev. D, 11-Oct-10 DWG: 93-5224-X	