


PowerPAK®
MLP(QFN), 4 x 4/3 x 3
DFN-10, 3 x 3
MLP33-8/10
PPAIR® 3 x 3



Notes

1. 10 sprocket hole pitch cumulative tolerance ± 0.2 mm.
2. Camber not to exceed 1 mm in 100 mm, also not to exceed 1.5 cm in 1 m actually.
3. Material: Black conductive or black static dissipative
4. It should be measured from:
 - a. sprocket hole to pocket center and
 - b. sprocket hole to pocket hole
5. All sizes in mm unless specified.
6. Tolerances will be ± 0.1 mm unless specified.
7. Vishay part number must be labeled at all reels of cover and carrier tape.
8. Surface resistivity - 10^5 max. Ω/sq .

Version	Package	B ₀
- 1	MLP(QFN), 4 x 4	4.35 \pm 0.1
- 2	MLP(QFN), 3 x 3	3.30 \pm 0.1
	MLP33-8/10	
	DFN-10, 3 x 3	
	PPAIR, 3 x 3	
ECN T11-0383-Rev. I, 29-Aug-11 DWG: 93-5225-X		

Quantity per Reel	
T1	2500
T1	3000 for MLP33-8/10 and PPAIR 3 x 3