



Si4435BDY vs. Si4435DY-REVA

Description: P-Channel, 30 V (D-S) MOSFET

Package: SOIC-8

Pin Out: Identical

Part Number Replacements:

Si4435BDY Replaces Si4435DY-REVA

Si4435BDY-E3 (Lead (Pb)-free version) Replaces Si4435DY-REVA

Si4435BDY-T1 Replaces Si4435DY-T1-REVA

Si4435BDY-T1-E3 (Lead (Pb)-free version) Replaces Si4435DY-T1-REVA

ABSOLUTE MAXIMUM RATINGS $T_A = 25\text{ }^\circ\text{C}$, unless otherwise noted				
Parameter	Symbol	Si4435BDY	Si4435DY-REVA	Unit
Drain-Source Voltage	V_{DS}	- 30	- 30	V
Gate-Source Voltage	V_{GS}	± 20	± 20	
Continuous Drain Current	$T_A = 25\text{ }^\circ\text{C}$	- 9.1	- 8.0	A
	$T_A = 70\text{ }^\circ\text{C}$	- 7.3	- 6.4	
Pulsed Drain Current	I_{DM}	- 50	- 50	
Continuous Source Current (MOSFET Diode Conduction)	I_S	- 2.1	- 2.1	
Power Dissipation	$T_A = 25\text{ }^\circ\text{C}$	2.5	2.5	W
	$T_A = 70\text{ }^\circ\text{C}$	1.6	1.6	
Operating Junction and Storage Temperature Range	T_J and T_{stg}	- 55 to 150	- 55 to 150	$^\circ\text{C}$
Maximum Junction-to-Ambient	R_{thJA}	50	50	$^\circ\text{C/W}$

SPECIFICATIONS $T_J = 25\text{ }^\circ\text{C}$, unless otherwise noted								
Parameter	Symbol	Si4435BDY			Si4435DY-REVA			Unit
		Min	Typ	Max	Min	Typ	Max	
Static								
Gate-Threshold Voltage	$V_{G(th)}$	- 1.0		- 3.0	- 1.0			V
Gate-Body Leakage	I_{GSS}			± 100			± 100	nA
Zero Gate Voltage Drain Current	I_{DSS}			- 1			- 1	μA
On-State Drain Current	$V_{GS} = - 10\text{ V}$	$I_{D(on)}$	- 40		- 40			A
	$V_{GS} = - 4.5\text{ V}$				- 10			
Drain-Source On-Resistance	$V_{GS} = - 10\text{ V}$	$r_{DS(on)}$	0.015	0.020	0.015	0.02		Ω
	$V_{GS} = - 4.5\text{ V}$		0.025	0.035	0.022	0.035		
Forward Transconductance	g_{fs}		24			20		S
Diode Forward Voltage	V_{SD}		- 0.8	- 1.2		- 0.75	- 1.2	V
Dynamic								
Total Gate Charge	Q_g		33	70		47	60	nC
Gate-Source Charge	Q_{gs}		5.8			9.5		
Gate-Drain Charge	Q_{gd}		8.6			8		
Switching								
Turn-On Time	$t_{d(on)}$		10	15		16	30	ns
	t_r		15	25		17	30	
Turn-Off Time	$t_{d(off)}$		110	170		75	120	
	t_f		70	110		31	80	
Source-Drain Reverse Recovery Time	t_{rr}		60	90		40	80	

Specification comparisons are supplied as a courtesy to compare two devices and do not constitute a commercial product datasheet or any guarantee of identical performance. Designers should refer to the appropriate datasheets of the same number for guaranteed specification limits.