


1206-8 ChipFET®



Notes

1. 10 sprocket hole pitch cumulative tolerance ± 0.2 .
2. Camber not to exceed 1 mm in 100 mm, also not to exceed 1.5 cm in 1 m actually.
3. Material: Black conductive or black static dissipative.
4. It should be measured from:
 - a. sprocket hole to pocket center and
 - b. sprocket hole to pocket hole
5. All sizes in mm unless specified.
6. Tolerances will be ± 0.1 mm unless specified.
7. Vishay part number must be labeled at all reels of carrier tape.
8. Surface resistivity - 10^5 max. Ω/sq .

QUANTITY PER REEL	
T1	3000
ECN: C10-0945-Rev. I, 04-Oct-10 DWG: 93-2346-X	