



N-CHANNEL ACCELERATED OPERATING LIFE TEST RESULT	
Sample Size	46 819
Equivalent Device Hours	23 453 206 587
Failure Rate in FIT	1.109

Failure Rate in FIT is calculated according to JEDEC Standard JESD85, *Methods for Calculating Failure Rates in Units of FITs*, based on accelerated high temperature operating life test results by using an apparent activation energy of 0.7 eV. The junction temperature of the device at use is assumed to be 55 °C. A constant failure rate distribution is assumed. The upper confidence bound of the failure rate is 60 %.