



## Si4948BEY vs. Si4948EY

**Description:** Dual P-Channel, 60 V (D-S) MOSFET

**Package:** SO-8

**Pin Out:** Identical

**Part Number Replacements:**

Si4948BEY-T1-E3 Replaces Si4948EY-T1-E3

Si4948BEY-T1-E3 Replaces Si4948EY-T1

<b>ABSOLUTE MAXIMUM RATINGS</b> $T_A = 25\text{ }^\circ\text{C}$ , unless otherwise noted				
Parameter	Symbol	Si4948BEY	Si4948EY	Unit
Drain-Source Voltage	$V_{DS}$	- 60	- 60	V
Gate-Source Voltage	$V_{GS}$	$\pm 20$	$\pm 20$	
Continuous Drain Current	$T_A = 25\text{ }^\circ\text{C}$	$I_D$	- 3.1	A
	$T_A = 70\text{ }^\circ\text{C}$		- 2.6	
Pulsed Drain Current	$I_{DM}$	- 25	- 30	
Continuous Source Current (MOSFET Diode Conduction)	$I_S$	- 2	- 2	
Power Dissipation	$T_A = 25\text{ }^\circ\text{C}$	$P_D$	15	W
	$T_A = 70\text{ }^\circ\text{C}$		1.7	
Operating Junction and Storage Temperature Range	$T_j$ and $T_{stg}$	- 55 to 175	- 55 to 175	$^\circ\text{C}$
Maximum Junction-to-Ambient	$R_{thJA}$	62.5	62.5	$^\circ\text{C/W}$

<b>SPECIFICATIONS</b> $T_J = 25\text{ }^\circ\text{C}$ , unless otherwise noted								
Parameter	Symbol	Si4948BEY			Si4948EY			Unit
		Min	Typ	Max	Min	Typ	Max	
<b>Static</b>								
Gate-Threshold Voltage	$V_{GS(th)}$	- 1.0		- 3.0	- 1.0		NS	V
Gate-Body Leakage	$I_{GSS}$			$\pm 100$			$\pm 100$	nA
Zero Gate Voltage Drain Current	$I_{DSS}$			- 1			- 1	$\mu\text{A}$
On-State Drain Current	$V_{GS} = - 10\text{ V}$	$I_{D(on)}$	- 25		- 20			A
Drain-Source On-Resistance	$V_{GS} = - 10\text{ V}$	$r_{DS(on)}$	0.100	0.120	0.100	0.120		$\Omega$
	$V_{GS} = - 4.5\text{ V}$		0.126	0.150	0.125	0.150		
Forward Transconductance		$g_{fs}$	8.5		7.5			S
Diode Forward Voltage		$V_{SD}$	- 0.8	- 1.2	- 0.8	- 1.2		V
<b>Dynamic</b>								
Total Gate Charge		$Q_g$	14.5	22	16	25		nC
Gate-Source Charge		$Q_{gs}$	2.2		4			
Gate-Drain Charge		$Q_{gd}$	3.7		1.6			
Gate Resistance		$R_g$	14		NS			$\Omega$
<b>Switching</b>								
Turn-On Time*		$t_{d(on)}$	10	15	8	15		ns
		$t_r$	15	22	10	20		
Turn-Off Time*		$t_{d(off)}$	50	75	35	50		
		$t_f$	35	55	12	25		
Source-Drain Reverse Recovery Time		$t_{rr}$	30	50	60	90		

NS denotes not specified in original data sheet.

Specification comparisons are supplied as a courtesy to compare two devices and do not constitute a commercial product datasheet or any guarantee of identical performance. Designers should refer to the appropriate datasheets of the same number for guaranteed specification limits.