SUP45P03-09



Vishay Siliconix

P-Channel 30 V (D-S) MOSFET

PRODUCT SUMMARY				
V _{DS} (V)	R _{DS(on)} (Ω) MAX.	I _D (A) ^d	Q _g (TYP.)	
-30	0.0087 at V _{GS} = -10 V	-45	60	
	0.0150 at V_{GS} = -4.5 V	-45	00	




FEATURES

- TrenchFET® power MOSFET
- 100 % R_g and UIS tested
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

APPLICATIONS

- Power switch
- Load switch in high current applications
- DC/DC converters
- DC/DC converters



RoHS COMPLIANT

HALOGEN

FREE

S

P-Channel MOSFET

Ordering Information:

SUP45P03-09-GE3 (lead (Pb)-free and halogen-free)

ABSOLUTE MAXIMUM RATINGS (To	$_{\rm C}$ = 25 °C, unless otherv	vise noted)			
PARAMETER	SYMBOL	LIMIT	UNIT		
Drain-Source Voltage		V _{DS}	-30	N	
Gate-Source Voltage		V _{GS}	± 20	V	
Continuous Drain Current (T ₁ = 150 °C) ^d	T _C = 25 °C	1-	-45		
Continuous Drain Current (1j = 150°C) °	T _C = 70 °C	Ι _D	-45		
Pulsed Drain Current (t = 100 µs)		I _{DM}	-100	A	
Avalanche Current	L = 0.1 mH	I _{AS}	-35		
Single Avalanche Energy ^a		E _{AS}	61	mJ	
Maximum Power Dissipation ^a	T _C = 25 °C	PD	73.5 ^b	W	
Maximum rower Dissipation ~	T _A = 25 °C °	гD	3.1	vv	
Operating Junction and Storage Temperature Range		T _J , T _{stg}	-55 to +150	°C	

THERMAL RESISTANCE RATINGS			
PARAMETER	SYMBOL	LIMIT	UNIT
Junction-to-Ambient (PCB Mount) ^c	R _{thJA}	40	°C/W
Junction-to-Case (Drain)	R _{thJC}	1.7	0/10

Notes

- a. Duty cycle \leq 1 %.
- b. See SOA curve for voltage derating.
- c. When mounted on 1" square PCB (FR4 material).

d. Package limited.

1

SUP45P03-09



www.vishay.com

Vishay Siliconix

PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNIT
Static						
Drain-Source Breakdown Voltage	V _{DS}	$V_{GS} = 0 V, I_D = -250 \mu A$	-30	-	-	V
Gate Threshold Voltage	V _{GS(th)}	$V_{DS} = V_{GS}$, $I_D = -250 \ \mu A$	-1	-	-2.5	V
Gate-Body Leakage	I _{GSS}	$V_{DS} = 0 V, V_{GS} = \pm 20 V$	-	-	± 250	nA
		V_{DS} = -30 V, V_{GS} = 0 V	-	-	-1	μA
Zero Gate Voltage Drain Current	I _{DSS}	V_{DS} = -30 V, V_{GS} = 0 V, T_J = 125 °C	-	-	-50	
		V_{DS} = -30 V, V_{GS} = 0 V, T_{J} = 150 °C	-	-	-250	
On-State Drain Current ^a	I _{D(on)}	$V_{DS}\!\leq$ -10 V, $V_{GS}\!=$ -10 V	-50	-	-	А
Drain-Source On-State Resistance a	P	$V_{GS} = -10 \text{ V}, \text{ I}_{D} = -20 \text{ A}$	-	0.0072	0.0087	0
Drain-Source On-State Resistance ~	R _{DS(on)}	$V_{GS} = -4.5 \text{ V}, \text{ I}_{D} = -15 \text{ A}$	-	0.0125	0.0150	Ω
Forward Transconductance ^a	g fs	$V_{DS} = -15 \text{ V}, \text{ I}_{D} = -20 \text{ A}$	-	45	-	S
Dynamic ^b						
Input Capacitance	C _{iss}		-	2700	-	pF
Output Capacitance	Coss	$V_{GS} = 0 V, V_{DS} = -15 V, f = 1 MHz$	-	515	-	
Reverse Transfer Capacitance	C _{rss}		-	445	-	
Total Gate Charge ^c	Qg		-	60	90	nC
Gate-Source Charge ^c	Q _{gs}	V_{DS} = -15 V, V_{GS} = -10 V, I_{D} = -20 A	-	9.3	-	
Gate-Drain Charge ^c	Q _{gd}		-	15	-	
Gate Resistance	Rg	f = 1 MHz	0.5	2.5	5	Ω
Turn-On Delay Time ^c	t _{d(on)}		-	12	20	
Rise Time ^c	t _r	$V_{DD} = -15 \text{ V}, \text{ R}_{\text{L}} = 1.5 \Omega$	-	11	20	
Turn-Off Delay Time ^c	t _{d(off)}	$I_D \cong -10$ A, $V_{GEN} = -10$ V, $R_g = 1 \Omega$	-	40	60	- ns
Fall Time ^c	t _f		-	12	20	
Drain-Source Body Diode Ratings a	nd Characteri	stics ^b (T _C = 25 °C)				
Continuous Current	ا _S		-	-	-45	
Pulsed Current (t = 100 µs)	I _{SM}		-	-	-100	A
Forward Voltage ^a	V _{SD}	$I_F = -10 \text{ A}, \text{ V}_{GS} = 0 \text{ V}$	-	-0.8	-1.5	V
Reverse Recovery Time	t _{rr}		-	27	40	ns
Peak Reverse Recovery Current	I _{RM(REC)}	I _F = -10 A, dl/dt = 100 A/μs	-	1.3	2	А
Reverse Recovery Charge	Q _{rr}		-	20	30	nC

Notes


a. Pulse test; pulse width \leq 300 µs, duty cycle \leq 2 %.

b. Guaranteed by design, not subject to production testing.

c. Independent of operating temperature.

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

2



S15-1158-Rev. A, 18-May-15

3

Document Number: 74702

60

80

SUP45P03-09

80

T_J = 150 °C


T_J = 25 °C

8

10

100

Vishay Siliconix



0.020

TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)

www.vishay.com

ISHAY

100

For technical questions, contact: pmostechsupport@vishay.com THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000

2

0

0

20

40

Q_q - Total Gate Charge (nC)


Gate Charge

ISHAY. www.vishay.com


SUP45P03-09

Vishay Siliconix


TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Source-Drain Diode Forward Voltage











Threshold Voltage



Drain Source Breakdown vs. Junction Temperature



S15-1158-Rev. A, 18-May-15


4 estions, contact: pmostechsupport Document Number: 74702

For technical questions, contact: <u>pmostechsupport@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



Vishay Siliconix

TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)



Normalized Thermal Transient Impedance, Junction-to-Case


Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see www.vishay.com/ppg?74702

S15-1158-Rev. A, 18-May-15	5	Document Number: 74702
For	technical questions, contact: pmostechsupport@vishay.com	<u>m</u>
	CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBE	
ARE SUBJECT TO	O SPECIFIC DISCLAIMERS, SET FORTH AT www.vishav.co	<u>om/doc?91000</u>



Vishay Siliconix


TO-220AB



	MILLIN	IETERS	INCHES	
DIM.	MIN.	MAX.	MIN.	MAX.
А	4.25	4.65	0.167	0.183
b	0.69	1.01	0.027	0.040
b(1)	1.20	1.73	0.047	0.068
С	0.36	0.61	0.014	0.024
D	14.85	15.49	0.585	0.610
D2	12.19	12.70	0.480	0.500
Е	10.04	10.51	0.395	0.414
е	2.41	2.67	0.095	0.105
e(1)	4.88	5.28	0.192	0.208
F	1.14	1.40	0.045	0.055
H(1)	6.09	6.48	0.240	0.255
J(1)	2.41	2.92	0.095	0.115
L	13.35	14.02	0.526	0.552
L(1)	3.32	3.82	0.131	0.150
ØР	3.54	3.94	0.139	0.155
Q	2.60	3.00	0.102	0.118
ECN: T14-0 DWG: 5471	0413-Rev. P, 1	16-Jun-14	•	•

Note

 * M = 1.32 mm to 1.62 mm (dimension including protrusion) Heatsink hole for HVM



Revison: 16-Jun-14

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.