


## TELUX LED



19232

### DESCRIPTION

This TELUX device is a clear, non diffused LED for applications where supreme luminous flux is required.

It is designed in an industry standard 7.62 mm square package utilizing highly developed super bright, AllnGaP technology.

The supreme heat dissipation of TELUX allows applications at high ambient temperatures.

All packing units are binned for luminous flux, forward voltage, and color to achieve the most homogeneous light appearance in application.

### PRODUCT GROUP AND PACKAGE DATA

- Product group: LED
- Package: TELUX
- Product series: power
- Angle of half intensity:  $\pm 45^\circ$

### FEATURES

- High luminous flux
- Supreme heat dissipation:  $R_{thJP}$  is 90 K/W
- High operating temperature:  
 $T_{amb} = -40^\circ\text{C}$  to  $+110^\circ\text{C}$
- Meets SAE and ECE color requirements for the automobile industry for color red
- Packed in tubes for automuioatic insertion
- Luminous flux, forward voltage, and color categorized for each tube
- Small mechanical tolerances allow precise usage of external reflectors or lightguides
- Compatible with wave solder processes according to CECC 00802
- ESD-withstand voltage: up to 2 kV according to JESD 22-A114-B
- AEC-Q101 qualified
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)

 AUTOMOTIVE  
GRADE

**RoHS**  
COMPLIANT  
HALOGEN  
**FREE**  
**GREEN**  
(5-2008)

### APPLICATIONS

- Exterior lighting
- Tail-, stop-, and turn signals of motor vehicles
- Traffic light and signs

### PARTS TABLE

| PART     | COLOR  | LUMINOUS FLUX (mIm) |      |        | at $I_F$ (mA) | WAVELENGTH (nm) |      |      | at $I_F$ (mA) | FORWARD VOLTAGE (V) |      |      | at $I_F$ (mA) | TECHNOLOGY    |
|----------|--------|---------------------|------|--------|---------------|-----------------|------|------|---------------|---------------------|------|------|---------------|---------------|
|          |        | MIN.                | TYP. | MAX.   |               | MIN.            | TYP. | MAX. |               | MIN.                | TYP. | MAX. |               |               |
| VLWY9930 | Yellow | 4000                | 8500 | 12 200 | 70            | 585             | 592  | 597  | 70            | 1.83                | 2.2  | 3.03 | 70            | AllnGaP on Si |

### ABSOLUTE MAXIMUM RATINGS ( $T_{amb} = 25^\circ\text{C}$ , unless otherwise specified)

#### VLWY9930

| PARAMETER                              | TEST CONDITION   | SYMBOL     | VALUE       | UNIT             |
|--|--|------------|-------------|------------------|
| Reverse voltage <sup>(1)</sup>         |  | $V_R$      | 10          | V                |
| DC forward current                     | $T_{amb} \leq 85^\circ\text{C}$  | $I_F$      | 70          | mA               |
| Surge forward current                  | $t_p \leq 10 \mu\text{s}$  | $I_{FSM}$  | 0.1         | A                |
| Power dissipation                      |  | $P_V$      | 212         | mW               |
| Junction temperature                   |  | $T_j$      | 125         | $^\circ\text{C}$ |
| Operating temperature range            |  | $T_{amb}$  | -40 to +110 | $^\circ\text{C}$ |
| Storage temperature range              |  | $T_{stg}$  | -40 to +110 | $^\circ\text{C}$ |
| Soldering temperature                  | $t \leq 5 \text{ s}$ , 1.5 mm from body preheat temperature $100^\circ\text{C} / 30 \text{ s}$ | $T_{sd}$   | 260         | $^\circ\text{C}$ |
| Thermal resistance junction to ambient | With anode heatsink of $70 \text{ mm}^2$   | $R_{thJA}$ | 200         | K/W              |
| Thermal resistance junction to pin     |  | $R_{thJP}$ | 90          | K/W              |

#### Note

<sup>(1)</sup> Driving the LED in reverse direction is suitable for a short term application



| <b>OPTICAL AND ELECTRICAL CHARACTERISTICS</b> ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified)<br><b>VLWY9930, YELLOW</b> |  |                    |      |          |        |            |
|---|--|--------------------|------|----------|--------|------------|
| PARAMETER   | TEST CONDITION   | SYMBOL             | MIN. | TYP.     | MAX.   | UNIT       |
| Total flux  | $I_F = 70\text{ mA}$ , $R_{thJA} = 200\text{ K/W}$       | $\phi_V$           | 4000 | 8500     | 12 200 | mlm        |
| Luminous intensity/total flux   | $I_F = 70\text{ mA}$ , $R_{thJA} = 200\text{ K/W}$       | $I_V/\phi_V$       | -    | 0.7      | -      | mcd/mlm    |
| Dominant wavelength   | $I_F = 70\text{ mA}$ , $R_{thJA} = 200\text{ K/W}$       | $\lambda_d$        | 585  | 592      | 597    | nm         |
| Peak wavelength   | $I_F = 70\text{ mA}$ , $R_{thJA} = 200\text{ K/W}$       | $\lambda_p$        | -    | 595      | -      | nm         |
| Angle of half intensity   | $I_F = 70\text{ mA}$ , $R_{thJA} = 200\text{ K/W}$       | $\phi$             | -    | $\pm 45$ | -      | $^{\circ}$ |
| Total included angle  | 90 % of total flux captured                              | $\phi_{0.9V}$      | -    | 100      | -      | $^{\circ}$ |
| Forward voltage   | $I_F = 70\text{ mA}$ , $R_{thJA} = 200\text{ K/W}$       | $V_F$              | 1.83 | 2.2      | 3.03   | V          |
| Reverse voltage   |  | $V_R$              | 10   | 20       | -      | V          |
| Temperature coefficient of $\lambda_{dom}$  | $I_F = 70\text{ mA}$                                     | $T_C\lambda_{dom}$ | -    | 0.1      | -      | nm/K       |
| Temperature coefficient of $V_F$  | $I_F = 70\text{ mA}$ , $T > -25\text{ }^{\circ}\text{C}$ | $T_{CVF}$          | -    | -2       | -      | mV/K       |

| <b>LUMINOUS FLUX CLASSIFICATION</b> |                     |        |
|-------------------------------------|---------------------|--------|
| GROUP                               | LUMINOUS FLUX (mlm) |        |
|                                     | MIN.                | MAX.   |
| H                                   | 4000                | 6100   |
| I                                   | 5000                | 7300   |
| K                                   | 6000                | 9700   |
| L                                   | 7000                | 12 200 |

**Note**

- Luminous flux is tested at a current pulse duration of 25 ms and an accuracy of  $\pm 11\%$ .  
The above type numbers represent the order groups which include only a few brightness groups. Only one group will be shipped on each tube (there will be no mixing of two groups on each tube).  
In order to ensure availability, single brightness groups will be not orderable.  
In a similar manner for colors where wavelength groups are measured and binned, single wavelength groups will be shipped in any one tube.  
In order to ensure availability, single wavelength groups will not be orderable

| <b>COLOR CLASSIFICATION</b> |                          |      |
|-----------------------------|--------------------------|------|
| GROUP                       | DOMINANT WAVELENGTH (nm) |      |
|                             | MIN.                     | MAX. |
| 0                           | 585                      | 588  |
| 1                           | 587                      | 591  |
| 2                           | 589                      | 594  |
| 3                           | 592                      | 597  |

**Note**

- Wavelengths are tested at a current pulse duration of 25 ms and an accuracy of  $\pm 1\text{ nm}$


| <b>FORWARD VOLTAGE CLASSIFICATION</b> |                     |      |
|---------------------------------------|---------------------|------|
| GROUP                                 | FORWARD VOLTAGE (V) |      |
|                                       | MIN.                | MAX. |
| Y                                     | 1.83                | 2.07 |
| Z                                     | 1.95                | 2.19 |
| 0                                     | 2.07                | 2.31 |
| 1                                     | 2.19                | 2.43 |
| 2                                     | 2.31                | 2.55 |
| 3                                     | 2.43                | 2.67 |
| 4                                     | 2.55                | 2.79 |
| 5                                     | 2.67                | 2.91 |
| 6                                     | 2.79                | 3.03 |

**Note**

- Voltages are tested at a current pulse duration of 1 ms

**MARKING EXAMPLE FOR SELECTION CODE ON LABEL**

Selection code: K21



**TYPICAL CHARACTERISTICS** ( $T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified)




Fig. 1 - Forward Current vs. Ambient Temperature




Fig. 4 - Relative Flux vs. Wavelength




Fig. 2 - Forward Current vs. Pulse Length




Fig. 5 - Percentage Total Luminous Flux vs. Total Included Angle for 90° Emission Angle




Fig. 3 - Relative Luminous Intensity vs. Angular Displacement






Fig. 6 - Thermal Resistance Junction Ambient vs. Anode Pads Size

**PACKAGE DIMENSIONS** in millimeters




Drawing-No.: 6.544-5392.01-4  
Issue: 3; 27.02.15

**FAN FOLD BOX DIMENSIONS** in millimeters




**LABEL OF FAN FOLD BOX** (example)



- A. 2D barcode
- B. Part No: Vishay part number
- C. QTY: quantity
- D. SelCode: selection bin code
- E. Country of origin
- F. PTC: production plant code
- G. Termination finish
- H. Region code
- I. Serial#: serial number
- K. Batch number: year, week, country code, plant code
- L. SL: storage location
- M. Environmental symbols: RoHS, lead (Pb)-free, halogen-free
- N. Lot numbers

**EXAMPLE FOR TELUX TUBE LABEL DIMENSIONS** in millimeters




- A. Bar code
- B. Type of component
- C. Manufacturing plant
- D. SEL - selection code (bin):
  - digit 1 - code for luminous flux group
  - digit 2 - code for dominant wavelength group
  - digit 3 - code for forward voltage group
- E. Date code
- F. Batch: no.
- G. Total quantity
- H. Company code

**TUBE WITH BAR CODE LABEL DIMENSIONS** in millimeters

"X"

90° gedreht / 90° turned




Wanddicke/wall thickness: 0.6±0.1

Geradheit/Straightness 2

Schnittwinkel/cut 90° ±1°

Geprüft nach/approved to: LV 5145

Bestücken mit 1 Stopper / equip with 1 stopper



Drawing-No.: 9.700-5223.0-4

Rev. 2; Date: 23.08.99

20438

Drawing Proportions not Scaled



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.