
TEMT1000, TEMT1020, TEMT1030, TEMT1040

Vishay Semiconductors

Silicon NPN Phototransistor, RoHS Compliant



FEATURES

- · Package type: surface mount
- · Package form: GW, RGW, yoke, axial
- Dimensions (L x W x H in mm): 2.5 x 2 x 2.7
- · High radiant sensitivity
- Daylight blocking filter matched with 870 nm to 950 nm IR emitters



ROHS

- Fast response times
- Angle of half sensitivity: $\varphi = \pm 15^{\circ}$
- Package matches with IR emitter series TSML1000
- Floor life: 168 h, MSL 3, acc. J-STD-020
- Compliant to RoHS Directive 2002/95/EC and in accordance with WEEE 2002/96/EC

DESCRIPTION

TEMT1000 series are silicon NPN phototransistors with high radiant sensitivity in black, surface mount, plastic packages with lens and daylight blocking filter. Filter bandwidth is matched with 870 nm to 950 nm IR emitters.

APPLICATIONS

- · Detector in electronic control and drive circuits
- IR detector for daylight application
- Photo interrupters
- Counter
- Encoder

PRODUCT SUMMARY				
COMPONENT	I _{ca} (mA)	φ (deg)	λ _{0.5} (nm)	
TEMT1000	7	± 15	730 to 1000	
TEMT1020	7	± 15	730 to 1000	
TEMT1030	7	± 15	730 to 1000	
TEMT1040	7	± 15	730 to 1000	

Note

· Test conditions see table "Basic Characteristics"

ORDERING INFORMATION				
ORDERING CODE	PACKAGING	REMARKS	PACKAGE FORM	
TEMT1000	Tape and reel	MOQ: 1000 pcs, 1000 pcs/reel	Reverse gullwing	
TEMT1020	Tape and reel	MOQ: 1000 pcs, 1000 pcs/reel	Gullwing	
TEMT1030	Tape and reel	MOQ: 1000 pcs, 1000 pcs/reel	Yoke	
TEMT1040	Bulk	MOQ: 1000 pcs, 1000 pcs/bulk	Axial leads	

Note

MOQ: minimum order quantity

ABSOLUTE MAXIMUM RATINGS (T _{amb} = 25 °C, unless otherwise specified)					
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT	
Emitter collector voltage		V _{ECO}	5	V	
Collector current		I _C	50	mA	
Collector peak current	$t_p/T = 0.5, t_p \le 10 \text{ ms}$	I _{CM}	100	mA	
Power dissipation	T _{amb} ≤ 55 °C	P _V	100	mW	
Junction temperature		Tj	100	°C	
Operating temperature range		T _{amb}	- 40 to + 85	°C	
Storage temperature range		T _{stg}	- 40 to + 100	°C	
Soldering temperature	t ≤ 5 s	T _{sd}	260	°C	
Thermal resistance junction/ambient	Soldered on PCB with pad dimensions: 4 mm x 4 mm	R _{thJA}	400	K/W	

Vishay Semiconductors




Fig. 1 - Power Dissipation Limit vs. Ambient Temperature

BASIC CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified)						
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Collector emitter voltage	I _C = 1 mA	V_{CEO}	70			V
Collector emitter dark current	V _{CE} = 20 V, E = 0	I _{CEO}		1	200	nA
Collector emitter capacitance	V _{CE} = 5 V, f = 1 MHz, E = 0	C _{CEO}		3		pF
Angle of half sensitivity		φ		± 15		deg
Wavelength of peak sensitivity		λ_{p}		880		nm
Range of spectral bandwidth		λ _{0.5}		730 to 1000		nm
Collector emitter saturation voltage	$E_{e} = 1 \text{ mW/cm}^{2}, \lambda = 950 \text{ nm},$ $I_{C} = 0.1 \text{ mA}$	V _{CEsat}			0.3	V
Turn-on time	$V_S = 5 \text{ V}, I_C = 5 \text{ mA}, R_L = 100 \Omega$	t _{on}		2.0		μs
Turn-off time	$V_S = 5 \text{ V}, I_C = 5 \text{ mA}, R_L = 100 \Omega$	t _{off}		2.3		μs
Cut-off frequency	$V_S = 5 \text{ V}, I_C = 5 \text{ mA}, R_L = 100 \Omega$	f _c		180		kHz
Collector light current	E_e = 1 mW/cm ² , λ = 950 nm, V_{CE} = 5 V	I _{ca}	2	7.0		mA

BASIC CHARACTERISTICS (T_{amb} = 25 °C, unless otherwise specified)




Fig. 2 - Collector Dark Current vs. Ambient Temperature




Fig. 3 - Relative Collector Current vs. Ambient Temperature

Vishay Semiconductors




Fig. 4 - Collector Light Current vs. Irradiance




Fig. 5 - Collector Emitter Capacitance vs. Collector Emitter Voltage




Fig. 6 - Turn-on/Turn-off Time vs. Collector Current




Fig. 7 - Relative Spectral Sensitivity vs. Wavelength




Fig. 8 - Relative Radiant Sensitivity vs. Angular Displacement

www.vishay.com

Vishay Semiconductors

PRECAUTIONS FOR USE

1. Over-current-proof

Customer must apply resistors for protection, otherwise slight voltage shift will cause big current change (burn out will happen).

2. Storage

- Storage temperature and rel. humidity conditions are:
 C to 35 °C, R.H. 60 %.
- Floor life must not exceed 168 h, acc. to JEDEC level 3, J-STD-020.
 - Once the package is opened, the products should be used within a week. Otherwise, they should be kept in a damp proof box with desiccant.
 - Considering tape life, we suggest to use products within one year from production date.
- If opened more than one week in an atmosphere 5 °C to 35 °C, R.H. 60 %, devices should be treated at 60 °C $\,\pm\,$ 5 °C for 15 h.
- If humidity indicator in the package shows pink color (normal blue), then devices should be treated with the same conditions as 2.3.

REFLOW SOLDER PROFILE






Fig. 9 - Lead Tin (SnPb) Reflow Solder Profile



22566

Fig. 10 - Lead (Pb)-Free Reflow Solder Profile acc. J-STD-020

PACKAGE DIMENSIONS in millimeters: **TEMT1000**



Drawing-No.: 6.544-5326.01-4 Issue: 4; 02.04.03

16104








www.vishay.com

Vishay Semiconductors

PACKAGE DIMENSIONS in millimeters: **TEMT1020**





Drawing-No.: 6.544-5325.01-4

Issue: 5; 19.01.06

16105

PACKAGE DIMENSIONS in millimeters: **TEMT1030**






Drawing-No.: 6.544-5329.02-4

Issue: 3; 08.05.03



All dimensions in mm






www.vishay.com

Vishay Semiconductors


PACKAGE DIMENSIONS in millimeters: **TEMT1040**



Drawing-No.: 6.544-5339.01-4 Issue: 2: 02.04.03

16500


REEL DIMENSIONS in millimeters




18033

Vishay Semiconductors

TAPING DIMENSIONS in millimeters: **TEMT1000**




TAPING DIMENSIONS in millimeters: **TEMT1020**



TEMT1000, TEMT1020, TEMT1030, TEMT1040

Vishay Semiconductors

TAPING DIMENSIONS in millimeters: TEMT1030





Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.