


## Ultrabright 0603 SMD LED



18562

### DESCRIPTION

The new 0603 LED series have been designed in the smallest SMD package. This innovative 0603 LED technology opens the way to

- smaller products of higher performance
- more design in flexibility
- enhanced applications

The 0603 LED is an obvious solution for small-scale, high power products that are expected to work reliably in an arduous environment.

The reflector inside this package is filled with a mixture of epoxy and yellow converter.

This yellow converter converts the blue emission partially to yellow, which mixes the remaining blue to give white.

### PRODUCT GROUP AND PACKAGE DATA

- Product group: LED
- Package: SMD 0603
- Product series: standard
- Angle of half intensity:  $\pm 80^\circ$

### FEATURES

- High efficient InGaN technology
- Smallest SMD package 0603 with exceptional brightness  
1.6 mm x 0.8 mm x 0.6 mm (L x W x H)
- High reliability lead frame based
- Temperature range - 40 °C to + 100 °C
- Chromaticity coordinate categorized according to CIE1931 per packing unit
- Typical color temperature 5500 K
- EIA and ICE standard package
- Compatible to IR reflow soldering
- Available in 8 mm tape reel
- Preconditioning: according to JEDEC level 2
- Compliant to RoHS Directive 2002/95/EC and in accordance to WEEE 2002/96/EC
- ESD-withstand voltage: up to 1 kV according to JESD22-A114-B
- AEC-Q101 qualified



### APPLICATIONS

- Automotive: backlighting in dashboards, switches and keypads
- Telecommunication: indicator and backlighting in telephone and fax
- Backlighting for audio and video equipment
- Backlighting in office equipment
- Indoor and outdoor message boards
- Flat backlight for LCDs, switches and symbols

### PARTS TABLE

| PART               | COLOR, LUMINOUS INTENSITY AT $I_F = 10 \text{ mA}$ | TECHNOLOGY             |
|--------------------|--|------------------------|
| VLMW11R2S2-5K8L-08 | White, $I_V = (140 \text{ to } 280) \text{ mcd}$   | InGaN/yellow converter |

\*\* Please see document "Vishay Material Category Policy": [www.vishay.com/doc?99902](http://www.vishay.com/doc?99902)

| ABSOLUTE MAXIMUM RATINGS <sup>1)</sup> VLMW11.. |   |                   |               |                  |
|---|---|-------------------|---------------|------------------|
| PARAMETER                                       | TEST CONDITION  | SYMBOL            | VALUE         | UNIT             |
| Reverse voltage <sup>2)</sup>                   | $I_R \text{ max.} = 10 \mu\text{A}$                     | $V_R$             | 5             | V                |
| DC forward current                              | $T_{\text{amb}} \leq 60 \text{ }^\circ\text{C}$         | $I_F$             | 20            | mA               |
| Surge forward current                           | $t_p \leq 10 \mu\text{s}$                               | $I_{\text{FSM}}$  | 0.1           | A                |
| Power dissipation                               |   | $P_V$             | 80            | mW               |
| Junction temperature                            |   | $T_j$             | 110           | $^\circ\text{C}$ |
| Storage temperature range                       |   | $T_{\text{stg}}$  | - 40 to + 100 | $^\circ\text{C}$ |
| Operating temperature range                     |   | $T_{\text{amb}}$  | - 40 to + 100 | $^\circ\text{C}$ |
| Thermal resistance junction/<br>ambient         | mounted on PC board<br>(pad size > 16 mm <sup>2</sup> ) | $R_{\text{thJA}}$ | 480           | K/W              |

Note:

<sup>1)</sup>  $T_{\text{amb}} = 25 \text{ }^\circ\text{C}$ , unless otherwise specified

<sup>2)</sup> Driving the LED in reverse direction is suitable for short term application

| OPTICAL AND ELECTRICAL CHARACTERISTICS <sup>1)</sup> VLMW11.., WHITE |                       |            |            |      |          |      |      |
|--|-----------------------|------------|------------|------|----------|------|------|
| PARAMETER  | TEST CONDITION        | PART       | SYMBOL     | MIN. | TYP.     | MAX. | UNIT |
| Luminous intensity   | $I_F = 10 \text{ mA}$ | VLMW11R2S2 | $I_V$      | 140  |          | 280  | mcd  |
| Chromaticity coordinate x acc. to<br>CIE 1931                        | $I_F = 10 \text{ mA}$ | VLMW11     | x          |      | 0.33     |      |      |
| Chromaticity coordinate y acc. to<br>CIE 1931                        | $I_F = 10 \text{ mA}$ | VLMW11     | y          |      | 0.33     |      |      |
| Angle of half intensity  | $I_F = 10 \text{ mA}$ |            | $\varphi$  |      | $\pm 80$ |      | deg  |
| Forward voltage  | $I_F = 20 \text{ mA}$ |            | $V_F$      | 2.9  |          | 4.0  | V    |
| Temperature coefficient of $V_F$                                     | $I_F = 10 \text{ mA}$ |            | $TC_{V_F}$ |      | - 3      |      | mV/K |
| Temperature coefficient of $I_V$                                     | $I_F = 10 \text{ mA}$ |            | $TC_{I_V}$ |      | - 0.4    |      | %/K  |

Note:

<sup>1)</sup>  $T_{\text{amb}} = 25 \text{ }^\circ\text{C}$ , unless otherwise specified

| LUMINOUS INTENSITY CLASSIFICATION |                       |          |      |      |
|-----------------------------------|-----------------------|----------|------|------|
| GROUP                             | LIGHT INTENSITY (mcd) |          |      |      |
|                                   | STANDARD              | OPTIONAL | MIN. | MAX. |
| R                                 | -                     | -        | -    | -    |
|                                   | 2                     |          | 140  | 180  |
| S                                 | 1                     |          | 180  | 224  |
|                                   | 2                     |          | 224  | 280  |

Note:

Luminous intensity is tested at a current pulse duration of 25 ms and an accuracy of  $\pm 11 \%$ .

The above type numbers represent the order groups which include only a few brightness groups. Only one group will be shipped on each reel (there will be no mixing of two groups on each reel). In order to ensure availability, single brightness groups are not be orderable.

In a similar manner for colors where wavelength groups are measured and binned, single wavelength groups will be shipped on any one reel.

In order to ensure availability, single wavelength groups are not be orderable.

| CROSSING TABLE |             |
|----------------|-------------|
| VISHAY         | OSRAM       |
| VLMW11R2S2     | LWL28G-R2S2 |

| CHROMATICITY COORDINATED GROUPS FOR WHITE SMD LED |       |       |    |       |       |
|---|-------|-------|----|-------|-------|
|   | X     | Y     |    | X     | Y     |
| 5L  | 0.291 | 0.268 | 7L | 0.330 | 0.330 |
|   | 0.285 | 0.279 |    | 0.330 | 0.347 |
|   | 0.307 | 0.312 |    | 0.347 | 0.371 |
|   | 0.310 | 0.297 |    | 0.345 | 0.352 |
| 5K  | 0.296 | 0.259 | 7K | 0.330 | 0.310 |
|   | 0.291 | 0.268 |    | 0.330 | 0.330 |
|   | 0.310 | 0.297 |    | 0.338 | 0.342 |
|   | 0.313 | 0.284 |    | 0.352 | 0.344 |
| 6L  | 0.310 | 0.297 | 8L | 0.345 | 0.352 |
|   | 0.307 | 0.312 |    | 0.347 | 0.371 |
|   | 0.330 | 0.347 |    | 0.367 | 0.401 |
|   | 0.330 | 0.330 |    | 0.364 | 0.380 |
| 6K  | 0.313 | 0.284 | 8K | 0.352 | 0.344 |
|   | 0.310 | 0.297 |    | 0.338 | 0.342 |
|   | 0.330 | 0.330 |    | 0.364 | 0.380 |
|   | 0.330 | 0.310 |    | 0.360 | 0.357 |

Note:

Chromaticity coordinate groups are tested at a current pulse duration of 25 ms and a tolerance of  $\pm 0.01$ .

### TYPICAL CHARACTERISTICS

$T_{amb} = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified




Figure 1. Forward Current vs. Ambient Temperature




Figure 2. Relative Intensity vs. Wavelength




Figure 3. Forward Current vs. Forward Voltage




Figure 6. Forward Voltage vs. Ambient Temperature




Figure 4. Relative Luminous Intensity vs. Forward Current




Figure 7. Coordinates of Colorgroups





Figure 5. Rel. Luminous Intensity vs. Ambient Temperature


**REEL DIMENSIONS** in millimeters



Drawing-No.: 9.800-5086.01-4  
Issue: 1; 29.04.04  
19043

Not indicated tolerances  $\pm 0.05$   
Material: black static dissipative


### TAPE DIMENSIONS in millimeters




Drawing-No.: 9.700-5290.01-4

Issue: 2; 10.07.06

19044

**PACKAGE DIMENSIONS** in millimeters

 Not indicated tolerances  $\pm 0.1$ 

Recommended solder pad



Drawing-No.: 6.541-5056.01-4

Issue: 2; 04.05.05

19426



**SOLDERING PROFILE**


Figure 8. Vishay Lead (Pb)-free Reflow Soldering Profile (acc. to J-STD-020C)


**BAR CODE PRODUCT LABEL  
EXAMPLE:**



- A) Type of component
- B) Manufacturing plant
- C) SEL - selection code (bin):  
e.g.: R1 = code for luminous intensity group  
5L = code for chrom. coordinate group
- D) Date code year/week
- E) Day code (e.g. 4: Thursday)
- F) Batch no.
- G) Total quantity
- H) Company code

**DRY PACKING**

The reel is packed in an anti-humidity bag to protect the devices from absorbing moisture during transportation and storage.



**FINAL PACKING**

The sealed reel is packed into a cardboard box. A secondary cardboard box is used for shipping purposes.

**RECOMMENDED METHOD OF STORAGE**

Dry box storage is recommended as soon as the aluminium bag has been opened to prevent moisture absorption. The following conditions should be observed, if dry boxes are not available:


- Storage temperature 10 °C to 30 °C
- Storage humidity ≤ 60 % RH max.

After more than 1 year under these conditions moisture content will be too high for reflow soldering.

In case of moisture absorption, the devices will recover to the former condition by drying under the following condition:

- 192 h at 40 °C + 5 °C/- 0 °C and < 5 % RH (dry air/nitrogen) or
- 96 h at 60 °C + 5 °C and < 5 % RH for all device containers or
- 24 h at 100 °C + 5 °C not suitable for reel or tubes.

An EIA JEDEC Standard JESD22-A112 level 2 label is included on all dry bags.



17028

Example of JESD22-A112 level 2 label

**ESD PRECAUTION**

Proper storage and handling procedures should be followed to prevent ESD damage to the devices especially when they are removed from the antistatic shielding bag. Electro-static sensitive devices warning labels are on the packaging.

**VISHAY SEMICONDUCTORS STANDARD  
BAR CODE LABELS**

The Vishay Semiconductors standard bar code labels are printed at final packing areas. The labels are on each packing unit and contain Vishay Semiconductors specific data.



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.