

Multi SMD LED RGB



20777

FEATURES

- High brightness tricolor SMD LED
- RGB individual control
- Compact package outline
- Black surface
- Qualified according to JEDEC moisture sensitivity level 2
- Compatible to IR reflow soldering
- Automotive qualified AEC-Q101
- Compliant to RoHS directive 2002/95/EC and in accordance to WEEE 2002/96/EC
- ESD-withstand voltage: up to 1 kV according to JESD22-A114-B


RoHS
COMPLIANT

DESCRIPTION

VLMRGB343.. tricolor LEDs is a high brightness device designed for demanding applications in efficiency and reduced space. An ideal device in emphasizing visual effects, advertisement, decoration as well as general backlighting needs.

PRODUCT GROUP AND PACKAGE DATA

- Product group: LED
- Package: SMD PLCC-4
- Product series: RGB
- Angle of half intensity: $\pm 60^\circ$

APPLICATIONS

- Wide range of accent and decorative lighting
- Displays: full color message and displays video boards
- Consumer appliances: backlight LCDs, PDAs, TVs
- Industry: white goods such as ovens, microwaves, etc.

PARTS TABLE		
PART	COLOR (λ_d), LUMINOUS INTENSITY	TECHNOLOGY
VLMRGB343-ST-UV-RS	Red, $I_V = (140 \text{ to } 285) \text{ mcd}$, (typ 625 nm)	AlInGaP
	True green, $I_V = (285 \text{ to } 560) \text{ mcd}$, (typ 525 nm)	InGaN
	Blue, $I_V = (100 \text{ to } 200) \text{ mcd}$, (typ 470 nm)	InGaN

Note:

Reel comes in a quantity of 2050 units per reel. Luminous intensity is measured with an accuracy of $\pm 11\%$. All electrical and optical data are measured at room temperature of 25 °C.

ABSOLUTE MAXIMUM RATINGS ¹⁾ VLMRGB343.., RED				
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT
Forward current		I_F	30	mA
Reverse voltage		V_R	12	V
Power dissipation		P_{tot}	75	mW
Junction temperature		T_j	125	°C
Surge current $t_p < 10 \mu s$, duty cycle = 0.005		I_{FM}	1000	mA
Thermal resistance junction/solder point 1 chip ON 3 chip ON		R_{thJP}	260 420	K/W
Thermal resistance junction/ambient 1 chip ON 3 chip ON		R_{thJA}	480 770	K/W
Operating temperature		T_{amb}	- 40 to + 100	°C
Storage temperature		T_{stg}	- 40 to + 100	°C
Forward voltage	20 mA	V_F	1.8 to 2.45	V

Note:

¹⁾ $T_{amb} = 25 \text{ °C}$, unless otherwise specified

ABSOLUTE MAXIMUM RATINGS ¹⁾ VLMRGB343.., TRUE GREEN, BLUE				
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT
Forward current		I_F	20	mA
Reverse voltage		V_R	5	V
Power dissipation		P_{tot}	85	mW
Junction temperature		T_j	125	°C
Surge current $t_p < 10 \mu s$, duty cycle = 0.005		I_{FM}	200	mA
Thermal resistance junction/solder point 1 chip ON 3 chip ON		R_{thJP}	290 470	K/W
Thermal resistance junction/ambient 1 chip ON 3 chip ON		R_{thJA}	530 820	K/W
Operating temperature		T_{amb}	- 40 to + 100	°C
Storage temperature		T_{stg}	- 40 to + 100	°C
Forward voltage	20 mA	V_F	3.7 to 4.25	V

Note:

¹⁾ $T_{amb} = 25 \text{ °C}$, unless otherwise specified

OPTICAL AND ELECTRICAL CHARACTERISTICS ¹⁾ VLMRGB343.., RED, TRUE GREEN, BLUE														
PARAMETER	TEST CONDITION	PART	FLOATING GROUPS	COLOR	SYMBOL	MIN.	TYP.	MAX.	UNIT					
Luminous intensity	$I_F = 20 \text{ mA}$	VLMRGB343-ST-UV-RS		red	I_V	140		285	mcd					
				true green		285		560						
				blue		100		200						
				VLMRGB343	S3U3R3	red	I_V	140		200	mcd			
						true green		285		400				
						blue		100		140				
								S3U3S3	red	I_V	140		200	mcd
									true green		285		400	
									blue		140		200	
								S3V3R3	red	I_V	140		200	mcd
									true green		400		560	
									blue		100		140	
								S3V3S3	red	I_V	140		200	mcd
									true green		400		560	
									blue		140		200	
								T3U3R3	red	I_V	200		285	mcd
									true green		285		400	
									blue		100		140	
								T3U3S3	red	I_V	200		285	mcd
									true green		285		400	
									blue		140		200	
								T3V3R3	red	I_V	200		285	mcd
									true green		400		560	
									blue		100		140	
								T3V3S3	red	I_V	200		285	mcd
									true green		400		560	
									blue		140		200	
					Dominant wavelength				red	λ_d	618	625	628	nm
									true green		521	526	536	
									blue		465	470	475	
Angle of half intensity					VLMRGB343..		red	ϕ		± 60		deg		
							true green							
							blue							
Forward voltage				red	V_F		1.8	2.45	V					
				true green			3.7	4.25						
				blue			3.6	4.25						

Note:

Not designed for reverse direction

¹⁾ $T_{amb} = 25 \text{ }^\circ\text{C}$, unless otherwise specified

LUMINOUS INTENSITY CLASSIFICATION RED, TRUE GREEN, BLUE		
GROUP	LUMINOUS INTENSITY I_V (mcd)	
STANDARD	MIN.	MAX.
R3	100	140
S3	140	200
T3	200	285
U3	285	400
V3	400	560

Note:

The standard shipping format for serial types includes a family group of 5, 6 or 9 individual brightness groups. Individual brightness groups cannot be ordered.

COLOR CLASSIFICATION						
GROUP	DOM. WAVELENGTH (nm)					
	RED ¹⁾		TRUE GREEN		BLUE	
	MIN.	MAX.	MIN.	MAX.	MIN.	MAX.
	618	628	521	536	465	475
A			521	526	465	470
B			526	531	470	475
C			531	536		

Note:

Wavelengths are tested at a current pulse duration of 25 ms and an accuracy of ± 1 nm. Only one wavelength group is allowed for each chip within one reel.

¹⁾ No color grouping for red. Only for check of color.

TYPICAL CHARACTERISTICS

$T_{amb} = 25\text{ }^\circ\text{C}$, unless otherwise specified




Figure 1. Forward Current vs. Ambient Temperature (1 Chip On)




Figure 2. Forward Current vs. Ambient Temperature (3 Chips On)




Figure 3. Relative Intensity vs. Wavelength




Figure 6. Relative Dominant Wavelength vs. Forward Current




Figure 4. Forward Current vs. Forward Voltage




Figure 7. Forward Current vs. Solder Point Temperature (1 Chip On)




Figure 5. Relative Luminous Intensity vs. Forward Current





Figure 8. Forward Current vs. Solder Point Temperature (3 Chips On)

TAPING DIMENSIONS in millimeters


Taping and orientation

Reels come in quantity of 2050 units.



200mm min. for $\phi 330$ reel

9600mm min. for $\phi 330$ reel





Technical drawings according to DIN specifications

Drawing-No.: 9.700-5323.01-4

Issue: 2; 05.02.08

20819

PACKAGE DIMENSIONS/SOLDERING PADS DIMENSIONS in millimeters



Drawing-No.: 6.541-5074.01-4
Issue: 2; 16.04.09
20820

SOLDERING PROFILE






Figure 9. Vishay Lead (Pb)-free Reflow Soldering Profile (acc. to J-STD-020)

DRY PACKING

The reel is packed in an anti-humidity bag to protect the devices from absorbing moisture during transportation and storage.



BAR CODE PRODUCT LABEL EXAMPLE:



- A) Type of component
- B) Manufacturing plant
- C) SEL - selection code (bin):
e.g.: DA = code for luminous intensity group
5 = code for color group
4 = code for forward voltage
- D) Batch:
200707 = year 2007, week 07
PH19 = plant code
- E) Total quantity

FINAL PACKING

The sealed reel is packed into a cardboard box. A secondary cardboard box is used for shipping purposes.

RECOMMENDED METHOD OF STORAGE

Dry box storage is recommended as soon as the aluminum bag has been opened to prevent moisture absorption. The following conditions should be observed, if dry boxes are not available:

- Storage temperature 10 °C to 30 °C
- Storage humidity ≤ 60 % RH max.

After more than 72 h under these conditions moisture content will be too high for reflow soldering.


In case of moisture absorption, the devices will recover to the former condition by drying under the following condition:

192 h at 40 °C + 5 °C/- 0 °C and < 5 % RH (dry air/nitrogen) or

96 h at 60 °C + 5 °C and < 5 % RH for all device containers or

24 h at 100 °C + 5 °C not suitable for reel or tubes.

An EIA JEDEC standard JESD22-A112 level 2 label is included on all aluminum dry bags.



17028

Example of JESD22-A112 level 2 label

ESD PRECAUTION

Proper storage and handling procedures should be followed to prevent ESD damage to the devices especially when they are removed from the antistatic shielding bag. Electro-static sensitive devices warning labels are on the packaging.

VISHAY SEMICONDUCTORS STANDARD BAR CODE LABELS

The Vishay Semiconductors standard bar code labels are printed at final packing areas. The labels are on each packing unit and contain Vishay Semiconductors specific data.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.