


## Clock Display



16770

### DESCRIPTION

Four digit display, with 10 mm digit charactersize. Designed as clock display with active colon between digit two and three.

### FEATURES

- High efficient AlInGAP technology
- Dark surface, white segments
- Common anode (TDC.1050m)
- Common cathode (TDC.1060m)
- Multiplex mode
- Recommended viewing distance up to 7 m
- Compliant to RoHS directive 2002/95/EC and in accordance to WEEE 2002/96/EC



**RoHS**  
COMPLIANT

### APPLICATIONS

- Clock modules for video/audioequipment, instrumentation, set top boxes

### PRODUCT GROUP AND PACKAGE DATA

- Product group: display
- Package: 10 mm clock
- Product series: standard
- Angle of half intensity:  $\pm 50^\circ$

### PARTS TABLE

PART	COLOR	LUMINOUS INTENSITY AT 10 mA	CIRCUITRY
TDCG1050m	Green	$I_V = (2800 \text{ to } 4000) \mu\text{cd}$	Common anode
TDCG1060m	Green	$I_V = (2800 \text{ to } 4000) \mu\text{cd}$	Common cathode
TDCR1050m	Red	$I_V = (4000 \text{ to } 6000) \mu\text{cd}$	Common anode
TDCR1060m	Red	$I_V = (4000 \text{ to } 6000) \mu\text{cd}$	Common cathode
TDCY1050m	Super yellow	$I_V = (4000 \text{ to } 8000) \mu\text{cd}$	Common anode
TDCY1060m	Super yellow	$I_V = (4000 \text{ to } 8000) \mu\text{cd}$	Common cathode

### ABSOLUTE MAXIMUM RATINGS <sup>(1)</sup> TDCG1050m, TDCG1060m, TDCR1050m, TDCR1060m, TDCY1050m, TDCY1060m

PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT
Reverse voltage per segment		$V_R$	5	V
DC forward current per segment		$I_F$	25	mA
Peak forward current per segment	Duty 1/10 at 1 kHz	$I_{FM}$	160	mA
Power dissipation		$P_V$	60	mW
Operating temperature range		$T_{amb}$	- 40 to + 85	$^\circ\text{C}$
Storage temperature range		$T_{stg}$	- 40 to + 100	$^\circ\text{C}$
Soldering temperature		$T_{sd}$	$260 \pm 5$	$^\circ\text{C}$

#### Note

<sup>(1)</sup>  $T_{amb} = 25 \text{ }^\circ\text{C}$ , unless otherwise specified



OPTICAL AND ELECTRICAL CHARACTERISTICS <sup>(1)</sup> TDCG1050m, TDCG1060m, GREEN							
PARAMETER	TEST CONDITION	PART	SYMBOL	MIN.	TYP.	MAX.	UNIT
Luminous intensity per segment <sup>(2)</sup>	$I_F = 2 \text{ mA}$	TDCG1050m	$I_V$	-	1000	-	$\mu\text{cd}$
		TDCG1060m					
	$I_F = 10 \text{ mA}$	TDCG1050m	$I_V$	2800	4000	-	$\mu\text{cd}$
		TDCG1060m					
Luminous intensity of colon	$I_F = 2 \text{ mA}$	TDCG1050m	$I_V$	-	200	-	$\mu\text{cd}$
		TDCG1060m					
	$I_F = 10 \text{ mA}$	TDCG1050m	$I_V$	500	1200	-	$\mu\text{cd}$
		TDCG1060m					
Dominant wavelength	$I_F = 20 \text{ mA}$	TDCG1050m, TDCG1060m	$\lambda_d$	562	573	575	nm
Peak wavelength	$I_F = 20 \text{ mA}$		$\lambda_p$	-	575	-	nm
Spectral bandwidth	$I_F = 20 \text{ mA}$		$\Delta\lambda$	-	20	-	nm
Forward voltage per segment or DP	$I_F = 20 \text{ mA}$		$V_F$	-	2	2.4	V
Reverse current per segment or DP	$V_R = 5 \text{ V}$		$I_R$	-	-	10	$\mu\text{A}$

**Notes**

<sup>(1)</sup>  $T_{amb} = 25 \text{ }^\circ\text{C}$ , unless otherwise specified

<sup>(2)</sup>  $I_{Vmin.}$  and  $I_V$  groups are mean values of all segments (a to g, D1 to D4), matching factor within segments is  $\geq 0.5$ , excluding decimal points and colon.

OPTICAL AND ELECTRICAL CHARACTERISTICS <sup>(1)</sup> TDCR1050m, TDCR1060m, RED							
PARAMETER	TEST CONDITION	PART	SYMBOL	MIN.	TYP.	MAX.	UNIT
Luminous intensity per segment <sup>(2)</sup>	$I_F = 2 \text{ mA}$	TDCR1050m	$I_V$	-	1500	-	$\mu\text{cd}$
		TDCR1060m					
	$I_F = 10 \text{ mA}$	TDCR1050m	$I_V$	4000	6000	-	$\mu\text{cd}$
		TDCR1060m					
Luminous intensity of colon	$I_F = 2 \text{ mA}$	TDCR1050m	$I_V$	-	400	-	$\mu\text{cd}$
		TDCR1060m					
	$I_F = 10 \text{ mA}$	TDCR1050m	$I_V$	500	800	-	$\mu\text{cd}$
		TDCR1060m					
Dominant wavelength	$I_F = 20 \text{ mA}$	TDCR1050m, TDCR1060m	$\lambda_d$	-	631	-	nm
Peak wavelength	$I_F = 20 \text{ mA}$		$\lambda_p$	-	639	-	nm
Spectral bandwidth	$I_F = 20 \text{ mA}$		$\Delta\lambda$	-	20	-	nm
Forward voltage per segment or DP	$I_F = 20 \text{ mA}$		$V_F$	-	2	2.4	V
Reverse current per segment or DP	$V_R = 5 \text{ V}$		$I_R$	-	-	10	$\mu\text{A}$

**Notes**

<sup>(1)</sup>  $T_{amb} = 25 \text{ }^\circ\text{C}$ , unless otherwise specified

<sup>(2)</sup>  $I_{Vmin.}$  and  $I_V$  groups are mean values of all segments (a to g, D1 to D4), matching factor within segments is  $\geq 0.5$ , excluding decimal points and colon.



OPTICAL AND ELECTRICAL CHARACTERISTICS <sup>(1)</sup> TDCY1050m, TDCY1060m, SUPER YELLOW							
PARAMETER	TEST CONDITION	PART	SYMBOL	MIN.	TYP.	MAX.	UNIT
Luminous intensity per segment <sup>(2)</sup>	$I_F = 2 \text{ mA}$	TDCY1050m	$I_V$	-	1500	-	$\mu\text{cd}$
		TDCY1060m					
	$I_F = 10 \text{ mA}$	TDCY1050m	$I_V$	4000	8000	-	$\mu\text{cd}$
		TDCY1060m					
Luminous intensity of colon	$I_F = 2 \text{ mA}$	TDCY1050m	$I_V$	-	400	-	$\mu\text{cd}$
		TDCY1060m					
	$I_F = 10 \text{ mA}$	TDCY1050m	$I_V$	500	1000	-	$\mu\text{cd}$
		TDCY1060m					
Dominant wavelength	$I_F = 20 \text{ mA}$	TDCY1050m, TDCY1060m	$\lambda_d$	-	589	-	nm
Peak wavelength	$I_F = 20 \text{ mA}$		$\lambda_p$	-	591	-	nm
Spectral bandwidth	$I_F = 20 \text{ mA}$		$\Delta\lambda$	-	15	-	nm
Forward voltage per segment or DP	$I_F = 20 \text{ mA}$		$V_F$	-	2	2.4	V
Reverse current per segment or DP	$V_R = 5 \text{ V}$		$I_R$	-	-	10	$\mu\text{A}$

### Notes

<sup>(1)</sup>  $T_{amb} = 25 \text{ }^\circ\text{C}$ , unless otherwise specified

<sup>(2)</sup>  $I_{Vmin.}$  and  $I_V$  groups are mean values of all segments (a to g, D1 to D4), matching factor within segments is  $\geq 0.5$ , excluding decimal points and colon.

### PINNING



Drawing-No.: 6.544-5332.01-4 Bl. 2

Issue: 1; 20.02.02

16715


# TDCG10..m, TDCR10..m, TDCY10..m

Vishay Semiconductors

Clock Display



## PACKAGE DIMENSIONS in millimeters




Drawing-No.: 6.544-5332.01-4 Bl. 1  
Issue: 3; 27.02.02

16764

## Display-10 mm Clock Multiplex

### Package Dimensions in mm



Drawing-No.: 6.544-5332.01-4 Bl. 1

Issue: 3; 27.02.02

16764

## Ozone Depleting Substances Policy Statement

It is the policy of **Vishay Semiconductor GmbH** to

1. Meet all present and future national and international statutory requirements.
2. Regularly and continuously improve the performance of our products, processes, distribution and operating systems with respect to their impact on the health and safety of our employees and the public, as well as their impact on the environment.

It is particular concern to control or eliminate releases of those substances into the atmosphere which are known as ozone depleting substances (ODSs).

The Montreal Protocol (1987) and its London Amendments (1990) intend to severely restrict the use of ODSs and forbid their use within the next ten years. Various national and international initiatives are pressing for an earlier ban on these substances.

**Vishay Semiconductor GmbH** has been able to use its policy of continuous improvements to eliminate the use of ODSs listed in the following documents.

1. Annex A, B and list of transitional substances of the Montreal Protocol and the London Amendments respectively
2. Class I and II ozone depleting substances in the Clean Air Act Amendments of 1990 by the Environmental Protection Agency (EPA) in the USA
3. Council Decision 88/540/EEC and 91/690/EEC Annex A, B and C (transitional substances) respectively.

**Vishay Semiconductor GmbH** can certify that our semiconductors are not manufactured with ozone depleting substances and do not contain such substances.

**We reserve the right to make changes to improve technical design  
and may do so without further notice.**

Parameters can vary in different applications. All operating parameters must be validated for each customer application by the customer. Should the buyer use Vishay Semiconductors products for any unintended or unauthorized application, the buyer shall indemnify Vishay Semiconductors against all claims, costs, damages, and expenses, arising out of, directly or indirectly, any claim of personal damage, injury or death associated with such unintended or unauthorized use.

Vishay Semiconductor GmbH, P.O.B. 3535, D-74025 Heilbronn, Germany  
Telephone: 49 (0)7131 67 2831, Fax number: 49 (0)7131 67 2423



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

## Material Category Policy

**Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.**

**Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.**