



Optocoupler



ONLINE CERTIFICATIONS DIRECTORY

FPQU8.E52744
Optical Isolators Certified for Canada - Component

Page Bottom

Optical Isolators Certified for Canada - Component

See General Information for Optical Isolators Certified for Canada - Component

VISHAY INFRARED COMPONENTS INC
2201 LAURELWOOD RD
SANTA CLARA, CA 95054-1516 USA

E52744

- Double Protected optical isolators having an isolation voltage of 5300 Vac, Model(s) VOT8024A, VOT8026, VOT8025, VOT8121A
Double protection optical isolator having an isolation voltage of 5300Vrms, Model(s) VOW135\*, VOW136\*, VOW137\*, VOW138\*, VOW139\*, VOW22XX@, VOW2601\*, VOW2611\*, VOW312X@
Double protection Optical isolator, insulation, provides 3750 Vac isolation, Model(s) SFH1690\*, SFH690\*, SFH691\*, SFH6916\*, VO160\*, VOM160\*, VOM305\*, VOM45\*, VOM618\*
Double protection optical isolator, provides 3125 Vac isolation, Model(s) SFH692\*
Double protection optical isolator, providing 4420 Vac isolation, System H, Model(s) SFH61\*
Double protection optical isolators having an isolation voltage of 2500Vrms, Model(s) LH1529FG, LH1529GP, LH1532FP
Double protection optical isolators having an isolation voltage of 3750 V ac, Model(s) VOM617A, VOM618A, VOS615A, VOS617A, VOS618A, VOS625A, VOS627A, VOS628A, VOT8024AM, VOT8121AM
Double protection optical isolators having an isolation voltage of 3750 Vrms, Model(s) LH1546AEF\*, VO1400\*, VOM1271\*, VOMA617\*, VOR1142(M4)#
Double protection optical isolators having an isolation voltage of 4420Vrms, Model(s) BRT1x, BRT2x, CNY1, CNY74, H11Ax, H11Bx, H11Dx, IL1, IL2, IL250, IL251, IL252, IL255, IL30, IL300, IL410/IL4108, IL4116, IL4117, IL4118, IL420/IL4208, IL4216, IL4217, IL4218, IL5, IL66, IL66B, IL755, IL755B, IL766, IL766B, ILD1, ILD1615, ILD2, ILD250, ILD251, ILD252, ILD30, ILD31, ILD32, ILD5, ILD55, ILD610, ILD615, ILD620, ILD621, ILD66, ILD74, ILD755, ILD766, ILQ1, ILQ1615, ILQ2, ILQ30, ILQ31, ILQ32, ILQ5, ILQ55, ILQ615, ILQ620, ILQ621, ILQ66, ILQ74, K814, K815, K824, K825, K827, K844, K845, K847, LH1544, MCA230, MCA231, MCA255, MCT5210, MCT5211, MCT6, MCT62H, MCT6H, MOC810, SFH1617A, SFH600, SFH601, SFH608, SFH6106, SFH610A, SFH6156, SFH615A, SFH6176, SFH617A, SFH6186, SFH618A, SFH619A, SFH6206, SFH620A, SFH6286, SFH628A, SFH636, SFH640, SFH655A, TCED1100, TCED2100, TCED4100, TCET1600, TCET2100, TCET2200, TCET2600, TCET4100, TCET4600, VO3052, VO3053, VO3062, VO3063, VO4154, VO4156, VO4157, VO4158, VO4254, VO4256, VO4257, VO4258
Double protection optical isolators having an isolation voltage of 5000 Vrms, Model(s) SFH601, SFH619A, SFH640, H11D1, VOH1016, VOT8123, VOT8125
Double protection optical isolators having an isolation voltage of 5000Vrms, Model(s) 4N25, 4N26, 4N27, 4N28, 4N35, 4N36, 4N37, 4N38, 6N137A, CNY117, CNY117F
Double protection optical isolators having an isolation voltage of 5000Vrms, Model(s) CNY17, may be followed by M, S, F, FM, FS, then followed by 1, 2, 3 or 4.
Double protection optical isolators having an isolation voltage of 5000Vrms, Model(s) CNY17F
Double protection optical isolators having an isolation voltage of 5300 V ac, Model(s) VOD3120
Double protection optical isolators having an isolation voltage of 5300Vrms, Model(s) 6N1135\*, 6N1136\*, 6N135\*, 6N136\*, 6N137\*, 6N138\*, 6N139\*, LH1500A\*, LH1503A\*, LH1505A\*, LH1510A\*, LH1513A\*, LH1518A\*, LH1520A\*, LH1522A\*, LH1525A\*, LH1526A\*, LH1529A\*, LH1529B\*, LH1532A\*, LH1533A\*, LH1535A\*, LH1540A\*, LH1546AA\*, LH1546AD\*, LH1546AT\*, LH1550A1\*, LH1556A\*, SFH1617A, SFH6135\*, SFH6136\*, SFH6138\*, SFH6139\*, SFH615A, SFH617A, SFH632x@, SFH6345\*, SFH670x@, SFH671x@, SFH673x@, SFH674x@, SFH675x@, VO14642A\*, VO2601\*, VO2611\*, VO263x@, VO4661\*, VO615C, VO617A, VO617B, VO617C, VO618A, VO618C, VOR1121(B6)#, VOR1142(A4)#, VOR1142(A6)#, VOR1142(B4)#, VOR1142(B6)#, VOR2121(A8)#, VOR2121(B8)#, VOR2142(A8)#, VOR2142(B8)#
Double protection optical isolators, providing 5000 Vac isolation, Model(s) 4N\*, CNY17\*, CNY75\*, CQY80\*, HS817\*, K233\*, K817P\*, TCDT110\*, TCDT111\*, TCDT112\*, TCET110\*, TCET111\*, TCET120\*, VO610A\*, VO615A\*
Double protection optical isolators, providing 5300 Vac isolation, Model(s) LH1262\*, VO1162\*, VO1263\*, VO15665\*
Optical isolators, single protection type, providing 3333 Vac isolation, System Y, Model(s) IL12\*, IL20\*, IL21\*, IL22\*, IL256\*, ILD12\*, ILD20\*, ILD21\*, ILD22\*, ILD256\*, ILD28\*, SFH63\*, SFH672\*, SFH674\*, SFH675\*, VO06\*, VO20\*
Optical isolators, single protection type, providing 3333 Vac isolation, System Y, Model(s) VO21\*, VO22\*, VOD20\*, VOD22\*
Single protection optical isolator, providing 4420 Vac isolation, System H, Model(s) VO2223, VO2223\*
Single protection optical isolator, providing 4420 Vac isolation, System H, Model(s) VO31x0, where x may be any number, may be followed by additional letters.
Single protection optical isolator, providing 4420 Vac isolation, System H, Model(s) VO31x0@, VO3526, VO3526\*
Single protection optical isolators, providing 4420 Vac isolation., Model(s) 4N3\*, K30\*

# - May be followed by additional alphanumeric characters, the VOR prefix shown and the suffixes in parentheses are optional.
(&) - where "X" can be any number between 0-9.
\* - May be followed by alphanumeric characters.
@ - Where X is any number, may be followed by additional alphanumeric characters.



Note - In addition to trademark/ tradename - system, model or catalog designation on the device itself or on the smallest shipping container. System designation may be preceded by an maximum 4 digit date code, and may be followed by the factory identification code, with or without spaces due to space constraints.

Marking: Company name or tradename "E52744" or trademark  , model designation and the Recognized Component Mark for Canada,



Last Updated on 2018-03-02

[Questions?](#)

[Print this page](#)

[Terms of Use](#)

[Page Top](#)

© 2018 UL LLC

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2018 UL LLC".