




Optocoupler



FPQU8.E52744
Optical Isolators Certified for Canada - Component

Page Bottom

Optical Isolators Certified for Canada - Component

See General Information for Optical Isolators Certified for Canada - Component

VISHAY INFRARED COMPONENTS INC
2201 LAURELWOOD RD
SANTA CLARA, CA 95054-1516 USA

E52744

Double protection optical isolator, provides 3125 Vac isolation, Model SFH692, may be followed by additional numbers and/or letters.

Double protection Optical isolator, insulation, provides 3750 Vac isolation, Models SFH690, SFH691, SFH1690, SFH6916, VO160, VOM45, VOM160, VOM305, and VOM618. All may be followed by additional numbers and/or letters.

Optical isolators, single protection type, providing 3333 Vac isolation, System Y: Models IL12, IL20, IL21, IL22, IL256, ILD12, ILD20, ILD21, ILD22, ILD256, ILD28, SFH63, SFH672, SFH674, SFH675, VO06, VO20, VO21, VO22, VOD20, VOD22 may be followed by additional numbers and/or letters.

Single protection optical isolator, providing 4420 Vac isolation, System H, Models VO2223, VO3526; Model VO31x0, where x may be any number. All models may be followed by additional letter(s).

Single protection optical isolators, having an isolation voltage of 4420Vrms, Models 4N3 and K30.

Double protection optical isolator, providing 4420 Vac isolation, System H, Model SFH61, may be followed by additional letters and numbers.

Double protection optical isolators, providing 5000 Vac isolation Models 4N, CNY17, CNY75, CQY80, K233, TCDDT110, TCDDT111, TCDDT112, HS817, K817P, TCET110, TCET111, TCET120, VO610A, VO615A, All models may be followed by additional alphanumeric characters.

Double protection optical isolators having an isolation voltage of 2500Vrms, Models LH1529FG, LH1529GP, and LH1532FP.

Double protection optical isolators having an isolation voltage of 5300Vrms, Models SFH617A, SFH1617A, SFH615A, VO617A, VO618A, VO615C, VO617C, VO618C, VO617B.

Double protection optical isolators having an isolation voltage of 5000Vrms, Model 6N137A, 4N25, 4N26, 4N27, 4N28, 4N35, 4N36, 4N37, 4N38, CNY17 [+], CNY117, CNY17F, CNY117F.

Double protection optical isolators, providing 5300 Vac isolation, Models LH1262, VO1162, VO1263 and VO15665. All models may be followed by additional alphanumeric characters.

Double protection optical isolators having an isolation voltage of 3750 Vrms, Models LH1546AEF, VO1400, VOM1271. All models may be followed by additional alphanumeric characters.

Double protection optical isolators having an isolation voltage of 5300Vrms, Models LH1500A, LH1503A, LH1505A, LH1510A, LH1513A, LH1518A, LH1520A, LH1522A, LH1525A, LH1526A, LH1529A, LH1529B, LH1532A, LH1533A, LH1535A, LH1540A, LH1546AA, LH1546AT, LH1546AD, LH1550A1, LH1556A, VO14642A. All models may be followed by additional alphanumeric characters.

Double protection optical isolators having an isolation voltage of 3750 V ac, Models VOS615A, VOS617A, VOS618A, VOS625A, VOS627A, VOS628A, VOM617A, VOM618A.

Double protection optical isolator having an isolation voltage of 5300Vrms, Models VOW135, VOW136, VOW137, VOW138, VOW139, VOW22XX, VOW312X, VOW2601, VOW2611, where X is any number. All models may be followed by additional alphanumeric characters.

Double protection optical isolators having an isolation voltage of 5300Vrms, Models 6N135, 6N136, 6N137, 6N138, 6N139, 6N1135, 6N1136, SFH6135, SFH6136, SFH6138, SFH6139, SFH632x, SFH6345, SFH670x, SFH671x, SFH673x, SFH674x, SFH675x, VO2601, VO2611, VO263x, VO4661, where x is any number. All models may be followed by additional alphanumeric characters.


[+] - may be followed by M, S, F, FM, FS, then followed by 1, 2, 3 or 4.

Double protection optical isolators having an isolation voltage of 4420Vrms, Models BRT1x, BRT2x, CNY1, CNY74, H11Ax, H11Bx, H11Dx, IL410/IL4108, IL420/IL4208, IL4116, IL4117, IL4118, IL4216, IL4217, IL4218, IL250, IL251, IL252, IL255, ILD250, ILD251, ILD252, IL1, IL5, IL2, IL30, IL755, IL755B, ILD755, IL766, IL766B, ILD766, IL66, IL66B, ILD66, ILQ66, ILD1, ILD2, ILD5, ILD74, ILQ74, ILQ1, ILQ2, ILQ5, ILD620, ILQ620, ILD615, ILD621, ILQ615, ILQ621, ILD30, ILD31, ILD32, ILD55, ILQ30, ILQ31, ILQ32, ILQ55, IL300, ILD610, ILD1615, ILQ1615, K815, K825, K845, K814, K824, K844, LH1544, MCA230, MCA231, MCA255, MCT5210, MCT5211, MOC810, MCT6, MCT6H, MCT62H, SFH600, SFH601, SFH608, SFH655A, SFH6206, SFH620A, SFH6286, SFH628A, SFH636, SFH640, SFH610A, SFH6106, SFH615A, SFH6156, SFH617A, SFH6176, SFH618A, SFH6186, SFH619A, SFH1617A, VO3052, VO3053, VO3062, VO3063, VO4154, VO4156, VO4157, VO4158, VO4254, VO4256, VO4257, VO4258, K827, K847, TCED1100, TCED2100, TCED4100, TCET1600, TCET2100, TCET2200, TCET2600, TCET4100, TCET4600.



Marking: Company name or "E52744" or trademark and system, model or catalog designation, and Recognized Component Mark for



Canada  on the device or smallest shipping carton. System designation may be preceded by an maximum 4 digit date code, and may be followed by the factory identification code, with or without spaces due to space constraints.

Last Updated on 2015-02-05

[Questions?](#)

[Print this page](#)

[Terms of Use](#)

[Page Top](#)

© 2015 UL LLC

When the UL Leaf Mark is on the product, or when the word "Environment" is included in the UL Mark, please search the [UL Environment database](#) for additional information regarding this product's certification.

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2015 UL LLC".