


Silicon NPN Phototransistor



FEATURES

- Package type: chip
- Package form: chip
- Dimensions (L x W x H in mm): 0.39 x 0.39 x 0.185
- High photo sensitivity
- High collector current
- Small size
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



DESCRIPTION

T5096P is an epitaxial phototransistor especially designed for optocoupler applications. Despite its small size it has a high sensitivity and ability to drive high currents even under saturation.

GENERAL INFORMATION

The datasheet is based on Vishay optoelectronics sample testing under certain predetermined and assumed conditions, and is provided for illustration purpose only. Customers are encouraged to perform testing in actual proposed packaged and used conditions. Vishay optoelectronics die products are tested using Vishay optoelectronics based quality assurance procedures and are manufactured using Vishay optoelectronics established processes. Estimates such as those described and set forth in this datasheet for semiconductor die will vary depending on a number of packaging, handling, use, and other factors. Therefore sold die may not perform on an equivalent basis to standard package products.

PRODUCT SUMMARY

COMPONENT	I_{ca} (μA)	φ (deg)	$\lambda_{0.1}$ (nm)
T5096P	200 to 310	± 60	480 to 1080

Note

- Test conditions see table "Basic Characteristics"

ORDERING INFORMATION

ORDERING CODE	PACKAGING	REMARKS	PACKAGE FORM
T5096P-SD-F	Wafer sawn on foil with disco frame	MOQ: 200 000 pcs	Chip

Note

- MOQ: minimum order quantity

ABSOLUTE MAXIMUM RATINGS ($T_{amb} = 25\text{ }^{\circ}C$, unless otherwise specified)

PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT
Collector emitter voltage		V_{CEO}	85	V
Emitter collector voltage		V_{ECO}	7.8	V
Collector current		I_C	50	mA
Junction temperature		T_j	125	$^{\circ}C$
Operating temperature range		T_{amb}	-55 to +125	$^{\circ}C$
Storage temperature range		T_{stg1}	-55 to +150	$^{\circ}C$

BASIC CHARACTERISTICS ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)						
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Collector emitter breakdown voltage	$E = 0\text{ mW/cm}^2$; $I_C = 10\text{ }\mu\text{A}$	$V_{(BR)CEO}$	85			V
Collector emitter dark current	$V_{CE} = 50\text{ V}$, $E = 0\text{ lx}$	I_{CEO}		< 1	50	nA
Wavelength of peak sensitivity		λ_p		910		nm
Range of spectral bandwidth		$\lambda_{0.1}$		480 to 1080		nm

Note

- The measurements are based on samples of die which are mounted on a TO-header without resin coating


BASIC CHARACTERISTICS ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)


Fig. 1 - Relative Spectral Sensitivity vs. Wavelength




Fig. 2 - Collector Emitter Capacitance vs. Collector Emitter Voltage


MECHANICAL DIMENSIONS						
PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	
Length of chip edge (x-direction)	L_x		0.39		mm	
Length of chip edge (y-direction)	L_y		0.39		mm	
Die height	H	0.170	0.185	0.200	mm	
Bond pad emitter	d		$\varnothing 0.10$ (bonding area)		mm	

ADDITIONAL INFORMATION	
Frontside metallization, emitter	AlSi 1.2 μm
Backside metallization, collector	AuSb 0.4 μm
Dicing	Sawing
Die bonding technology	Epoxy bonding

Note

- All products are checked in accordance with the Vishay Semiconductor, specification of visual inspection FVOV6870. The visual inspection shall be made in accordance with the "specification of visual inspection as referenced". The visual inspection of wafer backside is performed with stereo microscope with incident light and 40x to 80x magnification. The quality inspection (final visual inspection) is performed by production. An additional visual inspection step as special release procedure by QM is not installed.

CHIP DIMENSIONS in millimeters



Note

- Not indicated tolerances: ± 0.005
- (1) Only for information: dimension of sawn die under consideration of 30 μm saw kerf

HANDLING AND STORAGE CONDITIONS

- The hermetically sealed shipment lots shall be opened in temperature and moisture controlled cleanroom environment only. It is mandatory to follow the rules for disposition of material that can be hazardous for humans and environment.
- Product must be handled only at ESD safe workstations. Standard ESD precautions and safe work environments are as defined in MIL-HDBK-263.
- Singulated die are not to be handled with tweezers. A vacuum wand with non metallic ESD protected tip should be used.

PACKING

Chips are fixed on adhesive foil. For shipment, the wafers are arranged to stacks and hermetically sealed in plastic bags to ensure protection against environmental influence (humidity and contamination).
 Use for recycling reliable operators only. We can help getting in touch with your nearest sales office. By agreement we will take back packing material, if it is sorted. You will have to bear the costs of transport. We will invoice you for any costs incurred for packing material that is returned unsorted or which we are not obliged to accept.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.