

R-C Thermal Model Parameters

DESCRIPTION

The parametric values in the R-C thermal model have been derived using curve-fitting techniques. R-C values for the electrical circuit in the Foster/tank and Cauer/filter configurations are included. When implemented in P-SPICE, these values have matching characteristic curves to the single-pulse transient thermal impedance curves for the MOSFET.

These RC values can be used in the P-SPICE simulation to evaluate the thermal behavior of the MOSFET junction temperature under a defined power profile. These techniques are described in application note AN609, "Thermal Simulation of Power MOSFETs on the P-SPICE Platform".

R-C THERMAL MODEL FOR TANK CONFIGURATION



R-C VALUES FOR TANK CONFIGURATION			
THERMAL RESISTANCE (°C/W)			
Junction to	Ambient	Case	Foot
RT1	N/A	14.2126	N/A
RT2	N/A	8.8736	N/A
RT3	N/A	3.6050	N/A
RT4	N/A	13.3088	N/A
THERMAL CAPACITANCE (Joules/°C)			
Junction to	Ambient	Case	Foot
CT1	N/A	123.3086m	N/A
CT2	N/A	7.0034m	N/A
CT3	N/A	243.5268m	N/A
CT4	N/A	813.1737m	N/A

Note

N/A indicates not applicable

This document is intended as a SPICE modeling guideline and does not constitute a commercial product datasheet. Designers should refer to the appropriate datasheet of the same number for guaranteed specification limits.

R-C THERMAL MODEL FOR FILTER CONFIGURATION


R-C VALUES FOR FILTER CONFIGURATION			
THERMAL RESISTANCE (°C/W)			
Junction to	Ambient	Case	Foot
RF1	N/A	5.7044	N/A
RF2	N/A	16.4166	N/A
RF3	N/A	8.4326	N/A
RF4	N/A	9.4464	N/A
THERMAL CAPACITANCE (Joules/°C)			
Junction to	Ambient	Case	Foot
CF1	N/A	3.4965m	N/A
CF2	N/A	31.1355m	N/A
CF3	N/A	328.0864m	N/A
CF4	N/A	36.0185u	N/A

Note

N/A indicates not applicable



IRLL014, SiHLL014 Tank j-c Temperature: 27.0



IRLL014, SiHLL014 Filter j-c Temperature: 27.0

