

R-C Thermal Model Parameters

DESCRIPTION

The parametric values in the R-C thermal model have been derived using curve-fitting techniques. R-C values for the electrical circuit in the Foster/tank and Cauer/filter configurations are included. When implemented in P-SPICE, these values have matching characteristic curves to the single-pulse transient thermal impedance curves for the MOSFET.

These RC values can be used in the P-SPICE simulation to evaluate the thermal behavior of the MOSFET junction temperature under a defined power profile. These techniques are described in application note AN609, "Thermal Simulation of Power MOSFETs on the P-SPICE Platform".

R-C THERMAL MODEL FOR TANK CONFIGURATION



R-C VALUES FOR TANK CONFIGURATION			
THERMAL RESISTANCE (°C/W)			
Junction to	Ambient	Case	Foot
RT1	N/A	1.3994	N/A
RT2	N/A	670.4329m	N/A
RT3	N/A	289.4710m	N/A
RT4	N/A	1.2332	N/A
THERMAL CAPACITANCE (Joules/°C)			
Junction to	Ambient	Case	Foot
CT1	N/A	120.2206m	N/A
CT2	N/A	30.1813m	N/A
CT3	N/A	3.1535m	N/A
CT4	N/A	1.1064	N/A

Note

N/A indicates not applicable

This document is intended as a SPICE modeling guideline and does not constitute a commercial product datasheet. Designers should refer to the appropriate datasheet of the same number for guaranteed specification limits.



R-C THERMAL MODEL FOR FILTER CONFIGURATION




R-C VALUES FOR FILTER CONFIGURATION			
THERMAL RESISTANCE (°C/W)			
Junction to	Ambient	Case	Foot
RF1	N/A	434.8514m	N/A
RF2	N/A	1.1466	N/A
RF3	N/A	987.8640m	N/A
RF4	N/A	1.0126	N/A
THERMAL CAPACITANCE (Joules/°C)			
Junction to	Ambient	Case	Foot
CF1	N/A	3.0578m	N/A
CF2	N/A	30.1159m	N/A
CF3	N/A	115.7306m	N/A
CF4	N/A	976.0367m	N/A

Note

N/A indicates not applicable



IRLIZ34G, SiHLIZ34G Tank j-c Temperature: 27.0



IRLIZ34G, SiHLIZ34G Filter j-c Temperature: 27.0

