


R-C Thermal Model Parameters

DESCRIPTION

The parametric values in the R-C thermal model have been derived using curve-fitting techniques. R-C values for the electrical circuit in the Foster/tank and Cauer/filter configurations are included. When implemented in P-SPICE, these values have matching characteristic curves to the single-pulse transient thermal impedance curves for the MOSFET.

These RC values can be used in the P-SPICE simulation to evaluate the thermal behavior of the MOSFET junction temperature under a defined power profile. These techniques are described in application note AN609, "Thermal Simulation of Power MOSFETs on the P-SPICE Platform".

R-C THERMAL MODEL FOR TANK CONFIGURATION




R-C VALUES FOR TANK CONFIGURATION			
THERMAL RESISTANCE (°C/W)			
Junction to	Ambient	Case	Foot
RT1	53.8025	N/A	N/A
RT2	43.3725	N/A	N/A
RT3	17.4603	N/A	N/A
RT4	5.3647	N/A	N/A
THERMAL CAPACITANCE (Joules/°C)			
Junction to	Ambient	Case	Foot
CT1	483.6474m	N/A	N/A
CT2	221.9751m	N/A	N/A
CT3	34.0005m	N/A	N/A
CT4	2.6819m	N/A	N/A

Note

N/A indicates not applicable

This document is intended as a SPICE modeling guideline and does not constitute a commercial product datasheet. Designers should refer to the appropriate datasheet of the same number for guaranteed specification limits.

R-C THERMAL MODEL FOR FILTER CONFIGURATION



R-C VALUES FOR FILTER CONFIGURATION			
THERMAL RESISTANCE (°C/W)			
Junction to	Ambient	Case	Foot
RF1	7.4366	N/A	N/A
RF2	23.5780	N/A	N/A
RF3	59.6050	N/A	N/A
RF4	29.3804	N/A	N/A
THERMAL CAPACITANCE (Joules/°C)			
Junction to	Ambient	Case	Foot
CF1	3.0426m	N/A	N/A
CF2	29.8968m	N/A	N/A
CF3	113.4501m	N/A	N/A
CF4	545.6212m	N/A	N/A

Note

N/A indicates not applicable

