

R-C Thermal Model Parameters

DESCRIPTION

The parametric values in the R-C thermal model have been derived using curve-fitting techniques. R-C values for the electrical circuit in the Foster/tank and Cauer/filter configurations are included. When implemented in P-SPICE, these values have matching characteristic curves to the single-pulse transient thermal impedance curves for the MOSFET.

These RC values can be used in the P-SPICE simulation to evaluate the thermal behavior of the MOSFET junction temperature under a defined power profile. These techniques are described in application note AN609, "Thermal Simulation of Power MOSFETs on the P-SPICE Platform".

R-C THERMAL MODEL FOR TANK CONFIGURATION



R-C VALUES FOR TANK CONFIGURATION			
THERMAL RESISTANCE (°C/W)			
Junction to	Ambient	Case	Foot
RT1	N/A	291.5303m	N/A
RT2	N/A	326.0257m	N/A
RT3	N/A	111.5256m	N/A
RT4	N/A	22.2893m	N/A
THERMAL CAPACITANCE (Joules/°C)			
Junction to	Ambient	Case	Foot
CT1	N/A	178.8385m	N/A
CT2	N/A	25.2807m	N/A
CT3	N/A	5.8661m	N/A
CT4	N/A	1.2754m	N/A


Note

N/A indicates not applicable

This document is intended as a SPICE modeling guideline and does not constitute a commercial product datasheet. Designers should refer to the appropriate datasheet of the same number for guaranteed specification limits.



R-C THERMAL MODEL FOR FILTER CONFIGURATION




R-C VALUES FOR FILTER CONFIGURATION			
THERMAL RESISTANCE (°C/W)			
Junction to	Ambient	Case	Foot
RF1	N/A	117.4581m	N/A
RF2	N/A	301.8195m	N/A
RF3	N/A	273.3666m	N/A
RF4	N/A	58.0172m	N/A
THERMAL CAPACITANCE (Joules/°C)			
Junction to	Ambient	Case	Foot
CF1	N/A	2.3823m	N/A
CF2	N/A	11.3341m	N/A
CF3	N/A	68.3331m	N/A
CF4	N/A	739.0791m	N/A

Note

N/A indicates not applicable



IRFSL11N50A, SiHFSL11N50A Tank j-c Temperature: 27.0



IRFSL11N50A, SiHFSL11N50A Filter j-c Temperature: 27.0

