

R-C Thermal Model Parameters

DESCRIPTION

The parametric values in the R-C thermal model have been derived using curve-fitting techniques. R-C values for the electrical circuit in the Foster/tank and Cauer/filter configurations are included. When implemented in PSpice, these values have matching characteristic curves to the single-pulse transient thermal impedance curves for the MOSFET.

These RC values can be used in the PSpice simulation to evaluate the thermal behavior of the MOSFET junction temperature under a defined power profile. These techniques are described in application note AN609, "Thermal Simulation of Power MOSFETs on the PSpice Platform".

R-C THERMAL MODEL FOR TANK CONFIGURATION



R-C VALUES FOR TANK CONFIGURATION			
THERMAL RESISTANCE (°C/W)			
Junction to	Ambient	Case	Foot
RT1	n/a	408.0540m	n/a
RT2	n/a	375.1460m	n/a
RT3	n/a	1.4992	n/a
RT4	n/a	1.3176	n/a
THERMAL CAPACITANCE (Joules/°C)			
Junction to	Ambient	Case	Foot
CT1	n/a	1.2099m	n/a
CT2	n/a	16.3222m	n/a
CT3	n/a	173.3147m	n/a
CT4	n/a	199.8346m	n/a

Note

- n/a indicates not applicable

This document is intended as a SPICE modeling guideline and does not constitute a commercial product datasheet. Designers should refer to the appropriate datasheet of the same number for guaranteed specification limits.



R-C THERMAL MODEL FOR FILTER CONFIGURATION




R-C VALUES FOR FILTER CONFIGURATION			
THERMAL RESISTANCE (°C/W)			
Junction to	Ambient	Case	Foot
RF1	n/a	630.2240m	n/a
RF2	n/a	270.6278m	n/a
RF3	n/a	709.1276m	n/a
RF4	n/a	1.9919	n/a
THERMAL CAPACITANCE (Joules/°C)			
Junction to	Ambient	Case	Foot
CF1	n/a	1.3355m	n/a
CF2	n/a	50.9975m	n/a
CF3	n/a	23.2858u	n/a
CF4	n/a	64.7844m	n/a

Note

- n/a indicates not applicable



SiHF21N65EF Tank j-c Temperature:27.0



SiHF21N65EF Filter j-c Temperature:27.0

